

Leaded Inductors (Fixed Choke Coils)

FASTRON leaded inductors come with a very wide inductance range from 0.1µH to 100 000µH and with high Q values. They are available in tape and ammopack packing.

Applications These components are suitable for decoupling and interference suppression. Communication: RF blocking and filtering, e.g. 12 ~ 16 kHz blocking filter Others: Automotive electronics, electronic household appliances, entertainment electronics and lighting devices

Technical	Data

L – Value (rated inductance)	Measured with Bode 100 Vector Network Analyzer at frequency f
Q – Factor (min)	Measured with Bode 100 Vector Network Analyzer at frequency fq
SRF (min)	Measured with HP 8753ES Network Analyzer
DCR (max)	Measured at 25°C
Rated DC Current	I based on temperature rise, determined at the point where the temperature rise does not exceed
	40°C above the ambient temperature of 25°C
	I1 Current based on ambient temperature of 40°C and component temperature of max. 125°C
	Isat Current based on inductivity drop of 10% related to the unloaded inductivity
Operating Temperature	-55°C to +125°C (includes component self-heating)
Recommended soldering method	Wave
Solderability	Using lead free solder (Sn 99.9) at 260°C ± 5°C for 5 ± 0.5 seconds, min 90% solder coverage of
	metallization
	Standard: IEC 68-2-20 (Ta)
Resistance to Soldering Heat	Resistant to $260^{\circ}C \pm 5^{\circ}C$ for 10 ± 1 seconds
	Standard: IEC 68-2-20 (Tb)
Resistance to Solvent	Resistant to Isopropyl alcohol for 5 ± 0.5 minutes at $23^{\circ}C \pm 5^{\circ}C$
	Standard: IEC 68-2-45
Climatic Test	Defined by the following standards
	IEC 68-2-1 for Cold test: -55°C for 96 hours
	IEC 68-2-2 for Dry heat test: +125°C for 96 hours
	IEC 60068-2-78 for Humidity test: 40°C at RH 95% for 4 days
Tensile Strength of Leads	Components withstand a pulling force of 10N for 10 ± 1 seconds
(Pull Test)	IEC 60068-2-21 (Ua ₁)
Mechanical Shock	Mil-Std 202 Method 213
	Condition C
	3 axis, 6 times, total 18 shocks
	100 G, 6 ms, half-sine
Vibration	Mil-Std 202 Method 204
	20 mins at 5G
	10 Hz to 2000 Hz
	12 cycles each of 3 orientations

Colour Coding Reference according to IEC 60062 :

L (µH)	Nominal Inductance (µH)			Tol. **	
Code	Band 1	Band 2	Band 3	Band 4	code
Gold			x 0.1	± 5%	J
Silver			x0.01	± 10 %	К
Clear				± 20 %	М
Black		0	x1		
Brown	1	1	x10	±1%	F
Red	2	2	x100	±2%	G
Orange	3	3	x1000	±3%	А
Yellow	4	4	x10000		
Green	5	5			
Blue	6	6			
Violet	7	7			
Grey	8	8			
White	9	9			

Ordering Code

Example: SMCC-180X-YY

SMCC - 180 X - YY (Model) (Inductance Value) (Tolerance) (Packing Code) SMCC -

SMCC-180K-01

Core Type

Tolerances

-	Ferrite	, Phenolic	


- F (1%), G (2%), H (2.5%), A (3%), J (5%), K (10%), M (20%)

Packing Code	Packing Form	Taped / Reel	Taped / Ammopack
	Axial	01	02
	Radial	31, 51	32



Packing Specification








Fig. 2: Ammopack, axial Packing code : 02




Fig. 3: Axial Standard Taping (65mm) Packing code : 01, 02




Fig. 5: Radial Taping Packing code : 31, 32




Fig. 4: Axial Narrow Taping (38mm)

Packing code : 11, 12





Fig. 6: Ammopack, radial Packing code : 32



Packing Specification










Fig. 8: Axial preformed Packing code : 20




Fig. 9: Radial, (with kink) loose form Packing code : 40




Fig. 10: Radial, (without kink) loose form Packing code : 50

