DATASHEET - LSM-11S/RL



Safety position switch, metal, 1N/O+1N/C, rotary lever, smap-action contact



Part no. Catalog No. Eaton Catalog No. LSM-11S/RL EL-Nummer (Norway)

LSM-11S/RL 266152 4356147

Delivery program

Delivery program	
Basic function	Position switches Safety position switches
Part group reference	LS(M)
Product range	Rotary lever
Degree of Protection	IP66, IP67
Features	Complete unit
Ambient temperature	°C -25 - +70
Design	EN 50047 Form A
Snap-action contact	Yes
Contacts	
N/O = Normally open	1 N/O
N/C = Normally closed	1 NC 🛞
Notes) = safety function, by positive opening to IEC/EN 60947-5-1
Contact sequence	$-\frac{13}{14}$
Contact travel = Contact closed = Contact open	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$
Positive opening (ZW)	yes
Colour	
Enclosure covers	Yellow
Enclosure covers	
Housing	Metal
Connection type	Cage Clamp
Notes	Cage-Clamp is a registered trademark of Wago Kontakttechnik, 32432 Minden, Germany. Accessories for the Cage-Clamp terminals from Wago:power comb, gray, Wago

Technical data General		
Standards		IEC/EN 60947
Climatic proofing		Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Ambient temperature	°C	-25 - +70

	mm ²	1 x (0.5 - 2.5)
		1 x (0.5 - 1.5)
U _{imp}	V AC	4000
Ui	V	400
		III/3
l _e	А	
le	A	6
le	А	6
le	A	4
le	А	3
le	А	0.6
I _e	A	0.3
H _F	Fault probabilit	< 10 ⁻⁷ , < 1 fault in 107 operations ty
H _F	Fault probabilit	< 10 ⁻⁶ , < 1 failure at 5 x 10 ⁶ operations ty
	Hz	max. 400
	A gG/gL	6
	mm	0.15
Operations	x 10 ⁶	8
	g	25
Operations/h		≦ 6000
		1000
		1.0/8.0
		0.2
	m/s	1.5 for angle of actuation $\alpha = 0^{\circ}$
	Ie Ie	Uimp V AC Uimp V AC Ui V Ui V Ie A Ie Ie Ie Ie <t< td=""></t<>

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	In	А	6
Heat dissipation per pole, current-dependent	P _{vid}	W	0.17
Equipment heat dissipation, current-dependent	P _{vid}	W	0
Static heat dissipation, non-current-dependent	P _{vs}	W	0
Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0

Sensors (EG000026) / End switch (EC000030)

Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Position switch (Type 1) (ecl@ss10.0.1-27-27-06-01 [AGZ382015])


Width sensor	mm	31
Diameter sensor	mm	0
Height of sensor	mm	61
Length of sensor	mm	33.5
Rated operation current le at AC-15, 24 V	А	6
Rated operation current le at AC-15, 125 V	А	6
Rated operation current le at AC-15, 230 V	А	6
Rated operation current le at DC-13, 24 V	А	3
Rated operation current le at DC-13, 125 V	А	0.8
Rated operation current le at DC-13, 230 V	А	0.3
Switching function		Quick-break switch
Switching function latching		No
Output electronic		No
Forced opening		Yes
Number of safety auxiliary contacts		0
Number of contacts as normally closed contact		1
Number of contacts as normally open contact		1
Number of contacts as change-over contact		0
Type of interface		None
Type of interface for safety communication		None
Construction type housing		Cuboid
Material housing		Metal
Coating housing		Other
Type of control element		Rotary lever
Alignment of the control element		Other
Type of electric connection		Cable entry metrical
With status indication		No
Suitable for safety functions		Yes
Explosion safety category for gas		None
Explosion safety category for dust		None

Degree of protection (IP) IP67 Degree of protection (NEMA) 4X	Ambient temperature during operating	°C	2	25 - 70
Degree of protection (NEMA) 4X	Degree of protection (IP)		I	IP67
	Degree of protection (NEMA)		4	4X


Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	IEC: IP66, 67, UL/CSA Type 3R, 4X (indoor use only), 12, 13

Dimensions



Tightening torque of cover screws: 0.8 Nm ±0.2 Nm
 only with LS (insulated version)
 Fixing screws 2 x M4 ≥ 30
 M_A = 1.5 Nm



Additional product information (links)

IL053001ZU LS-Titan position switch: basic device

2)

Ø4