

PRODUCT DATASHEET FLOODLIGHT 20 W 4000 K IP65 BK

FLOODLIGHT 20 | Luminaire with symmetrical light output with 20 W



AREAS OF APPLICATION

- Replacement for floodlights with halogen lamps
- Car parks and underpasses
- Public areas
- Building facades
- Construction areas
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, f. e. by accumulation of dust

PRODUCT BENEFITS

- Energy savings of up to 90 % compared to halogen lamp floodlights
- Frosted cover made of tempered glass for uniform illumination
- Optimized weight and size due to compact design
- 3 years guarantee

PRODUCT FEATURES

- Luminaire efficacy: up to 110 lm/W
- Symmetrical beam angle: 100° x 100°
- Mounting bracket for up to 180° tilting
- Type of protection: IP65
- Impact resistance: IK07
- Ambient temperature in operation: -20...+50 °C
- Connection via 1 m cable, wiring required



March 11, 2019, 08:20:53 FLOODLIGHT 20 W 4000 K IP65 BK

TECHNICAL DATA

Electrical data


Nominal wattage	20.00 W
Operating mode	Integrated LED driver
Nominal voltage	220240 V
Power factor λ	> 0.90
Mains frequency	50/60 Hz

Photometrical data

Color temperature	4000 К
Luminous flux	2200 lm
Luminous efficacy	110 lm/W
Standard deviation of color matching	≤5 sdcm
Light color (designation)	Cool White
Color rendering index Ra	≥80

Light technical data

Dimensions & weight



Length	130.0 mm
Width	140.0 mm
Height	41.0 mm
Product weight	560.00 g
Cable length	1000 mm

Colors & materials

Body material	Polycarbonate (PC)
Housing color	Black

PRODUCT DATASHEET

Product color	Black
Cover material	Tempered glass

Temperatures & operating conditions

	Ambient temperature range	-2050 °C
--	---------------------------	----------

Lifespan

Lifespan L70 at 25 °C	50000 h
Lifespan L80 at 25 °C	30000 h
Lifespan L90 at 25 °C	15000 h

Additional product data

Mounting type	Surface
Mounting location	Wall / Ceiling / Floor


Capabilities


Dimmable	No
Type of connection	Cable, 3-pole
LED module replaceable	Not replaceable

Certificates & standards

Protection class IK (shock resistance)	IK07
Glow Wire Test according to IEC 695-2-1	650 ℃
Photobiological safety group EN62778	RG 1
Photobio. safety group acc. to EN62471	RG 0
Protection class	1
Type of protection	IP65
Standards	CE/CB/TÜV SÜD/EAC/RoHS

Light Distribution





LDC typ cone

LDC typ polar

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075097483	Folding carton box 1	46 mm x 146 mm x 197 mm	611.00 g	1.32 dm³
4058075097490	Shipping carton box 10	301 mm x 247 mm x 221 mm	6780.00 g	16.43 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.