

PRODUCT DATASHEETFLOODLIGHT 50 W 3000 K IP65 WT

FLOODLIGHT 50 | Luminaire with symmetrical light output with 50 W



AREAS OF APPLICATION

- Replacement for floodlights with halogen lamps
- Car parks and underpasses
- Garages
- Public areas
- Building facades
- Construction areas
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, f. e. by accumulation of dust

PRODUCT BENEFITS

- Energy savings of up to 90 % compared to halogen lamp floodlights
- Frosted cover made of tempered glass for uniform illumination
- Optimized weight and size due to compact design
- 3 years guarantee

PRODUCT FEATURES

Luminaire efficacy: up to 110 lm/WSymmetrical beam angle: 100° x 100°

- Mounting bracket for up to 180° tilting

Type of protection: IP65Impact resistance: IK07

- Ambient temperature in operation: -20...+50 °C

- Connection via 1 m cable, wiring required



TECHNICAL DATA

Electrical data

Nominal wattage	50.00 W
Operating mode	Integrated LED driver
Nominal voltage	220240 V
Power factor λ	> 0.90
Mains frequency	50/60 Hz


Photometrical data

Color temperature	3000 K
Luminous flux	5250 lm
Luminous efficacy	105 lm/W
Standard deviation of color matching	≤5 sdcm
Light color (designation)	Warm White
Color rendering index Ra	≥80

Light technical data

Beam angle 100 °	° x 100 °
------------------	-----------

Dimensions & weight



Length	155.0 mm
Width	180.0 mm
Height	46.0 mm
Product weight	930.00 g
Cable length	1000 mm

Colors & materials

Body material	Polycarbonate (PC)
Housing color	White

Product color	White
Cover material	Tempered glass
Temperatures & operating conditions	
Ambient temperature range	-2050 °C
Lifespan	
Lifespan L70 at 25 °C	50000 h
Lifespan L80 at 25 °C	30000 h
Lifespan L90 at 25 °C	15000 h
Additional product data	
Mounting type	Surface
Mounting location	Wall / Ceiling / Floor
Capabilities	
Dimmable	No
Type of connection	Cable, 3-pole
LED module replaceable	Not replaceable
Certificates & standards	
Protection class IK (shock resistance)	IK07
Glow Wire Test according to IEC 695-2-1	650 °C
Photobiological safety group EN62778	RG 1
Photobio. safety group acc. to EN62471	RG 0

I IP65


CE/CB/TÜV SÜD/EAC/RoHS


Protection class

Standards

Type of protection

Light Distribution





LDC typ cone LDC typ polar

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075097582	Folding carton box 1	52 mm x 186 mm x 207 mm	999.00 g	2.00 dm ³
4058075097599	Shipping carton box 10	385 mm x 277 mm x 231 mm	10380.00 g	24.63 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.