

PRODUCT DATASHEET

LN INDV D/I 1200 42 W 4000 K

LINEAR IndiviLED DIRECT/INDIRECT | Pendant luminaire for single luminaire or light line application

AREAS OF APPLICATION

- Direct replacement for luminaires with fluorescent lamps
- Offices, schools
- General indoor illumination
- Corridors, entrance areas
- Seamless linear lighting
- Shop lighting

PRODUCT BENEFITS

- Homogenous light distribution and reduced glare thanks to the IndiviLED optics
- Increased light comfort thanks to direct and indirect light emission
- The product family offers full lighting solution for different applications
- Energy savings of up to 50 % compared to T5 batten luminaires
- Robust structure with IK06

PRODUCT FEATURES

- Each LED with individual lens and reflector for UGR<16 and homogenous light distribution
- Additional module for indirect lighting with 850 lm
- Pendant mounting with suspension kit
- Linkable to an esthetic seamless light line with line connection adapter (surface or pendant mounting)
- Available with length of 1200 or 1500 mm
- Luminous flux up to 6550 lm
- Luminous efficacy: up to 120 lm/W



- Initial color consistency: < 4 SDCM
- Glow Wire Test according to IEC 60695-2-12: 850 °C

TECHNICAL DATA

Electrical data

Nominal wattage	42.00 W
Operating mode	Integrated LED driver
Nominal voltage	220...240 V
Power factor λ	>0.90
Mains frequency	50/60 Hz

Photometrical data

Color temperature	4000 K
Luminous flux	5050 lm
Luminous efficacy	120 lm/W
Standard deviation of color matching	<4 sdcM
Light color (designation)	Cool White
Color rendering index Ra	≥ 80

Light technical data

Beam angle	70 °
UGR lateral	<16
UGR longitudinal	<16

Dimensions & weight



Length	1199 mm
Width	120.0 mm
Height	40.0 mm
Product weight	2600.00 g

Colors & materials

Body material	Aluminum
Housing color	White
Product color	White
Cover material	Aluminium

Temperatures & operating conditions

Ambient temperature range	-20...45 °C
----------------------------------	-------------

Lifespan

Lifespan L70 at 25 °C	60000 h
Lifespan L80 at 25 °C	50000 h
Lifespan L90 at 25 °C	35000 h

Additional product data

Mounting type	Suspended
Mounting location	Ceiling



Capabilities

Dimmable	No
Type of connection	Screwless terminal
LED module replaceable	Not replaceable
Ball shot safe	No

Certificates & standards

Protection class IK (shock resistance)	IK06
Glow Wire Test according to IEC 695-2-1	650 °C
Photobiological safety group EN62778	RG 1
Photobio. safety group acc. to EN62471	RG 0
Protection class	I
Type of protection	IP20
Standards	CE/CB/ENEC/TÜV SÜD/EAC/RoHS

Light Distribution



LDC typ cone

LDC typ polar

EQUIPMENT / ACCESSORIES

- Ceiling connection box available
- Suspension kit available
- Line connection adapter available
- Through-wiring cable kit available

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075109742	Folding carton box 1	132 mm x 1334 mm x 52 mm	2393.00 g	9.16 dm ³
4058075109759	Shipping carton box 4	1357 mm x 207 mm x 169 mm	12102.00 g	47.47 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.