

PRODUCT DATASHEET

SPOT MULTI 2 x 30W 4000K FL WT/BK

SPOT MULTI 2x30W | Recessed mounted spotlight, swivelable with two spot



AREAS OF APPLICATION

- Accent- and general lighting for all kind of salesrooms
- Fashion shops, accessories shops
- Shops, boutiques
- Hotel rooms
- Cafés

PRODUCT BENEFITS

- Low flicker light thanks to special electronic control gear
- High luminous efficacy
- Covering against other ceiling installations thanks to closed sheet steel housing
- Easy replacement of external driver thanks plug with bayonet lock
- Functional and minimalistic design
- 5 years guarantee

PRODUCT FEATURES

- Large faceted reflector for high light output
- Beam angle: 38°
- Gimbal adjustment angle: +/- 25°



TECHNICAL DATA

Electrical data

Nominal wattage	2*30 W
Operating mode	External LED driver
Nominal voltage	220...240 V
Power factor λ	≥ 0.90
Mains frequency	50/60 Hz

Luminaire control gear data

ECG - Length	113 mm
ECG - Width	40 mm
Max. no. of lum. on circuit break. B16 A	16
Max. no. of lum. on circuit break. C10 A	13
Max. no. of lum. on circuit break. C16 A	20


Photometrical data

Color temperature	4000 K
Luminous flux	2*2700 lm
Luminous efficacy	90 lm/W
Standard deviation of color matching	≤ 4 sdc _m
Light color (designation)	Cool White
Color rendering index Ra	>80

Light technical data

Beam angle	38.00 °
------------	---------

Dimensions & weight



Length	330.0 mm
Width	173.0 mm

Height	135.0 mm
Product weight	2700.00 g

Colors & materials

Body material	Aluminum
Housing color	White
Product color	White
Cover material	Polymethylmethacrylate (PMMA)

Temperatures & operating conditions

Ambient temperature range	-10...40 °C
----------------------------------	-------------

Lifespan

Lifespan L70 at 25 °C	50000 h
Lifespan L80 at 25 °C	45000 h
Lifespan L90 at 25 °C	30000 h

Additional product data

Mounting type	Recessed
Mounting location	Ceiling



Capabilities

Adjustable	Yes
Dimmable	No
Type of connection	Screw terminal, 2-Pole (L,N)
LED module replaceable	Not replaceable

Certificates & standards

Protection class IK (shock resistance)	IK03
Glow Wire Test according to IEC 695-2-1	650 °C
Photobiological safety group EN62778	RG 1
Protection class	II
Type of protection	IP20
Standards	CE/CB/ENEC/TÜV SÜD/RoHS

Light Distribution



LDC typ cone

LDC typ polar

EQUIPMENT / ACCESSORIES

- Driver included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075113985	Folding carton box 1	210 mm x 355 mm x 175 mm	2810.00 g	13.05 dm ³
4058075113992	Shipping carton box 4	720 mm x 220 mm x 365 mm	11996.00 g	57.82 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see
 ▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.