


**ENERGIZER MAX**



**Industry Standard Dimensions**




**Specifications**





<b>Classification:</b>	Alkaline
<b>Chemical System:</b>	Zinc-Manganese Dioxide (Zn/MnO <sub>2</sub> ) No added mercury or cadmium
<b>Designation:</b>	ANSI-14A, IEC-LR14
<b>Nominal Voltage:</b>	1.5 volts
<b>Nominal IR:</b>	150 to 300 milliohms (fresh)
<b>Operating Temp:</b>	-18°C to 55°C (0°F to 130°F)
<b>Typical Weight:</b>	66.2 grams (2.3 oz.)
<b>Typical Volume:</b>	26.9 cubic centimeters (1.6 cubic inch)
<b>Jacket:</b>	Plastic Label
<b>Shelf Life:</b>	10 years at 21°C
<b>Terminal:</b>	Flat Contact

**Milliamp-Hours Capacity**


Continuous discharge to 0.8 volts at 21°C



**Device Selection Guide:**

- Portable Stereo 
- Toy 
- Lighting 
- Radio 

**Battery Selection Indicator**




**Important Notice**

This data sheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.


**ENERGIZER E93**



**Constant Resistance Performance**  
Typical Characteristics (21°C)




**Constant Current Performance**  
Typical Characteristics (21°C)




**Industry Standard Tests (21°C)**


**RADIO**  
20 ohm 4 hrs/day




**LIGHTING**  
3.9 ohm LIF



**TOY**  
3.9 ohm 1 hr/day



**PORTABLE STEREO**  
400 mA 2 hrs/day



**Important Notice**

This data sheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.