



AC-DC POWER SUPPLIES

3W

The MCE03 series of PCB mount single output AC-DC medical power supplies delivers a power output of 3W and offers single output voltages ranging from 3.3V to 48VDC. The MCE03 series, which is available in open-frame and encapsulated mechanical formats, is specifically designed for medical applications with 2 x MOPP isolation and is approved for Class II applications.

With world-wide medical safety approvals, class B compliance for conducted and radiated emissions, high efficiency, high reliability, 4kVAC isolation, the MCE series benefits system designers with easy integration into a wide range of BF rated medical applications including imaging, patient treatment, surgical equipment and home healthcare applications.

Features

- Single outputs 3.3V to 48VDC
- Input range 80 to 264VAC
- Available in open frame and encapsulated formats
- High efficiency, up to 81%
- 4kVAC input to output isolation
- Class B conducted and radiated emissions
- IEC 60601-1 medical safety agency approvals, 2 x MOPP
- IEC class II insulation rating
- -25°C to +70°C operating temperature
- Overvoltage, overload and short circuit protection

Applications







Healthcare

Home Healthcare

Medical Diagnostic

Dimensions

MCE03:

1.60 x 0.75 x 0.75" (40.6 x 19.1 x 19.1mm)

MCE03-P:

1.50 x 0.65 x 0.65" (38.1 x 16.5 x 16.5mm)

Models & Ratings

| Model Number ⁽¹⁾ | Output Voltage | Output Current | Efficiency ⁽²⁾ | Output Power |
|-----------------------------|----------------|----------------|---------------------------|--------------|
| MCE03US03 | 3.3VDC | 910mA | 75% | 3W |
| MCE03US05 | 5.0VDC | 600mA | 79% | 3W |
| MCE03US09 | 9.0VDC | 333mA | 79% | 3W |
| MCE03US12 | 12.0VDC | 250mA | 80% | 3W |
| MCE03US15 | 15.0VDC | 200mA | 80% | 3W |
| MCE03US24 | 24.0VDC | 125mA | 81% | 3W |
| MCE03US48 | 48.0VDC | 63mA | 80% | 3W |

Notes:

- 1. For Open Frame version add suffix -P to model number, e.g. MCE03US12-P.
- 2. Typical efficiency at 115VAC and full load.

○ MCE03 Series

Summary

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions | | |
|-----------------------|----------------------------------|---|---------|-------|---|--|--|
| Input Voltage Range | 80 | | 264 | VAC | Derate from 100% at 90 VAC to 90% at 80 VAC | | |
| No Load Input Power | | | 0.3 | W | | | |
| Efficiency | | 80 | | % | Model dependent, see Models & Ratings | | |
| Operating Temperature | -25 | | +70 | °C | Derate output linearly from 100% at 50°C to 50% at 70°C | | |
| EMC | EN55011 Lev | EN55011 Level B Conducted & Radiated, EN61000-3-2, EN61000-3-3, EN60601-1-2 | | | | | |
| Safety Approvals | IEC60601-1, EN60601-1, ES60601-1 | | | | | | |

Input

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|---------------------------|---------------|---|---------|-------|---|
| Input Voltage Range | 80 | | 264 | VAC | Derate from 100% at 90VAC to 90% at 80VAC |
| Input Frequency | 47 | | 63 | Hz | |
| Input Current - Full Load | | 0.06/0.04 | | A rms | At 115/230VAC |
| No Load Input Power | | | 0.3 | W | |
| Inrush Current | | | 40 | Α | At 230VAC, cold start 25°C |
| Earth Leakage Current | | | | | Class II construction no earth |
| Input Protection | External T1.0 | External T1.0 A/300 VAC fuse required in line and neutral | | | |

Output

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|--------------------------|---------|---------|---------|----------|--|
| Output Voltage | 3.3 | | 48 | VDC | |
| Initial Set Accuracy | | | 3/2 | % | 3% for 3V3 & 5V models, 2% for others at 50% load |
| Minimum Load | 0 | | | А | No minimum load required |
| Line Regulation | | | 1 | % | |
| Load Regulation | | | 6/4 | %0 | 6% for 3V3 & 5V models, 4% for other models |
| Start Up Delay | | | 2 | s | |
| Start Up Rise Time | | | 35 | ms | |
| Hold Up Time | 8 | 14 | | ms | At full load and 115VAC |
| Transient Response | | | 4 | % | Deviation, recovery within 1% in less than 500µs for a 25% load change |
| | | | 100 | mV pk-pk | 3.3-9V models, 20MHz bandwidth |
| Ripple & Noise | | | 1 | % pk-pk | 12V to 15V models, 20MHz bandwidth |
| | | | 1.5 | % pk-pk | 24V to 48V models, 20MHz bandwidth |
| Patient Leakage Current | | | 65 | μΑ | At 264VAC, 60Hz |
| Overvoltage Protection | 115 | | 145 | % Vnom | 220% typical for 3V3 model, auto recovery |
| Overload Protection | 110 | | 190 | % | |
| Short Circuit Protection | | | | | Trip & Restart (hiccup mode) |
| Temperature Coefficient | | | 0.05 | %/°C | |

─ MCE03 Series

General


| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|----------------------------|---------|------------|---------|--------|--|
| Efficiency | | 80 | | % | Model dependent |
| Isolation: Input to Output | 4000 | | | VAC | 2 x MOPP, suitable for BF applications |
| Switching Frequency | 17 | | 75 | kHz | Varies with load |
| Power Density | | | 4.7 | W/in³ | For '-P' version |
| Mean Time Between Failure | 550 | 600 | | khrs | MIL-HDBK-217F, +25°C GB |
| Weight | | 0.025 (10) | | lb (a) | Open frame versions (-P) |
| | | 0.067 (30) | | lb (g) | Encapsulated version |

Environmental


| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions | |
|-----------------------|--|---------|---------|-------|---|--|
| Operating Temperature | -25 | | +70 | °C | Derate output linearly from 100% at 50°C to 50% at 70°C | |
| Storage Temperature | -40 | | +85 | °C | | |
| Cooling | Convection-cooled | | | | | |
| Humidity | | | 95 | %RH | Non-condensing | |
| Operating Altitude | | | 5000 | m | | |
| Shock | IEC68-2-27, 30g, 11ms half sine, 3 times in each of 6 axes | | | | | |
| Vibration | IEC68-2-6, 2g, 10Hz to 500kHz, 10 mins/cycle, 60 mins each cycle | | | | | |

Efficiency Graphs

MCE03US12-P



MCE03US24-P



EMC: Emissions

| Phenomenon | Standard | Test Level | Notes & Conditions |
|------------------|-------------|------------|---|
| Conducted | EN55011 | Class B | If output is connected to ground, additional external components will |
| Radiated | EN55011 | Class B | be required. See application notes |
| Harmonic Current | EN61000-3-2 | Class A | |
| Voltage Flicker | EN61000-3-3 | | |

─ MCE03 Series

EMC: Immunity

| Phenomenon | Standard | Test Level | Criteria | Notes & Conditions |
|------------------------|--------------------------|--|----------|--------------------|
| Medical | EN60601-1-2 | As below | As below | |
| ESD Immunity | EN61000-4-2 | ±8kV contact, ±15kV air discharge | А | |
| Radiated Immunity | EN61000-4-3 | 10 V/m | Α | |
| EFT/Burst | EN61000-4-4 | 3 | Α | |
| Surge | EN61000-4-5 | 2 | Α | Line to line |
| Conducted | EN61000-4-6 | 10Vrms | Α | |
| Magnetic Fields | EN61000-4-8 | 30A/m | Α | |
| | EN61000-4-11 | 70% U _T (80.5VAC) for 100ms | Α | |
| | | 40% U _T (46VAC) for 200ms | В | |
| | (115VAC) | <5% U _T (0VAC) for 10ms | Α | |
| Discount Intermedian | | <5% U _T (0VAC) for 5000ms | В | |
| Dips and Interruptions | EN61000-4-11 (230VAC) | 70% U _T (161VAC) for 100 ms | А | |
| | | 40% U _T (92VAC) for 200ms | Α | |
| | | <5% U _T (0VAC) for 10ms | Α | |
| | | <5% U _T (0VAC) for 5000ms | В | |


Safety Approvals

| Certification | Standard | Notes & Conditions | | | |
|---------------|-----------------------------------|--------------------|--|--|--|
| СВ | IEC60601-1 | Medical, 2 x MOPP | | | |
| UL | ES60601-1/CSA-C22.2 No.60601-1:14 | Medical, 2 x MOPP | | | |
| TUV | EN60601-1 | Medical, 2 x MOPP | | | |
| CE | Meets all applicable directives | | | | |
| UKCA | Meets all applicable legislation | | | | |

Application Notes

EMC with output grounded

EMC with output grounded. This product is designed for class II operation, but if there is a requirement to connect the output to ground then additional components as shown below can be added to improve emissions.




Suggested value - C: X2 cap, 0.22 μ F/275V, 10% MKP HJC.


- L: CMCK DIP UU-9.8 Φ0.27*95T 17.6mH (min)

─ MCE03 Series

Mechanical Details


Encapsulated







| Pin Connections | | | | |
|-----------------|--------|--|--|--|
| Pin | Single | | | |
| 1 | ACL | | | |
| 2 | ACN | | | |
| 3 | +Vout | | | |
| 1 | Vout | | | |

Open Frame (-P)







Notes:

- 1. Dimensions in inches (mm).
- 2. Weight: Open frame versions (-P): 0.025lbs (10g) Encapsulated: 0.067lbs (30g)
- 3. Tolerances: x.xx = \pm 0.02 (x.x = \pm 0.5) x.xxx = \pm 0.01 (x.xx = \pm 0.25)