



20W

The MCE20 series of PCB mount single output AC-DC medical power supplies delivers a power output of 20W and offers single output voltages ranging from 3.3V to 48VDC. The MCE20 series, which is available in open-frame and encapsulated mechanical formats, is specifically designed for medical applications with 2 x MOPP isolation and is approved for Class II applications.

With world-wide medical safety approvals, class B compliance for conducted and radiated emissions, high efficiency, high reliability, 4kVAC isolation, the MCE series benefits system designers with easy integration into a wide range of BF rated medical applications including imaging, patient treatment, surgical equipment and home healthcare applications.

Features

- Single outputs 3.3V to 48VDC
- Input range 80 to 264VAC
- Available in open frame and encapsulated formats
- High efficiency, up to 85%
- 4kVAC input to output isolation
- Class B conducted and radiated emissions
- IEC 60601-1 medical safety agency approvals, 2 x MOPP
- IEC class II insulation rating
- -25°C to +70°C operating temperature
- Overvoltage, overload and short circuit protection

AC-DC POWER SUPPLIES



Applications







Healthcare

Home Healthcare

Medical Diagnostic

Dimensions

MCE20:

2.60 x 1.30 x 0.92" (66.0 x 33.0 x 23.4mm)

MCE20-P:

2.50 x 1.20 x 0.90" (63.5 x 30.5 x 22.9mm)

Models & Ratings

Model Number ⁽¹⁾	Output Voltage	Output Current	Efficiency ⁽²⁾	Output Power
MCE20US03	3.3VDC	4.55A	78%	15W
MCE20US05	5.0VDC	4.00A	83%	20W
MCE20US09	9.0VDC	2.22A	84%	20W
MCE20US12	12.0VDC	1.67A	85%	20W
MCE20US15	15.0VDC	1.32A	85%	20W
MCE20US24	24.0VDC	0.83A	85%	20W
MCE20US48	48.0VDC	0.42A	85%	20W

Notes:

- 1. For Open Frame version add suffix -P to model number, e.g. MCE20US12-P.
- 2. Typical efficiency at 230VAC and full load.

○ MCE20 Series

Summary

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions				
Input Voltage Range	80		264	VAC	Derate from 100% at 90 VAC to 90% at 80 VAC				
No Load Input Power			0.3	W					
Efficiency		85		%	Model dependent, see Models & Ratings				
Operating Temperature	O.F.	25	+70	°C	3V3 & 5V models	Derate output linearly from 100% at +45°C to 45% at +70°C			
	-25				Other models	Derate output linearly from 100% at 50°C to 50% at 70°C			
EMC	EN55011 Lev	EN55011 Level B Conducted & Radiated, EN61000-3-2, EN61000-3-3, EN60601-1-2							
Safety Approvals	IEC60601-1,	IEC60601-1, EN60601-1, ES60601-1							

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Input Voltage Range	80		264	VAC	Derate from 100% at 90VAC to 90% at 80VAC	
Input Frequency	47		63	Hz		
Input Current - Full Load		0.35/0.22		A rms	At 115/230VAC	
No Load Input Power			0.3	W		
Inrush Current			40	А	At 230VAC, cold start 25°C	
Earth Leakage Current					Class II construction no earth	
Input Protection	Internal T1.0	Internal T1.0 A/300 VAC fuse fitted in line and neutral				

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	3.3		48	VDC	
Initial Set Accuracy			1.5/1.0	%	1.5% for 3V3 & 5V models, 1% for others at 50% load
Minimum Load	0			А	No minimum load required
Line Regulation			1	%	
Load Regulation			2	%0	
Start Up Delay			2	s	
Start Up Rise Time			35	ms	
Hold Up Time	8	14		ms	At full load and 115VAC
Transient Response			4	%	Deviation, recovery within 1% in less than 500µs for a 25% load change
			100		3V3, 5V & 9V models, 20MHz bandwidth
Ripple & Noise			200	mV pk-pk	12V & 15V models, 20MHz bandwidth
			1	% pk-pk	24V & 48V models, 20MHz bandwidth
Patient Leakage Current			65	μA	At 264VAC, 60Hz
Overvoltage Protection	115		145	% Vnom	220% typical for 3V3 model, auto recovery
Overload Protection	110		190	%	
Short Circuit Protection					Trip & Restart (hiccup mode)
Temperature Coefficient			0.05	%/°C	

─ MCE20 Series

General


Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Efficiency		85		%	Model dependent	
Isolation: Input to Output	4000			VAC	2 x MOPP, suitable for BF applications	
Switching Frequency	17		80	kHz	Varies with load	
Power Density			7.4	W/in³	For '-P' version	
Mean Time Between Failure	550	600		khrs	MIL-HDBK-217F, +25°C GB	
Weight		0.09 (40)		lb (a)	Open frame versions (-P)	
		0.20 (90)		lb (g)	Encapsulated version	

Environmental


Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Operating Temperature	-25		70	°C	3V3 & 5V models	Derate output linearly from 100% at +45°C to 45% at +70°C
		+70	C	Other models	Derate output linearly from 100% at 50°C to 50% at 70°C	
Storage Temperature	-40		+85	°C		
Cooling	Convection-	cooled				
Humidity			95	%RH	Non-condensing	
Operating Altitude			5000	m		
Shock	IEC68-2-27,	30g, 11ms half	sine, 3 times in e	each of 6 axes		
Vibration	IEC68-2-6, 2	2g, 10Hz to 500	kHz, 10 mins/cyc	cle, 60 mins ea	ach cycle	

Efficiency Graphs

MCE20US12-P



MCE20US24-P



EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55011	Class B	If output is connected to ground, additional external components will
Radiated	EN55011	Class B	be required. See application notes
Harmonic Current	EN61000-3-2	Class A	
Voltage Flicker	EN61000-3-3		

EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Medical	EN60601-1-2	As below	As below	
ESD Immunity	EN61000-4-2	±8kV contact, ±15kV air discharge	А	
Radiated Immunity	EN61000-4-3	10 V/m	Α	
EFT/Burst	EN61000-4-4	3	Α	
Surge	EN61000-4-5	2	Α	Line to line
Conducted	EN61000-4-6	10Vrms	А	
Magnetic Fields	EN61000-4-8	30A/m	А	
	EN61000-4-11 (115VAC)	70% U _T (80.5VAC) for 100ms	А	
		40% U _T (46VAC) for 200ms	В	
		<5% U _T (0VAC) for 10ms	А	
Discount later weeting		<5% U _T (0VAC) for 5000ms	В	
Dips and Interruptions		70% U _T (161VAC) for 100 ms	А	
	EN61000-4-11	40% U _T (92VAC) for 200ms	Α	
	(230VAC)	<5% U _T (0VAC) for 10ms	Α	
		<5% U _T (0VAC) for 5000ms	В	


Safety Approvals

Certification	Standard	Notes & Conditions			
СВ	IEC60601-1	Medical, 2 x MOPP			
UL	ES60601-1/CSA-C22.2 No.60601-1:14	Medical, 2 x MOPP			
TUV	EN60601-1	Medical, 2 x MOPP			
CE	Meets all applicable directives				
UKCA	Meets all applicable legislation				

Application Notes

EMC with output grounded

EMC with output grounded. This product is designed for class II operation, but if there is a requirement to connect the output to ground then additional components as shown below can be added to improve emissions.




Suggested value - C: X2 cap, 0.22 μ F/275V, 10% MKP HJC.


- L: CMCK DIP UU-9.8 Φ0.27*95T 17.6mH (min)

─ MCE20 Series


Mechanical Details

Encapsulated





Open Frame (-P)



		0.11[2.8] max	0.17[4.4]	0.73[18.5]	0.90[22.9]
0.15[3.8]				, ,	
Ŧ	$ \begin{array}{c} 4-\phi 0.039[1.00] \\ 4-\phi 0.071[1.80] \\ 2.300[58.42] \end{array} $	- -			

Pin Connections Pin Single 1 ACN 2 ACL 3 -Vout 4 +Vout

Notes:

- 1. Dimensions in inches (mm).
- 2. Weight: Open frame versions (-P): 0.09lbs (40g) Encapsulated: 0.2lbs (90g)
- 3. Tolerances: $x.xx = \pm 0.02$ ($x.x = \pm 0.5$) $x.xxx = \pm 0.01$ ($x.xx = \pm 0.25$)