

Product datasheet

Specifications



PM5110 Meter, modbus, up to 15th H, 1DO 33 alarms

TSI code: 398144322 METSEPM5110

Main

Range	PowerLogic
Product name	PowerLogic PM5000
Device short name	PM5110
Product or component type	Power meter

Complementary

Power quality analysis	up to the 15th harmonic
Device application	Power monitoring
Type of measurement	Current Voltage Frequency Power factor Energy Active and reactive power
Supply voltage	100...415 V AC 45...65 Hz 125...250 V DC
Network frequency	50 Hz 60 Hz
[In] rated current	1 A 5 A
Type of network	1P + N 3P + N 3P
Maximum power consumption in VA	10 VA at 415 V
Ride-through time	80 ms 120 V AC typical 100 ms 230 V AC typical 100 ms 415 V AC typical
Display type	Backlit LCD
Display resolution	128 x 128 pixels
Sampling rate	64 samples/cycle
Measurement current	10...9000 mA
Analogue input type	Voltage (impedance 5 MOhm) Current (impedance 0.3 mOhm)
Measurement voltage	35...690 V AC 45...65 Hz between phases 20...400 V AC 45...65 Hz between phase and neutral
Frequency measurement range	45...65 Hz

Number of inputs	0
Measurement accuracy	Active energy +/- 0.5 % Reactive energy +/- 2 % Active power +/- 0.5 % Apparent power +/- 0.5 % Frequency +/- 0.05 % Power factor +/- 0.005 Current +/- 0.5 % Voltage +/- 0.5 %
Accuracy class	Class 0.5S active energy conforming to IEC 62053-22
Number of outputs	1 digital
Communication port protocol	Modbus RTU and ASCII at 9.6, 19.2 and 38.4 kbauds even/odd or none - 2 wires, insulation 2500 V JBUS
Communication port support	RS485
Data recording	Time stamping Min/max of instantaneous values
Connections - terminals	Voltage circuit: screw terminal block4 Control circuit: screw terminal block2 Current transformer: screw terminal block6 Input/output circuit: screw terminal block6 RS485 link: screw terminal block4
Mounting mode	Flush-mounted
Mounting support	Framework
Standards	UL 61010-1 EN 50470-3 EN 50470-1 IEC 62053-22 IEC 60529 IEC 62053-24 IEC 61557-12
Product certifications	CE conforming to IEC 61010-1 CULus conforming to UL 61010-1
Width	96 mm
Depth	72 mm
Height	96 mm
Net weight	380 g

Environment

Electromagnetic compatibility	Limits for harmonic current emissions class A conforming to IEC 61000-3-2 Electrostatic discharge level 4 conforming to IEC 61000-4-2 Conducted RF disturbances level 3 conforming to IEC 61000-4-6 Magnetic field at power frequency level 4 conforming to IEC 61000-4-8 Conducted and radiated emissions class B conforming to EN 55022
IP degree of protection	IP52 front: conforming to IEC 60529 IP30 body: conforming to IEC 60529
Relative humidity	5...95 % at 50 °C
Pollution degree	2
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	2000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	449 g
Package 1 Height	11.467 cm

Package 1 width	12.979 cm
Package 1 Length	12.544 cm
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	7.19 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P12
Number of Units in Package 3	288
Package 3 Weight	206.4 kg
Package 3 Height	105 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------