Multifunctional clock-pulse generator relay MFT ST22S



MFT ST22S

- 5 Function, 8 timer ranges
- Multivoltage: 12 ... 240 Vac/dc
- 2 Output contacts

Functions

- **TP** Cycling timer relay beginning on a pause
- **TI** Cycling timer relay beginning on a pulse
- **EA** Delay on and delay off
- **EI1** Input delay pulse limitation timer voltage control
- **EI3** Input delay pulse limitation with control contact
- **EI2** Input delay pulse with control contact
- I3 Pulse detection

Time end ranges

Adjustable 0,05 s ... 100 h

Output relay

2 potential free change over contact 250 Vac 8 A

Indicators

Green LED ON:indication of supply voltageGreen LED flashes slowly:indication of time t1Green LED flashes fast:indication of time t2Yellow LED ON/OFF:indication of relay output

Connecting voltage

12 ... 240 Vac/dc -10% +10% 48 ... 63 Hz, 100% duration of operation, IEC class 1c

Reference data

Selectron [®] MFT	Article no.
MFT ST22S	41140006
(Order data see chapter 1)	

Multifunctional clock-pulse generator relay

MFT ST22S

Technical data		
Nominal consumpti	on	
	12 240 Vac/dc	6 VA / 2 W
Control contact / Vo	oltage controlled	
	Parallel switching of loads possible	
	Parallel minimum load	1 VA or 0,5 W
	Voltage dependence:	The potential between connections 2 and 5
		must cover 90% of the supply voltage.
	Connecting length between connections 2 and 5:	10 m or capacity <10 nF
	Resistance	>1 M Ω (contact K2 open)
	Rest current at parallel load:	approx. 2 mA at contact K2 open
Accuracy		
	Base accuracy	±1% of scale limits
	Repetition accuracy	±5ms or <0,5%
	Adjustment accuracy	<5% of scale limits
	Temperature influence	≤0,01% / °C
	Voltage influence	-
Reaction times		
	Operating/return time K1	max. 60 ms / 30 ms
	Reaction time K2	max. 30 ms
	Min. pulse/pause time K2	ac 100 ms / dc 50 ms
	Recovery time	max. 100 ms

MFT S T 2 2 S -

Type key

Construction

S Pluggable 11 poles

Functions

- **U** Universal
- **A** Without auxiliary voltage
- **T** Cycling timer
- S Star-delta
- D Digital

Output

- 1 1 changer
- 2 2 changers
- **3** 1 changer / 1 immediate contact
- **4** 1 changer / 1 closing contact
- **5** 1 closing / 1 opening contact

Special functions

E External Potentiometer

Control

- **S** Voltage control
- P Potential free


Connecting range

- 1 24 Vdc/ac and
- 110 ... 240 Vac
- **2** 12 ... 240 Vac/dc
- **3** 24 ... 240 Vac/dc

Function descriptions

TP - Cycling timer relay beginning on a pause

When the supply voltage U (K1 closed) is applied, the set interval t1 begins (green LED U/t flashes slowly). After the



interval t1 has expired, the output relay R switches into onposition (yellow LED illuminated) and the set interval t2 begins (green LED U/t flashes fast). After the interval t2 has expired, the output relay switches into off-position (yellow LED not illuminated).

The output relay is triggered in the ratio of the two set intervals until the supply voltage U (K1 opened) is interrupted.

TI - Cycling timer relay beginning on a pulse

When the supply voltage U (K1 closed) is applied, the output relay R switches into on-position (yellow LED illumi-




nated) and the set interval t1 begins (green LED U/t flashes slowly). After the interval t1 has expired, the output relay switches into off-position (yellow LED not illuminated) and the set interval t2 begins (green LED U/t flashes fast). After the interval t2 has expired, the output relay switches into on-position again (yellow LED illuminated).

The output relay is triggered in the ratio of the two set intervals until the supply U (K1 opened) voltage is interrupted.

EA -Delay on and delay off

The supply voltage U (K1 closed or permanently connected) must be constantly applied to the device (green LED U/t




illuminated). When the control contact K2 is closed, the set interval t1 begins (green LED U/t flashes slowly). After the interval t1 has expired, the output relay R switches into onposition (yellow LED illuminated). When the control contact K2 is opened, the set interval t2 begins (green LED U/t flashes fast). After the interval t2 has expired, the output relay switches into off-position (yellow LED not illuminated).

If the control contact K2 is opened before the interval t1 has expired, the interval already expired is erased and is restarted with the next cycle.

EI1 - Input delay pulse limitation timer voltage control


When the supply voltage U (K1 closed) is applied, the set interval t1 begins (green LED U/t flashes slowly). After the interval t1 has expired, the output relay R switches into onposition (yellow LED illuminated) and the set interval t2 begins (green LED U/t flashes fast). After the interval t2 has expired, the output relay switches into off-position (yellow



LED not illuminated). If the supply voltage is interrupted before the interval t1+t2 has expired, the interval already expired is erased and is restarted when the supply voltage is next applied.

EI3 - Input delay pulse limitation timer with control contact


The supply voltage U (K1 closed) must be constantly applied to the device (green LED U/t illuminated). When the control



contact K2 is closed, the set interval t1 begins (green LED U/ t flashes slowly). After the interval t1 has expired, the output relay switches into on-position (yellow LED illuminated) and the set interval t2 begins (green LED U/t flashes fast). After the interval t2 has expired, the output relay switches into offposition (yellow LED not illuminated). During the interval, the control contact K2 can be operated any number of times. A further cycle can only be started when the cycle run has been completed.

EI2 - Input delay pulse with control contact

The supply voltage U (K1 closed or permanently connected) must be constantly applied to the device (green LED U/t




illuminated). After closing of K2, the set interval t1 begins (green LED U/t flashes slowly). After the interval t1 has expired, the output relay R switches into on-position (yelow LED illuminated) and the set interval t2 (green LED U/t flashes fast) begins. After the set interval t2 has expiered the output relay switches into off-position (yellow LED not illuminated). During the intervals t1 or t2, the control contact K2 can be operated any number of times. A further cycle can only be started when the running cycle has been completed.

Multifunctional clock-pulse generator relay MFT ST22S

Function descriptions

I3 - Pulse detection

When the supply voltage U (K1 closed) is applied, the set interval t1 begins (green LED U/t flashes slowly) and the




output relay R switches into on-position (yellow LED illuminated). After the interval t1 has expired, the set interval t2 begins (green LED U/t flashes fast). For the output relay to remain in on-position, the control contact K2 must be closed and reopened within the set interval t2. If this does not occur, the output relay R switches into off-position (yellow LED not illuminated) and all further pulses at the control contact K2 are ignored.To restart the function, the supply voltage must be interrupted and reapplied.

Connection


MFT ST22S





Load limit curve

MFT ST22S



Dimensions

