



# Lexmark MX331adn

Productivity. Reliability. Security.



# Lexmark MX331adn

Light, compact, and fast, the MX331adn multifunction supports output up to 38 pages per minute\*, plus single-side automatic scanning, copying, faxing and touch-screen convenience. Connect via USB or Ethernet and add an optional 550-sheet paper tray or available High Yield Unison™ toner that can print up to 15,000 pages\*\*.

## Compact monochrome versatility

- ▶ Get monochrome output at up to 38 pages per minute\*, with a first page as fast as 6.2 seconds.
- ▶ Capture documents with single-side automatic scanning at up to 46 images per minute.
- ▶ Tackle your workload with the power of a 1-GHz dual-core processor and 512 MB of memory.
- ▶ Compact dimensions of 339 mm high x 411 mm wide x 366 mm deep help it fit almost anywhere.



## Connect and command

- ▶ Connect via Ethernet and USB.
- ▶ Take command of printing, copying, faxing, and automatic two-sided scanning with a 7.2 cm colour touch screen.
- ▶ Built-in cloud connectors help you save scans to and retrieve files from popular cloud services Box, DropBox, Google Drive, and Microsoft OneDrive.

## Sustained output, enduring quality

- ▶ Available High Yield Unison™ toner provides up to 15,000 pages\*\* of output for more printing and less downtime.
- ▶ Optional paper tray increases total input capacity to 900 sheets to support longer print runs and enhanced media flexibility.
- ▶ Steel frame and lifetime imaging components mean long life and minimal maintenance.

## Robust, built-in security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—in the document, on the device, over the network, and everywhere in between.
- ▶ A range of embedded features harden the device against attacks.
- ▶ Standard Confidential Print feature helps ensure output security via simple PIN.

## Save paper, save energy

- ▶ Automatic two-sided printing is standard.
- ▶ Built-in energy-saving modes help support ratings of EPEAT® Silver and ENERGY STAR® certified.
- ▶ The Lexmark Cartridge Collection Programme (LCCP) and Lexmark Equipment Collection Programme (LECP) minimise waste and support recycling (availability varies by country).

\* Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

\*\* Average continuous mono declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19752. Actual yield will vary considerably based upon many factors. See [www.lexmark.com/yields](http://www.lexmark.com/yields) for more information.

# Lexmark MX331adn



1 Multifunction product with  
7.2 cm touch screen  
339 x 411 x 366 mm

2 100-Sheet multipurpose  
feeder  
Dimensions included as part of  
base model

3 250-Sheet tray  
Dimensions included as part of  
base model

4 550-Sheet Tray  
107 x 370 x 378 mm



Standard

Optional

Supports one optional 550-sheet tray.

All measurements are shown as height x width x depth. For more information about supported configurations, refer to the Printer, Option and Stand Compatibility Guide at [http://www.lexmark.com/publications/furniture\\_safety/](http://www.lexmark.com/publications/furniture_safety/)

Product Specifications		Lexmark MX331adn
<b>Printing</b>		
Display	2.8 inch (7.2 cm) LCD touch panel	
Print speed	up to: black: 38 ppm <sup>1</sup> (A4)	
Time to first page	as fast as: black: 6.2 seconds	
Print resolution	black: 2400 IQ (2400 x 600 dpi), 600 x 600 dpi	
Memory	standard: 512 MB / maximum: 512 MB	
Hard Disk	Not available	
Recommended monthly page volume	500 - 5000 pages <sup>2</sup>	
Maximum monthly duty cycle	up to: 50000 pages per month <sup>3</sup>	
<b>Copying</b>		
Copy speed	up to: black: 38 cpm <sup>1</sup> (A4)	
Time to first copy	as fast as: black: 6.2 seconds	
<b>Scanning</b>		
Scanner type / ADF scan	Flatbed scanner with ADF / Simplex	
Duplex scan speed	up to: black: N/A spm (A4) / colour: N/A spm (A4)	
Simplex scan speed	up to: black: 46 / 48 spm (A4) / colour: 20 / 21 spm (A4)	
ADF paper input capacity	up to: 50 pages	
<b>Faxing</b>		
Modem speed	ITU T.30, V.34 Half-Duplex, 33.6 kbps	
<b>Supplies<sup>4</sup></b>		
Cartridge yields	up to: 3000 <sup>5</sup> -page cartridge / up to: 15,000 <sup>5</sup> -page High Yield Cartridge	
Imaging unit yield	up to: 40000 pages, based on average 3 pages per print job and 5% coverage <sup>6</sup>	
Cartridge(s) shipped with product	1500 <sup>5</sup> -page starter Return Program toner cartridge	
<b>Paper Handling</b>		
Standard paper handling	100-Sheet Multipurpose Feeder, Integrated Duplex, 150-sheet output bin, 250-sheet input	
Optional paper handling	550-Sheet Tray	
Paper input capacity	up to: standard: 350 pages / maximum: 900 pages	
Paper output capacity	up to: standard: 150 pages / maximum: 150 pages	
Media types supported	Paper Labels, Card Stock, Plain Paper, Envelopes, Refer to the Paper & Specialty Media Guide	
Media sizes supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, Statement, Executive, Universal, DL Envelope, Folio, 10 Envelope	
<b>General Information<sup>7</sup></b>		
Standard connectivity	USB port (compatible with USB 2.0 specification, type B), Fast Ethernet (RJ-45)	
Noise Level	Operating: 53 dBA (Print) / 54 dBA (Copy) / 55 dBA (Scan)	
Specified operating environment	Humidity: 8 to 80% Relative Humidity / Temperature: 10 to 32°C (50 to 90°F) / Altitude: 0 - 2896 Meters (9,500 Feet)	
Product guarantee	1-Year Return-to-Base Service	
Size / Weight	HxWxD: 339 x 411 x 366 mm / 12.8 kg	
Energy Star Typical Electricity Consumption	TEC: 0.44 kWh per week	

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

<sup>1</sup> Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

<sup>2</sup> "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. <sup>3</sup> "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. <sup>4</sup> Product functions only with replacement cartridges designed for use in a specific geographical region. See [www.lexmark.com/regions](http://www.lexmark.com/regions) for more details. <sup>5</sup> Average standard page yield value declared in accordance with ISO/IEC 19752. <sup>6</sup> Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. <sup>7</sup> Printers are sold subject to certain license/agreement conditions. See [www.lexmark.com/printerlicense](http://www.lexmark.com/printerlicense) for details.

© 2020 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries.

Apple and AirPrint are trademarks of Apple Inc., registered in the U.S. and other countries. Google Cloud Print is a trademark of Google, LLC. MOPRIA®, the Mopria® Logo™ and the Mopria® Alliance logos are registered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorised use is strictly prohibited. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. EPEAT® is a trademark of the Green Electronics Council in the United States and other countries. All other trademarks are the property of their respective owners.

This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).