



## 19590-449 Over Trousers

breathable - wind- and waterproof  
 MASCOT® ACCELERATE SAFE



S	M	L	XL	2XL	3XL	4XL
5XL						


100% polyester  
 210 g/m<sup>2</sup>



Ripstop. Shrinkage max. 2%. The product is according to EN ISO 20471 certified to retain its qualities with 50 domestic washes.

**Industrial care category C2**

### Certifications



### Logo

You should choose a transfer that can be heated at a maximum of 145 degrees with consideration to print on the product. Remember to check the washing instructions for the chosen transfer before washing the product.

The product is certified with maximum 0,5000m<sup>2</sup> logo area. This approved area must not be exceeded. Logo respectively on the front or back of the product, can only constitute a maximum of 50% of the total approved logo area in order to maintain the EN ISO 20471-certification. Note: The listed area is only a guide to how much space is available for logo placement. In order to maintain the product's hi-vis class according to EN ISO 20471, the instructions on logo size must be observed.

### Logo placement:

- Workwear logo stretch. Left back pocket. Max 11X4 cm/4.3x1.5 inches
- Workwear logo stretch. Right back pocket. Max 11X4 cm/4.3x1.5 inches
- Workwear logo stretch. Vertical on left thigh, read from the bottom upwards. Max 20x5 cm/7.8x1.9 inches
- Workwear logo stretch. Vertical on right thigh, read from the top downwards. Max 20x5 cm/7.8x1.9 inches
- Workwear logo stretch. Horizontal on right thigh. Max 9X6 cm/3.5x2.3 inches
- Workwear logo stretch. Horizontal on left thigh. Max 9X6 cm/3.5x2.3 inches



- Breathable, wind and waterproof with taped seams.
- Very durable.
- Ergonomically shaped trouser legs are constructed to follow the body's natural movements.
- Elastic and drawstring waist.
- Zip on outside of legs.
- Co-certified for use with MASCOT kneepad type SHORT or LONG, as the kneepad pocket is height-adjustable.

### Technical info

Fluorescent and with reflective tape. The fabric is highly durable, breathable, wind and waterproof. Taped seams. Zipper openings at the front, on both sides, so holster pockets from the trousers underneath can be pulled through. Ergonomically formed trouser leg. Belt loops. D-ring. Elastic and drawstring at waist. Reinforced ruler pocket with a small pocket on the outside. Adjustable polyester kneepad pockets. Simple individual adjustment of kneepad pocket height. Zip with storm flap on outside of lower legs. Rib inside the bottom by ankles. We recommend 00418-100, 00718-100, 50451-916 and 20118-915 kneepads for this model. Co-certified together with kneepad type SHORT or LONG in accordance with EN 14404.

### User



- Workwear logo. Special placement. Contact to discuss further