




## PANEL MOUNTING

ø6.2

## **CONTACT ARRANGEMENT**

		toggle	toggle
code for x	function	towards keyway	opposite to keyway
D	On-On	1-2	2-3



		toggle	toggle	toggle	
code for x	function	towards keyway	in center	opposite to keyway	
Е	On-Off-On	1-2	open	2-3	

## Specifications:

Contact rating:

3A, 250V AC / 6A, 125V AC 4A, 30V DC / 5A, 12V DC

6A, 6V DC

Contact resistance:

20mOhm max.

Insulation resistance:

1 000MOhm min. at 500V DC

Dielectric strength:

1 500V, 50Hz for the duration of 1 minute

Operating temperature:

-45°C to +140°C min. 200 000 cycles

Soldering conditions:

Mechanical life:

hand-soldering: max.: 420°C, 3sec., 60W

auto-soldering: max.: 270°C, 5sec.

Mounting instruction:

max. torque: 49Ncm

Material:

Terminal: brass, C1020 silver plated

Case: DAP

Housing: stainless steel, CNS9265

Bushing: copper alloy, C3604BD nickel plated Actuator: copper alloy, C3604BD chrome plated

Cap: aluminium

Included accessories:

2 pcs. nut M6x0.75, nickel plated, 9mm wrench size

1 pc. tooth washer 1 pc. locking washer Cap is not included

Compliance: RohS II (2011/65/EU)

Tolerances: 0.00: ±0.25mm			Date	Name				
0.0: ±0.40mm			08/09	dr				
						MTL 10	6 x	
							U A	
Revised	10/17	dr		knitter-switc		1ch 30 19 07		Pogo
Dimension	01/11	dr	kni					Page
Panel mouting	05/10	dr						1/1
Modifications	Date	Name						