



Part Number : [2016066163](#)

Product Description : High Current Universal Clamp Terminal Block, 35.00mm DIN-rail Mount, 150.0A / 600V, Grey Housing and Cover, 3 Circuits

Series Number : 201606

Status : Active

Product Category : Terminal Blocks and Barrier Strip

Engineering Number : MX-KE61-03

---

## Documents & Resources

### Drawings

[Drawing 2016066163\\_sd.pdf](#)


### 3D Models and Design Files

[3D Model 2016066163\\_stp.zip](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	201606
Description	High Current Universal Clamp Terminal Block, 35.00mm DIN-rail Mount, 150.0A / 600V, Grey Housing and Cover, 3 Circuits
Application	Wire-to-Wire
Component Type	One Piece
Product Family	Terminal Blocks & Barrier Strips
Product Name	Universal Clamp
Type	High-Current Universal Clamps
UPC	78172551095

### Electrical

Current - Maximum per Contact	150.0A
Voltage - Maximum	600V

### Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Gray
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Aluminum
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide
Net Weight	77.000/g
Number of Rows	3
Orientation	Vertical
Panel Mount	No
Pitch - Mating Interface	N/A

Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Screw
Wire Size (AWG)	1/0-6, 6+6, 8+8+8
Wire Size mm <sup>2</sup>	13.00+13.00, 13.00-53.00, 8.30+8.30+8.30

---

---

This document was generated on Jul 30, 2024