

Note: This datasheet may be out of date.

Please download the latest datasheet of BNX026H01# from the official website of Murata

Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=BNX026H01%23

"#" indicates a package specification code.










< List of part numbers with package codes > BNX026H01B BNX026H01K BNX026H01L



Appearance & Shape







Packaging Information

Packaging	Specifications	Standard Packing Quantity
В	Bulk(Bag)	100
K	330mm Embossed Tape	1500
L	180mm Embossed Tape	400



Applications

Automotive Usage

Powertrain/Safety

1 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Note: This datasheet may be out of date.

Please download the latest datasheet of BNX026H01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=BNX026H01%23

"#" indicates a package specification code.



Features

BNX024H/025H/026H/027H (Block Type EMIFIL for automotive) is EMI suppression filter supporting large current, wide frequency.

And it also supports SMD mounting. This product is effective for noise suppression for DC switching line of automotive device and FA/OAdevice, because it covers wide temperature range from -55C degrees to 125 C degrees.

Features

- 1. Supporting large current (20A)
- 2. Supporting wide frequency range From 40kHz to 1GHz:35dB min.(BNX027)
- 3. Suitable for miniaturization with SMD shape.

Applications

Automotive devices/Displays (PDP/LCD-TV)/
Digital AV equipments/Amusement equipments/
PC peripheral equipments/Industry equipments/
Measurement equipments/Power supplies

2 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





Note: This datasheet may be out of date.

Please download the latest datasheet of BNX026H01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=BNX026H01%23

"#" indicates a package specification code.



Specifications

Shape	SMD	
Length	12.1mm	
Length Tolerance	±0.2mm	
Width	9.1mm	
Width Tolerance	±0.2mm	
Thickness	3.5mm	
Thickness Tolerance	±0.2mm	
Rated Current	20A	
Operating Temperature Range	-55°C to 125°C	
Mass(typ.)	0.86g	
Rated Voltage	50Vdc	
Withstanding Voltage	125Vdc	
Insulation Resistance(min.)	10ΜΩ	
Insertion Loss	50kHz to 1GHz:35dB min. (Line impedance=50Ω)	

3 of 4

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




Note: This datasheet may be out of date.


Please download the latest datasheet of BNX026H01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=BNX026H01%23

"#" indicates a package specification code.








Insertion Loss Characteristics

In operating temperature exceeding +85°C, derating of current is necessary for BNX024H/025H/026H/027H series. Please apply the derating curve shown in chart according to the operating temperature.

Derating of Rated Current



Equivalent Circuit

Derating of Rated Current

4 of 4

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

