



Part Number : 395443004

Series Number : 39544

Product Category : Terminal Blocks and Barrier Strip

Product Description : 5.08mm Pitch Eurostyle Vertical Fixed Mount PCB Terminal Block, 4 Circuits

Status : Active

Documents & Resources

Drawings
Drawing 395443004_sd.pdf

3D Models and Design Files
3D Model 395443004_stp.zip

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
 - REACH SVHC
 - Low-Halogen

- Multiple Part Industry Compliance Documents
- IPC 1752A Class C
 - IPC 1752A Class D
 - Molex Product Compliance Declaration
 - IEC-62474
 - chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39544
Description	5.08mm Pitch Eurostyle Vertical Fixed Mount PCB Terminal Block, 4 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Family	Terminal Blocks & Barrier Strips
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	822350547017

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Net Weight	5.650/g
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PC Tail Length	3.00mm
PCB Thickness - Recommended	2.00mm

Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	12, 14, 16, 18, 20, 22
Wire Size mm ²	0.33-3.31

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Temp	260