




Model Number

NBB0,6-3M22-E2


Features

- 0.6 mm embeddable
- Miniature design

Connection



Dimensions



Technical Data

General specifications

Switching element function		PNP	NO
Rated operating distance	s_n	0.6 mm	
Installation		embeddable	
Output polarity		DC	
Assured operating distance	s_a	0 ... 0.486 mm	
Reduction factor r_{Al}		0.4	
Reduction factor r_{Cu}		0.29	
Reduction factor r_{304}		0.76	
Reduction factor r_{Brass}		0.46	

Nominal ratings

Operating voltage	U_B	10 ... 30 V
Switching frequency	f	0 ... 1400 Hz
Hysteresis	H	typ. 5%
Reverse polarity protected		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_d	≤ 3 V
Operating current	I_L	0 ... 100 mA
Off-state current	I_r	0 ... 0.1 mA typ. at 25 °C
No-load supply current	I_0	≤ 10 mA
Indication of the switching state		LED, yellow

Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------

Mechanical specifications

Connection type	cable PVC, 2 m
Core cross-section	0.055 mm ²
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	PC
Protection degree	IP67

Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Products with a maximum operating voltage of ≤ 36 V do not bear a CCC marking because they do not require approval.

