NA Series

Ordering Information

NA5-□W

Product name	Specifications	Model
NA5-15W	15.4 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 1280 × 800 dots, Frame color : Silver	NA5-15W101S
NAS-15W	15.4 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 1280 × 800 dots, Frame color : Black	NA5-15W101B
NAC 10W	12.1 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 1280 × 800 dots, Frame color : Silver	NA5-12W101S
NA5-12W	12.1 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 1280 × 800 dots, Frame color : Black	NA5-12W101B
NAE OW	9 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 800 × 480 dots, Frame color : Silver	NA5-9W001S
NA5-9W	9 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 800 × 480 dots, Frame color : Black	NA5-9W001B
NA5-7W	7 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 800 × 480 dots, Frame color : Silver	NA5-7W001S
NA5-7W	7 inch wide screen, TFT LCD, 16,770,000 colors (24 bit full color), 800 × 480 dots, Frame color : Black	NA5-7W001B
High procure		NA-15WATW01
High-pressure Waterproof Attachment for NA5-□W	This metal frame is for high-pressure waterproofing. Install it to conform to UL Type 4X standards.	NA-12WATW01
	UL Type 4X is the rating for high-pressure wash-down applications with a flow rate of 246 liter/min. This attachment can be used for the NA5-□W. but not for the NA5-□U.	NA-9WATW01
	, , , , , , , , , , , , , , , , , , , ,	NA-7WATW01

Note: The NA5- U is also available. Contact your OMRON representative for details.

Options

Product name	Specifications	Model
CD mamaru aard	2 GB	HMC-SD291
SD memory card	4 GB	HMC-SD491
UCD Mamany	2 GB	FZ-MEM2G
USB Memory	8 GB	FZ-MEM8G
Replacement Battery	Battery life: 5 years (at 25°C). This Battery is provided as an accessory.	CJ1W-BAT01
Anti-reflection Sheets	For the NA5-15W. Attach a Sheet to the screen to protect against diffused reflections and dirt. The entire Sheet is colorless and transparent. Five Sheets are provided in one set.	NA-15WKBA04
	For the NA5-12W. Attach a Sheet to the screen to protect against diffused reflections and dirt. The entire Sheet is colorless and transparent. Five Sheets are provided in one set.	NA-12WKBA04
	For the NA5-9W. Attach a Sheet to the screen to protect against diffused reflections and dirt. The entire Sheet is colorless and transparent. Five Sheets are provided in one set.	NA-9WKBA04
	For the NA5-7W. Attach a Sheet to the screen to protect against diffused reflections and dirt. The entire Sheet is colorless and transparent. Five Sheets are provided in one set.	NA-7WKBA04

Automation Software

Product name	Specifications	Number of licenses	Media	Model		
	The Sysmac Studio is the software that provides an integrated environment for	- (Media only)	DVD	SYSMAC-SE200D		
Sysmac Studio	setting, programming, debugging and maintenance of machine automation controllers including the NJ/NX Series, EtherCAT Slave, and the HMI. Sysmac Studio runs on the following OS. Windows XP (Service Pack 3 or higher, 32-bit version) / Windows Vista (32-bit version) / Windows 8 (32-bit/64-bit version) / Windows 8 (32-bit/64-bit version)	setting, programming, debugging and maintenance of machine automation controllers including the NJ/NX Series, EtherCAT Slave, and the HMI. 3 lick Sysmac Studio runs on the following OS. Windows XP (Service Pack 3 or higher, 32-bit version) / Windows Vista (32-bit version) / Windows 7 (32-bit/64-bit version) / Windows 8 (32-bit/64-bit version)	1 license		SYSMAC-SE201L	
				3 licenses	İ	SYSMAC-SE203L
Ver.1.□□			10 licenses	-	SYSMAC-SE210L	
					30 licenses	
		50 licenses		SYSMAC-SE250L		

Note: Site licenses are available for users who will run Sysmac Studio on multiple computers. Ask your OMRON sales representative for details.

USB Cable

Product name	Specifications			
USB Cable	Use commercially available USB cable. Specifications: USB 2.0 cable (A connector - B connector), 5.0 m max.			

Ordering Information

Recommended Network Devices

Industrial Switching Hubs

	Specifications					
Product name	Functions	No. of ports	Failure detection	Accessories	Current consumption (A)	Model
Industrial Switching Hubs	Quality of Service (QoS): EtherNet/IP control data priority	3	No	Power supply connector	0.22	W4S1-03B
	Failure detection: Broadcast storm and LSI error	5	No	Power supply connector Connector for informing	0.22	W4S1-05B
	detection 10/100BASE-TX, Auto-Negotiation	5	Yes	Connector for informing error	0.22	W4S1-05C

Recommended Ethernet Communications Cables

Use STP (shielded twisted-pair) cable of category 6A or higher

Appearance	Туре	Cable Sheath Material	Part Number	Length in inch (cm)	xx = Length	y = Color
				7.87 (20)	20	
				11.8 (30)	30	
				19.6 (50)	50	
	Category 6A Cable with Connectors on Both Ends (RJ45/RJ45)	LOW Smoke Zero Halogen (LSZH)	ASOVI-OLSZNOSSKICIVI-V	39.4 (100)	100	B = Blue
				59.0 (150)	150	
				78.7 (200)	200	
				118 (300)	300	Y = Yellow G = Green
				196 (500)	500	G = Green
				295 (750)	750	
				393 (1000)	1000	†
				590 (1500)	1500	
				787 (2000)	2000	

Example: XS6W-6LSZH8SS100CMB = CAT6A cable with RJ45 connectors at both ends 39.4 inch (100 cm) long, Blue

NA Series

Performance Specifications

 $NA5-\square W \ and \ NA5-\square U \ have \ the \ same \ specifications \ and \ performance \ characteristics \ of \ hardware \ and \ software.$

Display

		Specification					
Item		NA5-15W	NA5-12W	NA5-9W	NA5-7W		
	Display device	TFT LCD	<u>.</u>	<u> </u>			
	Screen size	15.4 inches	12.1 inches	9.0 inches	7.0 inches		
	Resolution	1,280 × 800 dots (horizontal × vertical) 800 × 480 dots (horizontal × ver			al × vertical)		
Display panel *1	Colors	16,770,000 colors (24 bit full colors)					
	Effective display area	331 × 207 mm (horizontal × vertical)	261 × 163 mm (horizontal × vertical)	197 × 118 mm (horizontal × vertical)	152 × 91 mm (horizontal × vertical)		
	View angles	Left: 60°, Right: 60°, Top: 60°, Bottom: 60°					
Pooldiabt #0	Life	50,000 hours min. * 3					
Backlight #2	Brightness adjustment	200 levels	200 levels				
Front panel indicators #4	RUN	Lit green: Normal operati	it green: Normal operation Lit red: Error				

*1. There may be some defective pixels in the display. This is not a fault as long as the numbers of defective light and dark pixels fall within the following standard ranges.

Model	Standard range
NA5-15W	Number of light and dark pixels: 10 or less. (There must not be 3 consecutive light/dark pixels.)

- *2. The backlight can be replaced at an OMRON maintenance base.
 *3. This is the estimated time before brightness is reduced by half at room temperature and humidity. The life expectancy is drastically shortened if Programmable Terminal is used at high temperatures.
- *4. The brightness of the front panel indicators is also adjustable when you adjust the brightness of the backlight.

Operation

Item	Specification				
item	NA5-15W	NA5-12W	NA5-9W	NA5-7W	
	Method: Analog resistance membrane (pressure sensitive)				
Touch panel	Resolution: 16,384 × 16,384				
	Life: 1,000,000 operations				
Function keys *	3 inputs (capacitance inputs)				

^{*} Each function key has blue indicator. The brightness of the function key indicators is also adjustable when you adjust the brightness of the backlight.

Data Capacity

ltom	Specification			
Item	NA5-15W	NA5-12W	NA5-9W	NA5-7W
User data capacity	256 MB			

External Interfaces


It	em	Specifications (Same for all models.)
	Applications	Port 1: Connecting to anything other than the Sysmac Studio, e.g., device connections and VNC clients Port 2: Connecting to the Sysmac Studio in addition to the applications of port 1.
	Number of ports	2 ports
Ethernet ports	Compliant standards	IEEE 802.3i (10BASE-T), IEEE 802.3u (100BASE-TX), and IEEE 802.3ab (1000Base-T)
	Transmission media	Shielded twisted-pair (STP) cable: Category 5, 5e, or higher
	Transmission distance	100 m
	Connector	RJ-45 8P8C modular connector
	Applications	USB Memory Device, keyboard, or mouse
	Number of ports	2 ports
USB host ports	Compliant standards	USB 2.0
	Transmission distance	5 m max.
	Connector	Type-A connector
	Applications	Sysmac Studio connection
	Number of ports	1 port
USB slave port	Compliant standards	USB 2.0
	Transmission distance	5 m max.
	Connector	Type-B connector
	Applications	Device Connection
	Number of ports	1 port
Serial port *	Compliant standards	RS-232C
	Transmission distance	15 m max.
	Connector	D-DUB 9-pin female connector
	Applications	To transfer or store the project or to store log data.
SD Memory Card slot	Number of slots	1 slot
	Compliant standards	SD/SDHC
Expansion Unit Applications Expansion Unit		Expansion Unit
connector *	Quantity	1

^{*}The serial port and Expansion Unit connector are for future expansion.


General Specifications

и	Specification							
Item	NA5-15W□□□□	NA5-12W□□□□	NA5-9W□□□□	NA5-7W□□□□				
Rated supply voltage	24 VDC							
Allowable power supply voltage range	19.2 to 28.8 VDC (24 VDC ±20%)							
Allowable momentary power interruption time	Operation for momentary power interruption is not specified.							
Power consumption	47 W max.	45 W max.	40 W max.	35 W max.				
Ambient operating temperature	32 to 122°F (0 to 50°C) *1 *2	•	•	•				
Ambient storage temperature	-4 to 140°F (-20 to 60°C) *3							
Ambient operating humidity	10 to 90% * 2 Must be no condensation.							
Atmosphere	Must be free from corrosive gas	ses.						
Pollution degree	2 or less: JIS B 3502, IEC 6113	2 or less: JIS B 3502, IEC 61131-2						
Noise immunity	2 kV on power supply line (Conforms to IEC 61000-4-4.)							
Vibration resistance (during operation)		Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5 mm half amplitude and 8.4 to 150 Hz with 9.8 m/s² for 100 minutes each in X,Y, and Z directions (Time coefficient of 10 minutes × coefficient factor of 10 = total time of 100 min.)						
Shock resistance (during operation)	Conforms to IEC 60028-2-27. 147 m/s² 3 times each in X, Y,	and Z directions						
Dimensions W x H x D in (mm)	16.5 x 11.5 x 2.7 (420 x 291 x 69)	13.4 X 9.6 X 2.7 (340 X 244 X 69)	11.4 X 7.5 X 2.7 (290 X 190 X 69)	9.3 X 6.9 X 2.7 (236 X 165 X 69)				
Panel cutout dimensions (horizontal X vertical)	15.4 x 10.5 in +0.04 (392 x 268 mm +1) Panel thickness: .062 to .24 in (1.6 to 6.0 mm)	12.2 x 8.7 in +0.04 (310 x 221 mm +1) Panel thickness: .062 to .24 in (1.6 to 6.0 mm)	10.3 x 6.5 in +4 (261 x 166 mm +1) Panel thickness: .062 to .24 in (1.6 to 6.0 mm)	7.6 x 5.6 in +0.02 (197 x 141 mm +0.5) Panel thickness: .062 to .24 in (1.6 to 6.0 mm)				
Weight	7.0 lb (3.2 kg) max.	5.0 lb (2.3 kg) max.	3.7 lb (1.7 kg) max.	2.9 lb (1.3 kg) max.				
Degree of protection	Front-panel controls: IP65 oil-p	roof type, UL type 4X						
Battery life	Battery life: 5 years at 25°C The RTC will be backed up for 5 days after the battery runs low. The RTC will be backed up by a super capacitor for 5 minutes after removing the old battery. (This assumes that the power is first turned ON for at least 5 minutes and then turned OFF.)							
International standards	EMC Directive (2004/108/EC) Bipbuilding standards LR, DN IP65 oil-proof, UL type 4X (fron ANSI 12.12.01 Class 1 Divisior RoHS Directive (2002/95/EC)	UL 508/CSA standard C22.2 No.142 * 4 EMC Directive (2004/108/EC) EN 61131-2:2007 Shipbuilding standards LR, DNV, and NK IP65 oil-proof, UL type 4X (front panel only) ANSI 12.12.01 Class 1 Division 2/CSA standard C22.2 ROHS Directive (2002/95/EC) KC Standards KN 61000-6-2:2012-06 for EMS and KN 61000-6-4:2012-06 for EMI						

- *1. The ambient operating temperature is subject to the following restrictions, depending on the mounting angle.
 - The ambient operating temperature is 0° to 40°C when the mounting angle is 0° or more and less than 45° to the horizontal.
 - The ambient operating temperature is 0° to 50°C when the mounting angle is 45° or more and 90° or less to the horizontal.
 - The ambient operating temperature is 0° to 50°C when the mounting angle is 90° or more and 135° or less to the horizontal.




*2. Use the Programmable Terminal within the following temperature and humidity ranges.



*4. Use power supply Class 2 to conform to UL Standards.

*3. Store the Programmable Terminal within the following temperature and humidity ranges.



NA Series


Version Information

NA series and Programming Devices

NA series		Corresponding unit versions/version	
Model	NA system version	NJ/NX-series CPU Units NX701-□□□□ NJ501-□□□□ NJ301-□□□□ NJ101-□□□□	Sysmac studio
NA5-15W NA5-12W	1.02 or later	NX701: 1.10 or later NJ101: 1.10 or later	1.13 or higher
NA5-72W NA5-9W NA5-7W	1.01 or later	NJ501 : 1.01 or later NJ501 Database Connection : 1.05 or later NJ301 : 1.01 or later	1.11 or higher


Components and Functions

Front Panel



No.	Name	Description	
(1)	Display	The entire display is a touch panel that also functions as an input device.	
(2)	RUN indicator	The status of the indicator changes according to the status of the NA.	
(3)	Function keys	There are three function keys: F1, F2, and F3. F1 Key, F2 Key, F3 Key You can use the function keys as execution conditions for the actions for global or page events. You can also use the function keys for interlocks.	

Components and Functions



No.	Name	Description	
(a)	Battery cover	Open this cover to replace the Battery.	
(b)	Expansion Unit connector *	For future expansion.	
(c)	SD Memory Card connector	Insert an SD Memory Card here.	
(4)	Ethernet port 1	Connect a device other than the Sysmac Studio.	
(d)	Ethernet port 2	Connect mainly the Sysmac Studio.	
(e)	Serial port *	For future expansion.	
(f)	USB host port Connect this port to a USB Memory Device, mouse, etc.		
(g)	USB slave port Connect the Sysmac Studio or other devices.		
(h)	Reset switch Use this switch to reset the NA.		
(i)	Battery connector Connect the connector on the backup Battery here.		
(j)	DIP switch * For future expansion. (The DIP switch is on a PCB that is accessed by opening the Battery cover Do not change any of the factory settings of the pins on the DIP switch. (Default setting: OFF)		
(k)	Battery This is the battery to backup the clock information in the NA.		
(I)	DC input terminals	Cinput terminals These are the power supply terminals. Connect the accessory power supply connector and supply power.	
(m)	ID information label	rmation label You can check the ID information of the NA.	

^{*}The DIP switch, Expansion Unit connector, and serial port are for future expansion.

Supported Devices

Manufacturer	Models	Connection method	Communications driver
	NX701 NJ501 NJ301 NJ101	Built-in EtherNet/IP port	Ethernet
	CJ2H-CPU64/65/66/67/68-EIP CJ2M-CPU31/32/33/34/35	Built-in EtherNet/IP port	- CIP Ethernet
•	CJ2H-CPU64/65/66/67/68-EIP CJ2M-CPU31/32/33/34/35	CJ1W-EIP21	
OMRON	CJ2H-CPU64/65/66/67/68-EIP CJ2M-CPU31/32/33/34/35	Built-in EtherNet/IP port	
	CJ1H-CPU65H/66H/67H CJ1H-CPU65H/66H/67H-R CJ1G-CPU42H/43H/44H/45H CJ1M-CPU11/12/13/21/22/23 CJ2H-CPU64/65/66/67/68(-EIP) CJ2M-CPU11/12/13/14/15 CJ2M-CPU31/32/33/34/35	CJ1W-ETN21 CJ1W-EIP21	FINS Ethernet