


connecting cable

NEBC-M12W8-E-10-N-B-LE8

Part number: 8094481

FESTO



Data sheet

Feature	Value
Based on the standard	EN 61076-2-101
Authorisation	c UL us - Listed (OL)
Certificate issuing department	UL E474609
Cable identification	Without inscription label holder
Product weight	489 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
Operating voltage range DC	0 ... 30 V
Operating voltage range AC	0 ... 30 V
Acceptable current load at 40°C	2 A
Surge strength	0.8 kV
Shielding	No
Cable length	10 m
Cable attribute	Suitable for chain link trunking
Test conditions of cable	Test conditions on request
Bending radius, fixed cable installation	≥ 30 mm
Bending radius, flexible cable installation	≥ 30 mm
Cable diameter	6 mm
Cable diameter tolerance	± 0,2 mm
Cable structure	8x0,25
Nominal conductor cross-section	0.25 mm ²
Wire ends	Sheath removed
Protection class	IP65 IP67
Note on degree of protection	in assembled condition
Ambient temperature	-25 ... 90 °C
Ambient temperature with flexible cable installation	-25 ... 90 °C
CE mark (see declaration of conformity)	in accordance with EU RoHS directive
Materials note	Conforms to RoHS
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Silver-grey
Material housing	TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Brass
Material insulation	PP