## NEUTRIK



## **NL4MPRXX**

This connector is fully compliant to the device standard IEC 62368-1, due to its component certification according to IEC 61984.

4 pole chassis connector, black round G-size flange, countersunk thru holes, 3/16" flat tabs.

The speakON panel mount connectors are the standard chassis connectors for loudspeaker / amplifier interconnections. They feature a unique metal locking system, making contact only once fully locked. The speakON receptacles are robust, versatile and easy to terminate.

## **Features & Benefits**

- IEC 61984 certified > IEC 62368-1 compliant
- Precise keyway for secure mating
- Metal insert in locking area

- Glass reinforced V-0 materials make it extremely robust and dependable
- Accurate twist lock latching system
- Airtight design optimized for speaker applications



## **Technical Information**

Product	
Title	NL4MPRXX
Gender	male

Electrical	
Contact resistance	≤ 2 mΩ
Dielectric strength	2.8 kVac
Insulation resistance	>0.1 G $\Omega$ (after dampheat)
Rated current per contact	25 A rms continuous (audio rating significantly higher, depending on signal)
Rated voltage	250 V ac
Attention	speakON is NOT to be used as an AC mains or power supply connector!

Mechanical	
Lifetime	> 5000 mating cycles
Termination	3/16" flat tabs (e.g. NLFASTON)
Locking device	Quick Lock
Chassis shape	round G-size flange
Layout	four thru holes

Material	
Contact plating	Ag
Locking element	Stainless Steel
Shell	Polyamide (PA 6.6)
Contacts	Copper Alloy

Environmental	
Flammability	UL94 V-0
Temperature range	-30 °C to +80 °C