General Specifications

Electrical Capacity (Resistive Load)

0.4VA maximum @ 28V AC/DC maximum Logic Level:

(Applicable Range 0.1mA ~ 0.1A @ 20mV ~ 28V)

Other Ratings

Contact Resistance: 50 milliohms maximum

Insulation Resistance: 500 megohms minimum @ 250V DC

Dielectric Strenath: 250V AC minimum between contacts for 1 minute minimum

Mechanical Life: 500,000 operations minimum **Electrical Life:** 500,000 operations minimum Standard: 1.5N ±0.5N **Nominal Operating Force:**

> High: 2.5N ±0.8N 1.5mm (.059") Stroke:

Materials & Finishes

Silicon rubber **Actuator:** Polycarbonate resin Case:

Base: Glass fiber reinforced polyamide resin **Movable Contact:** Silver over nickel with gold plating

Stationary Contacts: Brass with gold plating **Switch Terminals:** Brass with gold plating

Environmental Data

Operating Temperature Range: -25°C through +50°C (-13°F through +122°F) for Illuminated

-25°C through +70°C (-13°F through +158°F) for Nonilluminated

90 ~ 95% humidity for 96 hours @ 40°C (104°F) **Humidity:**

Vibration: 10 ~ 55Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range & returning

in 1 minute; 3 right angled directions for 2 hours

Shock: 50G (490m/s²) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)

Installation

Cap Installation Force: 5.0N maximum downward force on actuator

PCB Processing

Wave Soldering: 270°C maximum @ 6 seconds maximum Soldering:

Manual Soldering: 390°C maximum @ 4 seconds maximum

These devices are not process sealed. Hand clean locally using alcohol based solution. Cleaning:

Standards & Certifications

The NPO1 Series pushbuttons have not been tested for UL recognition or CSA certification. These switches are designed for use in a low-voltage, low-current, logic-level circuit.

When used as intended in a logic-level circuit, the results do not produce hazardous energy.



Distinctive Characteristics

Soft touch actuation achieved by mechanical silicon rubber structure.

Distinct, long stroke of 1.5mm (.059").

Entire cap is fully illuminated with single or bicolor LED.

Compact design with dimension of 12.5mm (.492") from PC board to top of cap.


Alternating legend options with bicolor LED.

Available in both high (2.5N) or standard (1.5N) operating force.


Gold plated contacts provide high reliability.

Crimped terminals ensure secure PC mounting and prevent dislodging during soldering.

Molded-in terminals prevent entry of flux, solvents, and other contaminants.




Actual Size





Amber/Blue



Refer to Ordering Table for Alternating Legend that corresponds with last 2 digits of part number.

AT3023JDG11 ~ AT3023JDG14

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

NP0115HG03LF-JF





POLE & CIRCUIT

Illuminated Models

		Plunger Position () = Momentary		Connected Terminals		Throw & Switch Schematic			
Pole	Model	Normal	Down	_	_	Notes:	Notes: Switch is marked with LC1, 1, L3, L4, L1, L2, 2, LC2. Lamp circuit is isolated and requires an external power source.		
SP	NP0115AG03L NP0115HG03L	OFF	(ON)	Normally Open	1-2	SPST	1 P 2 (+)O O (-)		

Nonilluminated Models

		Plunger Position () = Momentary		Connected Terminals		Throw & Switch Schematic			
Pole	Model	Normal	Down	_	_	Note:	Switch is marked with LC1, 1, L3, L4, L1, L2, 2, LC2.		
SP	NP0115AG03N NP0115HG03N	OFF	(ON)	Normally Open	1-2	SPST	1 2		

OPERATING FORCE



Standard Nominal Operating Force

1.5 ±0.5N Switch base is Black



High Nominal Operating Force

 $2.5 \pm 0.8N$ Switch base is Gray

CONTACTS, TERMINALS, & RATING

G03

Gold Contacts

Straight PC Terminals

0.4VA maximum @ 28V AC/DC maximum

ILLUMINATION



Illuminated




Nonilluminated



LED COLORS & SPECIFICATIONS

LEDs are an integral part of the switch and not available separately. The electrical specifications shown are determined at a basic temperature of 25°C.


If the source voltage exceeds the forward voltage, a ballast resistor is required. Specifications in parentheses () below for Bicolor LED denote simultaneous illumination of Red and Green.



 $R = \frac{E - V_F}{I_F}$

Where: R = Resistor Value (Ohms)
E = Source Voltage (V)
V_F = Forward Voltage (V)
I_E = Forward Current (A)

ATTENTION		Single Color LE	D	Bicolor LED			
ELECTROSTATIC SENSITIVE DEVICES	С	D	F	CF		DG	
Col	or Red	Amber	Green	Red	Green	Amber	Blue
Maximum Forward Current I _F	30mA	30mA	25mA	30 (25)mA	25 (25)mA	30mA	30mA
Typical Forward Current I _F	20mA	20mA	16mA	20 (20)mA	16 (5)mA	20mA	20mA
Forward Voltage V	1.95V	2.0V	3.3V	1.95V	3.3V	2.0V	3.2V
Maximum Reverse Voltage V	5V						
Current Reduction Rate Δ	0.41mA/°C above 25°C	0.38mA/°C above 25°C	0.33mA/°C above 25°C	0.40mA/°C above 25°C	0.33mA/°C above 25°C	0.40mA/°C above 25°C	0.40mA/°C above 25°C
Ambient Temperature Range		−25° ~ +50°C	•	−25° ~ +50°C			



CAP TYPES & COLORS

AT3022 12mm Square Cap

Material: Polycarbonate Resin



Cap for Single or Bicolor LED

JB Clear Lens/White Diffuser

Clear Lens/Red Diffuser

JD Clear Lens/Amber Diffuser

Clear Lens/Green Diffuser

AT3023 12mm Square Cap

Material: Polycarbonate Resin



Alternating Legend Cap for Bicolor LED

JCF Red/Green

JDG Amber/Blue

Clear Lens Alternating Legend Filter

14

Standard Alternating Legend Pairs



Green/Red or Blue/Amber




OFF

OFF

13

START

<u>'</u>



Green/Red

Blue/Amber

Green/Red Green/Red
or or
Blue/Amber Blue/Amber

Cap illumination is alternating Green/Red or Blue/Amber; legend text is black.


Contact factory for other Alternating Legends.

Legend illustrations are approximate representations of the actual characters on the filters.



AT3024 12mm Square Cap

Material: Polycarbonate Resin





Black











TYPICAL SWITCH DIMENSIONS

Illuminated • Straight PC











NP0115HG03LF-JF

PACKAGING



Partitioned Tray


Any quantity. No code is required. Switches may be packaged with or without caps installed.




Stick-Tube Packaging

50 pieces per stick

Switches must be ordered in 50-piece increments when stick-tube packaging is selected. This packaging is for the switch body only. Caps will be packaged separately.





LEGEND ORIENTATION

Top View

Bottom View






Orient cap with legend as shown here, and "LC2" at lower right of switch body. Orders for switches with legends will be assembled as illustrated.

PRECAUTIONS FOR HANDLING & STORAGE

- 1. NPO1 Pushbuttons are electrostatically sensitive. To prevent damage to LED, devices must be properly isolated from static electricity.
- 2. Once the cap is installed onto the switch body, it cannot be removed.
- 3. When assembling cap, align projection on switch body to slot on inside of cap. (Refer to illustration at right.)
- 4. * Legends may be printed on the lens with laser etch, screen print or pad print methods. Epoxy based ink is recommended.
- 5. Do not use excessive force during installation on PC board or for cap installation.
 - * NKK Switches can provide custom legends for caps. Contact factory for more information.





D79 www.nkk.com

Toggles

Pushbuttons

Programmable Illuminated PB

Keylocks

Ė

Touch

Accessories