



Netac flash drives can be widely used in computers, in-vehicle devices, game consoles and other devices that have a USB interface and are compatible with this product. It can easily realize data backup, storage and transmission.



## U352 Flash Drive

16GB

32GB

64GB

• Reliable and stable

128GB

## Highlights

- Curved smooth line design.
- Zinc alloy shell material, sturdy and durable.
- With lanyard hole at bottom.

## Product Specification

Interface	USB 3.0
Dimension(mm)	66.7*19.4*8.2mm
Net Weight(g)	About 18 g
Housing material	Zinc alloy
Standard color	Pearl nickel
Data transfer rate write(MB/s)	8-45MB/s
Data transfer rate read(MB/s)	60-150MB/s
operating temperature (°C)	0-60°C
Storage temperature (°C)	-20-70°C
Operation System	Windows 7/8 /10+ ;Mac OS X 10.5 +; Linux 2.6.x or +
Max Working Voltage(V)/Current(mA)	V=5V/A=150mA
Warranty period	5 years