

COMP-CARD®-System

SMC-40

Ceramic Capacitors, SMD
32 Values / 3.360 Pieces



Nova Article No.	SMC-40
Brand of Components	Vishay or alternative
Type	VJ
Size	0805
Tolerance	Depending on Capacitance and Ceramic
Temperature range	Depending on Capacitance and Ceramic
Voltage	10V-DC - 50V-DC
Number of Values	32
Quantity per Value	105
Total Quantity	3.360
Ring Binder	No
Flap	2 x FL16/10

Capacity	Voltage	Ceramic	Tolerance	Temperature
1pF-2,2pF	50V	COG/NP 0	± 0,1pF	-55 bis +125°C
3,3pF-6,8pF	50V	COG/NP 0	± 0,25pF	-55 bis +125°C
10pF-1,5nF	50V	COG/NP 0	± 5%	-55 bis +125°C
2,2nF - 100nF	50V	X7R	± 10%	-55 bis +125°C
150nF- 470nF	50V	X7R	± 10%	-55 bis +125°C
680nF	16V	X7R	± 10%	-55 bis +125°C
1000nF	10V	X7R	± 10%	-55 bis +125°C

Value-Quantity-Selection Flap 1



Nova Elektronik GmbH, Sachsstr. 6, 50259 Pulheim

www.nova-elektronik.de

For any questions please contact Info@nova-elektronik.de

Rev.01 13.12.22

COMP-CARD[®]-System

SMC-40

105 x 1pF	105 x 1,5pF	105 x 2,2pF	105 x 3,3pF
105 x 4,7pF	105 x 6,8pF	105 x 10pF	105 x 15pF
105 x 22pF	105 x 33pF	105 x 47pF	105 x 68pF
105 x 100pF	105 x 150pF	105 x 220pF	105 x 330pF

Value-Quantity-Selection Flap 2

105 x 470pF	105 x 1nF	105 x 1,5nF	105 x 2,2nF
105 x 4,7nF	105 x 6,8nF	105 x 10nF	105 x 15nF
105 x 22nF	105 x 33nF	105 x 47nF	105 x 100nF
105 x 220nF	105 x 470nF	105 x 680nF	105 x 1000nF

