





(€





### **Model Number**

### OBT40-R102-2P1-IO-V31-IR

Triangulation sensor (BGS) M8 connector, 4-pin

# **Features**

- Miniature design with versatile mounting options
- Best background suppressor in its
- Precision object detection, almost irrespective of the color
- Extended temperature range -40°C ... 60°C
- High degree of protection IP69K
- IO-link interface for service and process data


# **Product information**

The miniature optical sensors are the first devices of their kind to offer an end-to- end solution in a small single standard design from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.


The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

# **Dimensions**



# **Electrical connection**




### **Pinout**

Wire colors in accordance with EN 60947-5-2

BN WH BU BK (brown (white) (blue) (black)

# Indicators/operating means



- Operating indicator / dark on
- Signal indicator
- 3 Operating indicator / light on

#### **Technical data General specifications** 10 ... 40 mm Detection range 10 ... 50 mm Detection range max. starts from 50 mm Background suppression standard white, 100 mm x 100 mm Reference target Light source Light type modulated infrared light 850 nm LED risk group labelling exempt group Black/White difference (6 %/90 %) approx. 1 mm Diameter of the light spot approx. 3 mm at 40 mm Angle of divergence approx. 5 Ambient light limit EN 60947-5-2: 40000 Lux Functional safety related parameters 600 a $\mathsf{MTTF}_\mathsf{d}$ Mission Time (T<sub>M</sub>) 20 a 0 % Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator LED yellow: constantly on - object detected constantly off - object not detected **Electrical specifications** Operating voltage $\mathsf{U}_\mathsf{B}$ 10 ... 30 V DC max. 10 % Ripple No-load supply current $I_0$ < 25 mA at 24 V supply voltage Protection class Interface IO-Link (via C/Q = BK) Interface type Device profile Smart Sensor COM 2 (38.4 kBaud) Transfer rate IO-Link Revision 1.1 Min. cycle time 2.3 ms Process data witdh Process data input 1 Bit Process data output 2 Bit SIO mode support Device ID 0x11051A (1115418) Compatible master port type Output Switching type C/Q - Pin4: NPN normally closed / dark-on, PNP normally open / light-on, IO-Link /Q - Pin2: NPN normally open / light-on, PNP normally closed / Signal output 2 push-pull (4 in 1)outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max. 30 V DC max. 100 mA, resistive load Switching current Usage category DC-12 and DC-13 < 1.5 V DC Voltage drop $U_{d}$ Switching frequency 500 Hz Response time 1 ms Conformity Communication interface IEC 61131-9 Product standard EN 60947-5-2 **Ambient conditions** Ambient temperature -40 ... 60 °C (-40 ... 140 °F) Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Housing width 13.9 mm Housing height 31.9 mm Housing depth 18.3 mm Degree of protection IP67 / IP69 / IP69K Connection M8 x 1 connector, 4-pin Material Housing PC (Polycarbonate) Optical face Float glass approx. 10 g Cable length Approvals and certificates **UL** approval E87056, cULus Listed, class 2 power supply, type rating 1

### Accessories

#### IO-Link-Master02-USB

IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection

Other suitable accessories can be found at www.pepperl-fuchs.com

# **Curves/Diagrams**

