



2.5-in SSD DATA SHEET Built for Fast Data Centre Applications Nytro 3000 SAS SSD Series



The Seagate[®] Nytro[®] 3050 SAS SSDs delivers up to 15 TB in a 2.5-in × 15 mm form factor, a 12 Gb/s interface with dual ports for speeds up to 2,200 MB/s, drive monitoring, government-grade encryption, and up to 10 DWPD for fast, scalable, secure performance for demanding enterprise workloads.



Best-Fit Applications

- Server virtualisation
- OLTP databases
- Software-defined storage
- All-flash arrays
- Caching and tiering



Key Advantages

12 Gb/s SAS interface and dual ports for 24×7 performance

High-density capacities of up to 15 TB in a 2.5-in × 15 mm form factor

Low latency and high QoS for better responsiveness and user experience

Easily manage and monitor SSD health with SeaChest

Three endurance options to meet workload, deployment and TCO demands

Ensures reliable data protection for mission-critical applications

Seagate Secure[™] with Secure Download and Diagnostics (SD&D), SED, and SED FIPS 140-2 options for advanced data security¹

Built for easy integration with Linux and Microsoft OS

1 Self-encrypting drives (SED) are not available in all models or countries. May require TCG-compliant host or controller support.





Specifications			Nytro 3350 — Scaled Endurance		
Capacity	15.36TB	7.68TB	3.84TB	1.92TB	960GB
Standard Model	XS15360SE70045	XS7680SE70045	XS3840SE70045	XS1920SE70045	XS960SE70045
Standard Seagate Secure SED Model ¹	XS15360SE70055	XS7680SE70055	XS3840SE70055	XS1920SE70055	XS960SE70055
Seagate Secure FIPS 140-2/Common Criteria Mode ¹	XS15360SE70065	XS7680SE70065	XS3840SE70065	XS1920SE70065	XS960SE70065
Seagate Instant Secure Erase (ISE) Model	XS15360SE70075	XS7680SE70075	XS3840SE70075	XS1920SE70075	XS960SE70075
Features					
Interface (Dual Port)	12 Gb/s SAS	12 Gb/s SAS	12 Gb/s SAS	12 Gb/s SAS	12 Gb/s SAS
NAND Flash Type	3D eTLC	3D eTLC	3D eTLC	3D eTLC	3D eTLC
Form Factor	2.5 in × 15 mm	2.5 in × 15 mm	2.5 in × 15 mm	2.5 in × 15 mm	2.5 in × 15 mm
Performance — Single Port 12 Gb\s					
Sequential Read (MB/s) Sustained, 128 KB ¹	1,050	1,100	1,100	1,100	1,100
Sequential Write (MB/s) Sustained, 128 KB ²	950	1,050	1,050	1,050	1,050
Random Read (IOPS) Sustained, 4 KB ²	125,000	195,000	195,000	195,000	190,000
Random Write (IOPS) Sustained, 4 KB ²	15,000	80,000	80,000	70,000	60,000
Random 30% Write (IOPS) Sustained, 4 KB ²	60,000	150,000	150,000	135.000	115,000
Performance — Dual Port 12 Gb\s					
Sequential Read (MB/s) Sustained, 128 KB ²	2,100	2,200	2,200	2,200	2,150
Sequential Write (MB/s) Sustained, 128 KB ²	1,100	1,800	1,800	1,550	1,300
Random Read (IOPS) Sustained, 4 KB ²	165,000	250,000	250,000	250,000	250,000
Random Write (IOPS) Sustained, 4 KB ²	20,000	80,000	80,000	70,000	60,000
Random 30% Write (IOPS) Sustained, 4 KB ²	60,000	170,000	170.000	160,000	130,000
Endurance/Reliability	00,000	170,000	170,000	180,000	130,000
Lifetime Endurance (Drive Writes per Day)	1	1	1	1	1
Total Bytes Written (TB)	28,000	14,000	7,000	3,500	1,700
Non-recoverable Read Errors per Bits Read	1 per 10E17	1 per 10E17	1 per 10E17	1 per 10E17	1 per 10E17
Mean Time Between Failures (MTBF, hrs)	2.5 Million	2.5 Million	2.5 Million	2.5 Million	2.5 Million
Annualised Failure Rate (AFR)	0.35%	0.35%	0.35%	0.35%	0.35%
Limited Warranty (years)	5	5	5	5	5
Power Management					
+5/+12 V Max Start Current (A)	0.75/0.24	0.80/0.26	0.72/0.23	0.74/0.2	0.76/0.27
Average Idling Power (W)	4.6	4.6	4.6	4.6	4.6
Physical				-	
Height (in/mm, max) ³	0.591/15.00	0.591/15.00	0.591/15.00	0.591/15.00	0.591/15.00
Width (in/mm, max) ³	2.760/70.10	2.760/70.10	2.760/70.10	2.760/70.10	2.760/70.10
Depth (in/mm, max) ³	3.955/100.45	3.955/100.45	3.955/100.45	3.955/100.45	3.955/100.45
Weight (Ib/gm)	0.3638/165	0.3638/165	0.3638/165	0.3638/165	0.3638/165
Carton Unit Quantity	10	10	10	10	10
Cartons per Pallet	90	90	90	90	90
Cartons per Layer	9	9	9	9	9

1 Not all drives may be available in all countries. Seagate Secure drives meet ISO/IEC 27040 and NIST 800-88 standards and may require use of TCG-compliant host or controller support.

2 All performance measured at queue depth of 32 per PHY at beginning of life. System application performance may vary based on SAS host and prior system workload.

3 These base deck dimensions conform to the Small Form Factor Standard (SFF-8201) found at www.sffcommittee.org. For connector-related dimensions, see SFF-8223 (SAS models).





Specifications	Nytro 3550 — Mixed Workloads								
Capacity	6.4TB	3.2TB	1.6TB	800GB					
Standard Model	XS6400LE70045	XS3200LE70045	XS1600LE70045	XS800LE70045					
Standard Seagate Secure SED Model ¹	XS6400LE70055	XS3200LE70055	XS1600LE70055	XS800LE70055					
Seagate Secure FIPS 140-2/Common Criteria Mode ¹	XS6400LE70065	XS3200LE70065	XS1600LE70065	XS800LE70065					
Seagate Instant Secure Erase (ISE) Model	XS6400LE70075	XS3200LE70075	XS1600LE70075	XS800LE70075					
Features									
Interface (Dual Port)	12 Gb/s SAS	12 Gb/s SAS	12 Gb/s SAS	12 Gb/s SAS					
NAND Flash Type	3D eTLC	3D eTLC	3D eTLC	3D eTLC					
Form Factor	2.5 in × 15 mm	2.5 in × 15 mm	2.5 in × 15 mm	2.5 in × 15 mm					
Performance — Single Port 12 Gb/s									
Sequential Read (MB/s) Sustained, 128 KB ¹	1,100	1,100	1,100	1,100					
Sequential Write (MB/s) Sustained, 128 KB ²	1,050	1,050	1,050	1,050					
Random Read (IOPS) Sustained, 4 KB ²	195,000	195,000	195,000	190,000					
Random Write (IOPS) Sustained, 4 KB ²	130,000	130,000	130,000	105,000					
Random 30% Write (IOPS) Sustained, 4 KB ²	175,000	175,000	165,000	135,000					
Performance — Dual Port 12 Gb/s									
Sequential Read (MB/s) Sustained, 128 KB ²	2,200	2,200	2,200	2,150					
Sequential Write (MB/s) Sustained, 128 KB ²	1,800	1,800	1,700	1,300					
Random Read (IOPS) Sustained, 4 KB ²	250,000	250,000	250,000	250,000					
Random Write (IOPS) Sustained, 4 KB ²	135,000	130,000	130,000	105,000					
Random 30% Write (IOPS) Sustained, 4 KB ²	220,000	220,000	220,000	160,000					
Endurance/Reliability									
Lifetime Endurance (Drive Writes per Day)	3	3	3	3					
Total Bytes Written (TB)	35,000	17,500	8,700	4,400					
Non-recoverable Read Errors per Bits Read	1 per 10E17	1 per 10E17	1 per 10E17	1 per 10E17					
Mean Time Between Failures (MTBF, hrs)	2.5 Million	2.5 Million	2.5 Million	2.5 Million					
Annualised Failure Rate (AFR)	0.35%	0.35%	0.35%	0.35%					
Limited Warranty (years)	5	5	5	5					
Power Management									
+5/+12 V Max Start Current (A)	0.81/0.23	0.75/0.26	0.78/0.24	0.76/0.25					
Average Idling Power (W)	4.6	4.6	4.6	4.6					
Physical	ŕ	·	,						
Height (in/mm, max) ³	0.591/15.00	0.591/15.00	0.591/15.00	0.591/15.00					
Width (in/mm, max) ³	2.760/70.10	2.760/70.10	2.760/70.10	2.760/70.10					
Depth (in/mm, max) ³	3.955/100.45	3.955/100.45	3.955/100.45	3.955/100.45					
Weight (Ib/gm)	0.3638/165	0.3638/165	0.3638/165	0.3638/165					
Carton Unit Quantity	10	10	10	10					
Cartons per Pallet	90	90	90	90					
Cartons per Layer	9	9	9	9					

1 Not all drives may be available in all countries. Seagate Secure drives meet ISO/IEC 27040 and NIST 800-88 standards and may require use of TCG-compliant host or controller support.

2 All performance measured at queue depth of 32 per PHY at beginning of life. System application performance may vary based on SAS host and prior system workload.

3 These base deck dimensions conform to the Small Form Factor Standard (SFF-8201) found at www.sffcommittee.org. For connector-related dimensions, see SFF-8223 (SAS models).





Specifications	Nytro 3750 — Write Intensive								
Capacity	3.2TB	1.6TB	800GB	400GB					
Standard Model	XS3200ME70045	XS1600ME70045	XS800ME70045	XS400ME70045					
Standard Seagate Secure SED Model ¹	XS3200ME70055	XS1600ME70055	XS800ME70055	XS400ME70055					
Seagate Secure FIPS 140-2/Common Criteria Mode ¹	XS3200ME70065	XS1600ME70065	XS800ME70065	XS400ME70065					
- Ŭ									
Seagate Instant Secure Erase (ISE) Model XS3200ME70075 XS1600ME70075 XS800ME70075 XS400ME70075 Features									
Interface (Dual Port)	12 Gb/s SAS	12 Gb/s SAS	12 Gb/s SAS	12 Gb/s SAS					
NAND Flash Type	3D eTLC	3D eTLC	3D eTLC	3D eTLC					
Form Factor	2.5 in × 15 mm	2.5 in × 15 mm	2.5 in × 15 mm	2.5 in × 15 mm					
Performance — Single Port 12 Gb\s									
Sequential Read (MB/s) Sustained, 128 KB ¹	1,100	1,100	1,100	1,100					
Sequential Write (MB/s) Sustained, 128 KB ²	1,050	1,050	1,050	1,050					
Random Read (IOPS) Sustained, 4 KB ²	195,000	195,000	195,000	190,000					
Random Write (IOPS) Sustained, 4 KB ²	200,000	200,000	200,000	160,000					
Random 30% Write (IOPS) Sustained, 4 KB ²	200,000	200,000	200,000	160,000					
Performance — Dual Port 12 Gb\s	200,000		200,000	100,000					
Sequential Read (MB/s) Sustained, 128 KB ²	2.200	1,400	2,200	2,150					
Sequential Write (MB/s) Sustained, 128 KB ²	1,800	1,800	1,700	1,300					
Random Read (IOPS) Sustained, 4 KB ²	250,000	250,000	250,000	250,000					
Random Write (IOPS) Sustained, 4 KB ²	210,000	210,000	220,000	180,000					
	-			*					
Random 30% Write (IOPS) Sustained, 4 KB ² 250,000 250,000 240,000 190,000 Endurance/Reliability									
Lifetime Endurance (Drive Writes per Day)	10	10	10	10					
Total Bytes Written (TB)	58,400	29,200	14,600	7,300					
Non-recoverable Read Errors per Bits Read	1 per 10E17	1 per 10E17	1 per 10E17	1 per 10E17					
Mean Time Between Failures (MTBF, hrs)	2.5 Million	2.5 Million	2.5 Million	2.5 Million					
Annualised Failure Rate (AFR)	0.35%	0.35%	0.35%	0.35%					
Limited Warranty (years)	5	5	5	5					
Power Management									
+5/+12 V Max Start Current (A)	0.81/0.26	0.74/0.25	0.75/0.23	0.73/0.23					
Average Idling Power (W)	4.6	4.6	4.6	4.6					
Physical			· · · · · · · · · · · · · · · · · · ·						
Height (in/mm, max) ³	0.591/15.00	0.591/15.00	0.591/15.00	0.591/15.00					
Width (in/mm, max) ³	2.760/70.10	2.760/70.10	2.760/70.10	2.760/70.10					
Depth (in/mm, max) ³	3.955/100.45	3.955/100.45	3.955/100.45	3.955/100.45					
Weight (Ib/gm)	0.3638/165	0.3638/165	0.3638/165	0.3638/165					
Carton Unit Quantity	10	10	10	10					
Cartons per Pallet	90	90	90	90					
Cartons per Layer	9	9	9	9					

1 Not all drives may be available in all countries. Seagate Secure drives meet ISO/IEC 27040 and NIST 800-88 standards and may require use of TCG-compliant host or controller support.

2 All performance measured at queue depth of 32 per PHY at beginning of life. System application performance may vary based on SAS host and prior system workload.

3 These base deck dimensions conform to the Small Form Factor Standard (SFF-8201) found at www.sffcommittee.org. For connector-related dimensions, see SFF-8223 (SAS models).

seagate.com

© 2022 Seagate Technology LLC. All rights reserved. Seagate, Seagate Technology, and the Spiral logo are registered trademarks of Seagate Technology LLC in the United States and/or other countries. Nytro, the Nytro logo, Seagate Secure, and the Seagate Secure logo are either trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. When referring to drive capacity, one gigabyte, or GB, equals one billion bytes and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formating and other functions, and thus will not be available for data storage. Actual data rates may vary depending on operating environment and other factors, such as chosen interface and disk capacity. The export or re-export of Seagate reserves the right to change, without notice, product offerings or specifications. DS2101-2206GB

