

PRODUCT DATASHEET P CLAS A 75 FR 11 W/827 K E27

PARATHOM CLASSIC A DIM | Dimmable LED lamps, classic bulb shape



AREAS OF APPLICATION

- Domestic applications
- General illumination
- Outdoor applications only in suitable luminaires

- Very long lifetime of up to 25,000 h
- Low energy consumption
- High color consistency thanks to narrow binning
- Easy replacement of classic lamps thanks to compact design
- Instant 100 % light, no warm-up time

PRODUCT FEATURES

- LED alternative to conventional lamps
- Good quality of light; color rendering index R_a : \geq 80; constant chromaticity
- High color consistency: < 6 SDCM
- Dimmable (with many common dimmers, see also www.ledvance.com/dim)
- Mercury-free lamps



March 14, 2019, 21:38:38 P CLAS A 75 FR 11 W/827 K E27

TECHNICAL DATA

Electrical data

Rated wattage	11.00 W
Nominal wattage	11.00 W
Nominal voltage	220240 V
Operating frequency	5060 Hz
Power factor λ	> 0.80
Claimed equiv. conventional lamp power	75 W

Photometrical data

Nominal luminous flux	1055 lm
Rated luminous flux	1055 lm
Rated color temperature	2700 К
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 К
Luminous flux	1055 lm
Color rendering index Ra	≥80
Standard deviation of color matching	≤6 sdcm
Color rendering index Ra	≥80

Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

Dimensions & weight



Overall length	115.0 mm
Diameter	60.0 mm
Outer bulb	A60

PRODUCT DATASHEET

Length	115.0 mm
Lifernan	

Lifespan

Nominal lamp life time	25000 h
Rated lamp life time	25000 h
Number of switching cycles	100000
Lumen maintenance at end of service life	0.70

Additional product data

Base (standard designation)	E27		
Mercury content	0.0 mg		
Mercury-free	Yes		
Design / version	Frosted		
Show WEEE picto	Yes		
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value/In development, data preliminary/In preparation/LED lamps contain several electronic components. Under unfavourable conditions these can lead to acoustic noise. In case of resonance even low noise can cause audible effect. Possible factors influencing this are the installation, the design of the		


Capabilities

Dimmable	Yes
Certificates & standards	
Energy efficiency class	A+
Energy consumption	11 kWh/1000h

Order reference	LEDPCLA75D 10,5
-----------------	-----------------

lamp holder and the luminaire (acoustic resonance effect) as well as the dimmer or the transformer (harmonics or electronic resonance)

Light Distribution



LDC typ polar

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075100992	Folding carton box 1	60 mm x 60 mm x 120 mm	95.00 g	0.43 dm ³
4058075101005	Shipping carton box 10	315 mm x 131 mm x 126 mm	1063.00 g	5.20 dm ³
4058075292574	Folding carton box 1	61 mm x 61 mm x 109 mm	97.00 g	0.41 dm³
4058075292581	Shipping carton box 10	318 mm x 133 mm x 134 mm	1088.00 g	5.67 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For dimming conformity see

www.ledvance.com/dim

For further products and actual information concerning LED lamps see

www.ledvance.com/ledlamps

For Guarantee see

www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.