

# PRELIMINARY-PRODUCT DATASHEET P CLAS A 150 21 W/827 K E27

PARATHOM CLASSIC A DIM | Dimmable LED lamps, classic bulb shape



#### **AREAS OF APPLICATION**

- Domestic applications
- General illumination
- Outdoor applications only in suitable luminaires

#### **PRODUCT BENEFITS**

- Very long lifetime of up to 25,000 h
- Low energy consumption
- High color consistency thanks to narrow binning
- Easy replacement of classic lamps thanks to compact design
- Instant 100 % light, no warm-up time

#### **PRODUCT FEATURES**

- LED alternative to conventional lamps
- Good quality of light; color rendering index  $R_a$ :  $\geq 80$ ; constant chromaticity
- High color consistency: < 6 SDCM
- Dimmable (with many common dimmers, see also www.ledvance.com/dim)
- Mercury-free lamps



# **TECHNICAL DATA**

# Electrical data

Rated wattage	21.00 W
Nominal wattage	21.00 W
Nominal voltage	220240 V
Operating frequency	5060 Hz
Power factor λ	> 0.90
Claimed equiv. conventional lamp power	150 W


# Photometrical data

Nominal luminous flux	2452 lm
Rated luminous flux	2452 lm
Rated color temperature	2700 K
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 K
Luminous flux	2452 lm
Color rendering index Ra	≥80
Standard deviation of color matching	≤6 sdcm
Color rendering index Ra	≥80

# Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

# Dimensions & weight



Overall length	143.0 mm
Diameter	67.0 mm
Outer bulb	A67

Length	143.0 mm

# Temperatures & operating conditions

Maximum temperature at tc test point	109 °C
--------------------------------------	--------

# Lifespan

Nominal lamp life time	25000 h	
Rated lamp life time	25000 h	
Number of switching cycles	100000	
Lumen maintenance at end of service life	0.70	

#### Additional product data

Base (standard designation)	E27	
Mercury content	0.0 mg	
Mercury-free	Yes Frosted	
Design / version		
Show WEEE picto	Yes	
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value	

# Capabilities

Ī	Dimmable	Yes

#### Certificates & standards

Energy efficiency class	A+
Energy consumption	21 kWh/1000h

### Country-specific categorizations

Order reference LEDPCLA150D	
-----------------------------	--

#### **LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075147072	Folding carton box 1	67 mm x 67 mm x 145 mm	233.00 g	0.65 dm <sup>3</sup>
4058075147089	Shipping carton box 10	345 mm x 142 mm x 157 mm	1947.00 g	7.69 dm³
4058075292611	Folding carton box 1	67 mm x 67 mm x 145 mm	233.00 g	0.65 dm <sup>3</sup>

4058075292628	Shipping carton box	348 mm x 145 mm x 159 mm	2457.00 g	8.02 dm³
	10			

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

#### **REFERENCES / LINKS**

For dimming conformity see

www.ledvance.com/dim

For further products and actual information concerning LED lamps see

www.ledvance.com/ledlamps

For Guarantee see

www.ledvance.com/guarantee

#### **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.