

«PeakTech® P 1403» 50 MHz / 2CH, 500MS/s Digital storage oscilloscope



Product number: P 1403

EAN: 4250569406539

Description

Specially developed for the education and hobby sector, this new series of fully-fledged digital storage oscilloscopes offers the best possible price/performance ratio without having to compromise on functionality or technical features. Whether Autoset and Autoscale, mathematical measurement functions, FFT or XY mode and even a zoom function, all standard market functions are already integrated in this series. The data storage of the waveforms is either internal with memory for 16 waveforms or external on a USB memory in TXT, CSV or BIN format, which can be read out with the included software. Configurations can also be saved internally or screenshots of the display can be saved externally. The display of the waveforms can be achieved quickly and user-friendly through the Autoset function, via AutoScale the measured waveforms can be displayed even more precisely as required, whereby these settings can of course also be carried out completely manually via the key control.

Technical features

- 2 channel oscilloscope with 50 MHz analogue bandwidth at max. 500 MS/s sampling rate
- 17,5 cm (7") TFT colour display with 800 x 480 pixels
- USB device connection for real-time data transmission
- USB host connection for external USB data carriers
- Handy and flat housing design with carrying handle
- Autoset function for user-friendly operation



- Recording length of max. 10.000 points
- Automatic measuring modes, XY mode and FFT function
- Safety: EN 61010-1; CAT II 400V
- Accessories: USB cable, software CD for Windows, mains cable, probes and operating instructions

Specifications

Sampling 1 CH: 500 MS/s

Sampling 2 CH: 250 MS/s

USB:

Bandwidth: 50 MHz

Channels: 2 CH

Display Type: Color-TFT

Hor. scale max.: 1000 s/div

Hor. scale min.: 2 ns/div

Mains voltage: 110/240 V AC; 50/60 Hz

Memory depth: 10.000 Points

Resolution: 800 x 480 Pixel

Rise Time: < 7 ns

Screen size (TFT): 17,5 cm (7")

Vert. resolution: 8 Bit

Vert. scale max.: 5 V/div

Vert. scale min.: 2 mV/div