
Precision Surface Mount Resistors



PCF Series

- Precision metal film technology
- Extended ohmic range 1R 3M
- Precision to ±0.01% and 5ppm/°C
- TCR grades 50, 25, 15, 10, 5ppm/°C
- Passivated range for superior humidity performance
- Load life stability and humidity to 0.05%



Electrical Data - Standard Range

	TCR	Power	Limiting Element	Ment Ohmic Value Range*				
Туре	(ppm/°C)	(W)	Voltage (V)	0.5%	0.25%	0.1%	0.05%	0.01%
PCF0201	50 25	0.031	15	49R9-33K ¹ 49R9-5K ¹			-	
	50 25				10R-205K			-
PCF0402	15 10	0.063	25		-		49R9-33K 49R9-12K	
	5 50			2R.		4R7-1M	49R9-5K	
PCF0603	25 15	0.063	50		• 1101		4R7-332K	2400 4000
	10 5				-	4R7-332K	24R9-15K	24R9-100K
••••••	50 25			1R-	-2M	4R7-2M	2 113 131	-
PCF0805	15	0.1	100	•••••	•••••	4R7-511K	4R7-511K	24R9-200K
	10 5			-		24R9-30K ²		24R9-30K
	50 25		150	1R-	2M5	4R7-2M5	4R7-511K	-
PCF1206	15 10	0.125		150		_	4R7-1M	417-3118
	5					24R9-50K ²		24R9-50K
	50 25			1R-	2M5	4R7-2M5	4R7-1M	-
PCF1210	15 10 5	0.2	150		-	4R7-1M		24R9-500K
	5 50			24R9-50		-50K ²	24R9-50K	
	25			1R-	-3M	4R7-3M	4R7-1M	-
PCF2010	15 10	0.25	150		-	4R7-1M		24R9-500K
	5				•••••		24R9-100K	T
	50 25			1R-	-3M	4R7-3M	4R7-1M	-
PCF2512	15 10	0.5	150		_	4R7-1M	7107 1101	24R9-500K
	5						24R9-100K	

^{*} Standard values E24 or E96. Other values may be available by request.

Note 1: PCF0201 also available in 1% tolerance. Note 2: Higher values available on request.

General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.



www.bitechnologies.com www.irctt.com www.welwyn-tt.com



Electrical Data - High Power Range

	T.C.D.	Power	Limiting	Ohmic Value Range *				
Туре	TCR (ppm/°C)	(W)	Element Voltage (V)	0.5%	0.25%	0.1%	0.05%	0.01%
	50 25				4R7-1M		4R7-332K	2.400.4001/
PCF0603H	15 10	0.1	75		4R7-332K		4K/-33ZK	24R9-100K
L	5					24R9-15K		
	50 25			1R	-1M	4R7–1M	407 54416	2.400.2001/
PCF0805H	15 10	0.125	150		4R7-1M 4R7-511K		4R7-511K	24R9-200K
	5							
	50 25			4R7-1M		24R9-500	24R9-500K	
PCF1206H	15 10	0.25	200				24N9 300K	
•••••	5 50			24R9-50K			·····	
PCF1210H	25 15 10	0.33	200	4R7-1M			24R9-500K	
	5			24R9-50K				
PCF2010H	50 25 15 10	0.33	200			4R7-1M		24R9-500K
	5			24R9-50K				
PCF2512H	50 25 15 10	0.75	200	1R	-2K	4R7	7-2K	24R9-2K

^{*} Standard values E24 or E96. Other values may be available by request.

Electrical Data - Extended High Power Range

				•		•		
	TCR	Power	Limiting Ohmic Value Range *					
Туре	(ppm/°C)	(W)	Voltage (V)	0.5%	0.25%	0.1%	0.05%	0.01%
PCF0603X	50 25	0.166	100	10R-332K				
PCF0805X	50 25	0.25	150	10R-500K				
PCF1206X	50 25	0.333	200	10R-1M				
PCF2512X	50 25	1	200	1R-100R 4R7-100R				

Electrical Data - Passivated Range

_	TCR	TCR Power Limiting Element			Oh	mic Value Raı	nge *		
Type	(ppm/°C)	(W)	Voltage (V)	0.5%	0.25%	0.1%	0.05%	0.01%	
PCF0402P	50 25	0.063	25	25R-25K					
	15				• • • • • • • • • • • • • • • • •	49R9-12K	•••••	• • • • • • • • • • • • •	
PCF0603P	50 25	0.063	0.063 50			25R-332K			
	15			25R-100K				• • • • • • • • • • • • • •	
PCF0805P	50 25	0.1	0.1 100		10R-800K				
	15			25R-200K					
PCF1206P	50 25	0.125	150	10R-1M					
	15			25R-500K				• • • • • • • • • • • • • • • • • • • •	
PCF2010P	50 25 0.25	0.25	150			10R-1M			
	15				• • • • • • • • • • • • • • • • • • • •	25R-500K	• • • • • • • • • • • • • • • • • •	• • • • • • • • • • • • • •	
PCF2512P	50 25	0.5	150			10R-1M			
	15		.50	• • • • • • • • • • • • • • • • • • • •	•••••	10R-1M	•••••		

^{*} Standard values E24 or E96. Other values may be available by request.

General Note


TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.





Physical Data

Dimensions (mm) and Weight						
	L	W	T max	Α	С	Wt
0201	0.58 ± 0.05	0.29 ± 0.05	0.26	0.15 ± 0.05	0.12 ± 0.05	1
0402	1.0 ± 0.05	0.5 ± 0.05	0.40	0.2 ± 0.1	0.2 ± 0.1	3
0603	1.6 ± 0.2	0.8 <u>±</u> 0.2	0.55	0.3 <u>±</u> 0.2	0.3 <u>±</u> 0.2	6
0805	2.0 ± 0.2	1.25 ± 0.2	0.65	0.4 ± 0.25	0.3 ± 0.2	9
1206	3.05 ± 0.15	1.55 ± 0.15	0.65	0.35 ± 0.25	0.42 ± 0.2	20
1210	3.10 ± 0.15	2.4 ± 0.15	0.50	0.55 ± 0.25	0.4 ± 0.2	25
2010	4.9 ± 0.2	2.4 ± 0.2	0.65	0.5 <u>±</u> 0.25	0.6 ± 0.3	36
2512	6.3 ± 0.2	3.1 ± 0.2	0.65	0.5 ± 0.25	0.6 ± 0.3	55



Construction

A thin-film material is selectively deposited on a 96% alumina substrate together with metallic contacts at each end of the resistor. The unadjusted resistors are heat treated to give the required TCR and stability, then a precisely controlled laser trim process adjusts the resistance value. Epoxy protection is applied and wrap-around terminations are added and plated with Nickel then Tin. Each resistor is measured immediately before packing into tape.

Terminations

The chips are supplied with 100% Sn matte plated wrap-around terminations suitable for soldering.

Performance Data - Standard Range

Test Parameters	Conditions	Maximum change (+0.05R)			
		≥0.05% tolerance	Chip size	0.01% tolerance	
			0402	0603 to 2512	
Load life	1000 hours rated load @ 70°C	0.25%	0.5%	0.05%	
Humidity 1000 hours @ 40°C, 90 - 95%RH		0.3%	0.3%	0.05%	
Short term overload	6.25 x rated Power , or 2 x LEV, for 5 sec	0.5%	0.5%	0.05%	
High temperature operation	1000 hours at 125°C	0.25%	0.25%	0.25%	
Temperature cycle	5 cycles -55 C, 125°C	0.1%	0.1%	0.05%	
Resistance to solder heat	270°C, 10 sec	0.2%	0.2%	0.05%	
Solderability	235°C, 2 sec	95% minimum coverage		ge	

Performance Data - High Power Range/Extended High Power Range

Test Parameters	Conditions	Maximum change (+0.05R)	
Load life	1000 hours rated load @ 70°C	0.5%	
Humidity 1000hrs @ 40°C, 90 - 95%F		0.5%	
Short term overload	6.25 x rated Power, or 2 x LEV, for 5 sec	0.5%	
High temperature operation	1000 hours at 155°C	0.5%	
Temperature cycle	5 cycles -55°C, 150°C	0.25%	
Resistance to solder heat	270°C, 10 sec	0.2%	
Solderability	235°C, 2 sec	95% minimum coverage	

Performance Data - Passivated Range

Test Parameters	Conditions	Maximum change (+0.05R)		
		0603 to 2512	0402	
Load life 1000 hours rated load @ 70°C		0.05%	0.25%	
Humidity	1000hrs @ 40°C, 90 - 95%RH	0.05%	0.5%	
Short term overload	6.25 x rated Power, or 2 x LEV, for 5 sec	0.02%	0.1%	
High temperature operation	High temperature operation 1000 hours at 125°C		0.5%	
Temperature cycle	5 cycles -55 C, 125°C	0.02%	0.1%	
Resistance to solder heat 270°C, 10 sec		0.02%	0.1%	
Solderability	235°C, 2 sec	95% minim	um coverage	

General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.




Precision Surface Mount Resistors

PCF Series







Solderability

The terminations have an electroplated nickel barrier and tin coating. This ensures excellent 'leach' resistance properties and solderability.

Packaging

PCF Resistors are supplied taped and reeled as per IEC 286-3.


Application Notes

PCF resistors are ideally suited for handling by automatic methods due to their rectangular shape and the small dimensional tolerances. Electrical connection to a ceramic substrate or to a printed circuit board can be made by reflow or wave soldering of wrap-around terminations.

Wrap-around terminations provide good leach properties and ensure reliable contact. Due to the robust construction, the PCF can be immersed in the solder bath for 30 seconds at 260 C. This enables the resistor to be mounted on one side of a printed circuit board and wire-leaded components applied on the other side.

PCF resistors themselves can operate at a maximum temperature of 125 C (see performance above) (155 C for High Power grades). For soldered resistors, the joint temperature should not exceed 110 C. This condition is met when the stated power levels at 70 C are used.

Ordering Procedure



Packing

0.1%

В

		0201, 0402	10,000/reel			
		0603, 0805, 1206,	•••••••	Ctandard		
I		1210	5000/reel	Standard		
		2010, 2512	4000/reel			
T1		0402, 0603, 0805,	1000/2001	Please enquire to confirm		
''	11	1206, 2010, 2512	1000/reel	availability of 1000 piece reels		

General Note

TT electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT electronics' own data and is considered accurate at time of going to print.

