DATASHEET - PFIM-63/4/003-XG/B



Residual current circuit-breaker, all-current sensitive, 63 A, 4p, 30 mA, type XG/B



Part no. Catalog No. PFIM-63/4/003-XG/B 300306

Delivery program			
Basic function			Residual current circuit-breakers
Number of poles			4 pole
Application			Switchgear for residential and commercial applications
Rated current	l _n	A	63
Rated short-circuit strength	I _{cn}	kA	10
Rated fault current	$I_{\Delta N}$	А	0.03
Туре			Туре В
Tripping		s	Short time-delayed
Product range			PFIM
Sensitivity			All current sensitive
Impulse withstand current			Surge-proof, 3 kA

Technical data

Electrical			
Types conform to			IEC/EN 61008 IEC/EN 62423
Current test marks			As per inscription
Standards			IEC/EN 61008 IEC/EN 62423
Rated operational voltage	Ue	V	
	Ue	V AC	
Rated operating voltage	U _e	V AC	230/400
Rated frequency	f	Hz	50
Limit values of the operating voltage			
Test circuit		V AC	196 - 253
Sensitivity			All current sensitive
Rated insulation voltage	Ui	V	440
Rated impulse withstand voltage	U _{imp}	kV	4
Rated short-circuit strength	I _{cn}	kA	10
Max. admissible back-up fuse			
Short-circuit	gG/gL	А	63
Overload	gG/gL	А	63
Rated making and breaking capacity / Rated residual making and breaking capacity	$I_m / I_{\Delta m}$	A	630
Max. back-up fuse		A gL/gG	63
Maximum max. as short-circuit protective device		A gL	
Back-up fuse		A gL	63
lifespan			
Electrical	Operations		≧ 4000
Mechanical	Operations		≧ 20000
References			
Auxiliary switch for subsequent installation			Z-HK 248432
Tripping signal contact for subsequent installation			Z-NHK 248434
Remote control and automatic switching device			Z-FW/LP 248296
Compact enclosure			KLV-TC-4 276241
Switching interlock			IS/SPE-1TE 101911
Sealing cover set			Z-RC/AK-4MU 101062

Mechanical

Mechanica		
Standard front dimension	mm	45
Device height	mm	80
Built-in width	mm	70 (4TE)
Mounting		Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715
Degree of Protection		IP40, IP54 (with moisture-proof enclosure)
Terminals top and bottom		Open mouthed/lift terminals
Terminal protection		finger and hand touch safe, DGUV VS3, EN 50274
Terminal cross-section		
Solid	mm ²	1.5 - 35
Stranded	mm ²	2 x 16
Thickness of busbar material	mm	0.8 - 2
Permissible storage and transport temperatures	°C	-35 - +60
Climatic proofing		25-55°C/90-95% relative humidity according to IEC 60068-2
Thickness of busbar material	mm	
Material thickness	mm	0.8 - 2

Design verification as per IEC/EN 61439

Design verification as per IEC/EN 61439			
Technical data for design verification			
Rated operational current for specified heat dissipation	I _n	А	63
Heat dissipation per pole, current-dependent	P _{vid}	W	0
Equipment heat dissipation, current-dependent	P _{vid}	W	10
Static heat dissipation, non-current-dependent	P _{vs}	W	0
Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	50
			Starting at 40 °C, the max. permissible continuous current decreases by 2.2% for every 1 °C
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Meets the product standard's requirements.
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9 Insulation properties			
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0				
Circuit breakers and fuses (EG000020) / Residual current circuit breaker (RCCB) (EC000003)				
Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / Residual current circuit breaker (RCCB) (ecl@ss10.0.1-27-14-22-01 [AAB906014])				
Number of poles		4		
Rated voltage	V	400		
Rated current	А	63		
Rated fault current	А	30		
Rated insulation voltage Ui	V	440		
Rated impulse withstand voltage Uimp	kV	4		
Mounting method		DIN rail		
Leakage current type		В		
Selective protection		No		
Short-time delayed tripping		Yes		
Short-circuit breaking capacity (Icw)	kA	10		
Surge current capacity	kA	3		
Frequency		50 Hz		
Additional equipment possible		Yes		
With interlocking device		Yes		
Degree of protection (IP)		IP20		
Width in number of modular spacings		4		
Built-in depth	mm	70.5		
Ambient temperature during operating	°C	-25 - 50		
Pollution degree		2		
Connectable conductor cross section multi-wired	mm²	1.5 - 16		
Connectable conductor cross section solid-core	mm²	1.5 - 35		