
Polycarbonate enclosures PK







Material:

Grey enclosure and cover (version .000) from fibreglass-reinforced polycarbonate, transparent cover (version .100) from polycarbonate, cover screws from polyamide, insulating bungs from polyethylene.

Colour: RAL 7035

Protection category: IP 66 to EN 60 529/10.91

Supply includes:

Enclosure and cover, cover screws, insulating bung for wall mounting screws (not with 9530.000 and 9531.000), all-round foamed-in PU seal.

Approvals:

Bureau Veritas

| Width (B1) in mm | 50 | 50 | 65 | 65 | 94 | 94 | 94 | 94 |
|-------------------------------------|----------|----------|----------|----------|----------|----------|----------|----------|
| Height (H1) in mm | 52 | 65 | 65 | 65 | 65 | 65 | 94 | 94 |
| Depth (T1) in mm | 35 | 35 | 57 | 81 | 57 | 81 | 57 | 81 |
| Model No. PK with cable gland | 9530.000 | 9531.000 | _ | - | _ | _ | _ | _ |
| Model No. PK with grey cover | - | _ | 9500.000 | 9501.000 | 9502.000 | 9503.000 | 9504.000 | 9505.000 |
| Model No. PK with transparent cover | - | - | - | - | _ | - | 9504.100 | _ |
| Packs of | 10 | 10 | 12 | 12 | 8 | 8 | 6 | 6 |
| | | | | | | | | |
| Width (B1) in mm | 110 | 110 | 130 | 130 | 130 | 130 | 180 | 180 |
| Height (H1) in mm | 110 | 110 | 94 | 94 | 130 | 130 | 94 | 94 |
| Depth (T1) in mm | 66 | 90 | 57 | 81 | 75 | 99 | 57 | 81 |
| Model No. PK with grey cover | 9506.000 | 9507.000 | 9508.000 | 9509.000 | 9510.000 | 9511.000 | 9512.000 | 9513.000 |
| Model No. PK with transparent cover | 9506.100 | 9507.100 | 9508.100 | 9509.100 | 9510.100 | 9511.100 | 9512.100 | 9513.100 |
| Packs of | 6 | 6 | 4 | 4 | 4 | 4 | 2 | 2 |





Material:

Grey enclosure and cover (version .000) from fibreglass-reinforced polycarbonate, transparent cover (version .100) from polycarbonate, cover screws from polyamide, insulating bungs from polyethylene.

Colour: **RAL 7035**

Protection category: IP 66 to EN 60 529/10.91

Supply includes:

Enclosure and cover, cover screws, insulating bungs for wall mounting screws, all-round foamed-in PU seal.

Approvals:

Bureau Veritas

| Width (B1) in mm | 180 | 180 | 180 | 182 | 182 | 182 |
|-------------------------------------|----------|----------|----------|----------|----------|----------|
| Height (H1) in mm | 110 | 110 | 110 | 180 | 180 | 180 |
| Depth (T1) in mm | 90 | 111 | 165 | 90 | 111 | 165 |
| Model No. PK with grey cover | 9514.000 | 9515.000 | 9516.000 | 9517.000 | 9518.000 | 9519.000 |
| Model No. PK with transparent cover | 9514.100 | 9515.100 | 9516.100 | 9517.100 | 9518.100 | 9519.100 |
| Packs of | 2 | 2 | 2 | 1 | 1 | 1 |

| Width (B1) in mm | 254 | 254 | 254 | 360 | 360 |
|-------------------------------------|----------|----------|----------|----------|----------|
| Height (H1) in mm | 180 | 180 | 180 | 254 | 254 |
| Depth (T1) in mm | 90 | 111 | 165 | 111 | 165 |
| Model No. PK with grey cover | 9520.000 | 9521.000 | 9522.000 | 9523.000 | 9524.000 |
| Model No. PK with transparent cover | 9520.100 | 9521.100 | 9522.100 | 9523.100 | 9524.100 |
| Packs of | 1 | 1 | 1 | 1 | 1 |



Turn-lock fastener

A quick, convenient screw fastening aid is obtained by clipping into the head of the lid screw.

| Material | : |
|----------|----|
| Polyami | de |

| | Packs of | Model No. PK |
|--------------------|----------|--------------|
| For all enclosures | 100 | 9582.000 |


Supply includes:

1 pack

Polycarbonate enclosures PK

With metric knockouts





Material: Grey enclosure and lid of fibreglass-reinforced polycarbonate, lid screws of polyamide, insulating bung of polythene.

Colour: RAL 7035

Protection category: IP 66 to EN 60 529

Supply includes: Enclosure and lid, cover screws, insulating bungs for wall mounting screws, all-round foamed-in PU seal. Approvals:

• Bureau Veritas

| Width (B1) in mm | 65 | 130 | 180 | 254 |
|-------------------|----------|----------|----------|----------|
| Height (H1) in mm | 65 | 94 | 110 | 180 |
| Depth (T1) in mm | 57 | 57 | 90 | 111 |
| Model No. PK | 9500.050 | 9508.050 | 9514.050 | 9521.050 |
| Packs of | 12 | 4 | 2 | 1 |

PK 9500.050

PK 9508.050

PK 9514.050

PK 9521.050

→ M16/20


M20M20/25

M25/32

M32/40







Accessories



Mounting plate

For individual configuration of the enclosure interior, the mounting plate offers a stable, secure and flexible design option.

Design:

Melamine phenol-coated laminated paper, 2.5 mm thick.

Colour:

RAL 7035

Supply includes: Self-tapping assembly screws.

| To fit | Width mm | Height mm | Packs of | Model No. PK |
|--|-------------|--------------|----------|------------------------|
| PK 9500.000 / PK 9501.000 | 45 | 45 | 12 | 9540.000 ¹⁾ |
| PK 9502.000 / PK 9503.000 | 74 | 45 | 12 | 9541.000 ¹⁾ |
| PK 9504.000 / PK 9505.000 | 74 | 74 | 12 | 9542.000 ¹⁾ |
| PK 9506.000 / PK 9507.000 | 90 | 90 | 12 | 9543.000 ¹⁾ |
| PK 9508.000 / PK 9509.000 | 110 | 74 | 12 | 9544.000 ¹⁾ |
| PK 9510.000 / PK 9511.000 | 110 | 110 | 10 | 9545.000 |
| PK 9512.000 / PK 9513.000 | 160 | 74 | 10 | 9546.000 |
| PK 9514.000 / PK 9515.000 PK 9516.000 | 150 | 90 | 10 | 9547.000 |
| PK 9517.000 / PK 9518.000 PK 9519.000 | 150 | 150 | 10 | 9548.000 |
| PK 9520.000 / PK 9521.000 PK 9522.000 | 220 | 150 | 8 | 9549.000 |
| PK 9523.000 / PK 9524.000 | 331 | 220 | 4 | 9550.000 |
| 1) | | | | |

¹⁾ with spacers



Mounting plate

for polycarbonate enclosures

- PK 9530.000
- PK 9531.000

Via a 3-way depth-adjustable assembly component, the mounting plate may also be used as an inner cover for installed equipment.

| For enclosure | Packs of | Model No. PK |
|---------------|----------|--------------|
| 9530.000 | 10 | 9551.000 |
| 9531.000 | 10 | 9552.000 |

Material:

Polycarbonate

Supply includes:

Assembly parts.



Hinges

For hinged attachment of lids. The supplied drilling template ensures problem-free assembly.

Supply includes:

- 1 set =
- 2 hinges,
- 4 assembly screws,
- 3 polyethylene sealing bungs,
- 1 drilling template.

| For enclosure | Material | Packs of | Model No. PK |
|---------------------------|---------------|----------|--------------|
| PK 9500.000 – PK 9513.000 | Polycarbonate | 10 sets | 9580.000 |
| PK 9514.000 - PK 9524.000 | Polystyrene | 10 sets | 9581.000 |





External mounting bracket

To fit enclosure

• PK 9530.000

• PK 9531.000 With moulded lug for cable tie.

Material

| Polyamide |
|-----------|

| Packs of | Model No. PK |
|----------|--------------|
| 10 | 9553.000 |

Supply includes: Assembly parts.

Rittal Small Enclosures

Accessories



Wall mounting brackets

The enclosure can be screwed to the wall using four wall mounting brackets. The bracket is securely attached to the enclosure by means of pins.

Material:


Polyamide, grey

| | Packs of | Model No. PK |
|--------------------|----------|--------------|
| For all enclosures | 40 | 9583.000 |

Supply includes:

1 pack


The assembly screw is located in the wall mounting bracket, making it accessible at all times. The wall mounting bracket may be fitted to the side or top.



Wall attachment can also be made directly without the bracket:

Variant 1

Wall attachment in the cover screw channel is a simple, secure means of attachment.



Variant 2

By knocking out the hole in the enclosure base, mounting in the enclosure interior is also possible.

The screws must be concealed using the sealing bungs supplied with the enclosure. The spacing between the attachment holes is marked on the rear panel of the enclosure.



Support rail

The two support rail sections provide good flexibility for accommodating terminal blocks and installed components.

Design.

The support rails are designed in accordance with EN 50 045 (TS 15/5.5) or EN 50 022 (TS 35/7.5); the surface finish is zinc-plated.



Supply includes:

Two self-tapping assembly screws.

| Rail | with the following terminal sizes | | | Bar length | Packs of | Model No. PK |
|-----------|-----------------------------------|-------------------|--------------------|------------|----------|--------------|
| | 2.5 mm ² | 4 mm ² | 10 mm ² | mm | | |
| TS 15/5.5 | 5 | 5 | 4 | 49.5 | 12 | 9560.000 |
| | 11 | 11 | 8 | 80 | 12 | 9561.000 |
| | 14 | 14 | 10 | 92 | 12 | 9562.000 |
| | 18 | 18 | 13 | 111 | 12 | 9563.000 |
| TS 35/7.5 | 12 | 9 | 5 | 81 | 12 | 9564.000 |
| | 17 | 13 | 8 | 106 | 12 | 9565.000 |
| | 24 | 20 | 11 | 144 | 12 | 9566.000 |
| | 38 | 32 | 19 | 216 | 12 | 9567.000 |
| | 61 | 50 | 30 | 336 | 12 | 9568.000 |

Calculation of the maximum number of terminals is based on two end holders and a cover.