

Part no. Article no. PLSM-C25/3N-MW 242545



## Similar to illustration

| echnical data for design verification  |                   |    |   |
|--|-------------------|----|---|
| Rated operational current for specified heat dissipation   | In                | А  | 25  |
| Heat dissipation per pole, current-dependent   | P <sub>vid</sub>  | W  | 0   |
| Equipment heat dissipation, current-dependent  | P <sub>vid</sub>  | W  | 9.7   |
| Static heat dissipation, non-current-dependent   | P <sub>vs</sub>   | W  | 0   |
| Heat dissipation capacity  | P <sub>diss</sub> | W  | 0   |
| Operating ambient temperature min.   |                   | °C | -25   |
| Operating ambient temperature max.   |                   | °C | 75  |
|  |                   |    | linear, per +1 °C, results in a 0.5% reduction of current carrying capacity   |
| C/EN 61439 design verification   |                   |    |   |
| 10.2 Strength of materials and parts   |                   |    |   |
| 10.2.2 Corrosion resistance  |                   |    | Meets the product standard's requirements.  |
| 10.2.3.1 Verification of thermal stability of enclosures   |                   |    | Meets the product standard's requirements.  |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat   |                   |    | Meets the product standard's requirements.  |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |                   |    | Meets the product standard's requirements.  |
| 10.2.4 Resistance to ultra-violet (UV) radiation   |                   |    | Meets the product standard's requirements.  |
| 10.2.5 Lifting   |                   |    | Does not apply, since the entire switchgear needs to be evaluated.  |
| 10.2.6 Mechanical impact   |                   |    | Does not apply, since the entire switchgear needs to be evaluated.  |
| 10.2.7 Inscriptions  |                   |    | Meets the product standard's requirements.  |
| 10.3 Degree of protection of ASSEMBLIES  |                   |    | Does not apply, since the entire switchgear needs to be evaluated.  |
| 10.4 Clearances and creepage distances   |                   |    | Meets the product standard's requirements.  |
| 10.5 Protection against electric shock   |                   |    | Does not apply, since the entire switchgear needs to be evaluated.  |
| 10.6 Incorporation of switching devices and components   |                   |    | Does not apply, since the entire switchgear needs to be evaluated.  |
| 10.7 Internal electrical circuits and connections  |                   |    | Is the panel builder's responsibility.  |
| 10.8 Connections for external conductors   |                   |    | Is the panel builder's responsibility.  |
| 10.9 Insulation properties   |                   |    |   |
| 10.9.2 Power-frequency electric strength   |                   |    | Is the panel builder's responsibility.  |
| 10.9.3 Impulse withstand voltage   |                   |    | Is the panel builder's responsibility.  |
| 10.9.4 Testing of enclosures made of insulating material   |                   |    | Is the panel builder's responsibility.  |
| 10.10 Temperature rise   |                   |    | The panel builder is responsible for the temperature rise calculation. Eaton wil provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating   |                   |    | Is the panel builder's responsibility. The specifications for the switchgear must observed.                                     |
| 10.12 Electromagnetic compatibility  |                   |    | Is the panel builder's responsibility. The specifications for the switchgear mus observed.                                      |
| 10.13 Mechanical function  |                   |    | The device meets the requirements, provided the information in the instruction<br>leaflet (IL) is observed.                     |

## **Technical data ETIM 6.0**

Circuit breakers and fuses (EG000020) / Miniature circuit breaker (MCB) (EC000042)

| Electric engineering, automation, process control engineering / Electrical installati<br>[AAB905011]) | on, device / Miniature o | circuit breaker system (MCB) / Miniature circuit breaker (MCB) (ecl@ss8.1-27-14-19-01 |
|---|--------------------------|---|
| Release characteristic  |                          | C   |
| Number of poles (total)   |                          | 4   |
| Number of protected poles   |                          | 4   |
| Nominal rated current   | А                        | 25  |
| Nominal rated voltage   | V                        | 400   |
| Rated short-circuit breaking capacity Icn EN 60898 at 230 V   | kA                       | 10  |

| Rated short-circuit breaking capacity Icn EN 60898 at 400 V    | kA | 10      |
|--|----|---------|
| Rated short-circuit breaking capacity Icu IEC 60947-2 at 230 V | kA | 0       |
| Rated short-circuit breaking capacity Icu IEC 60947-2 at 400 V | kA | 0       |
| Voltage type   |    | AC      |
| Current limiting class   |    | 3       |
| Frequency  | Hz | 50 - 60 |
| Concurrently switching N-neutral                               |    | Yes     |
| Suitable for flush-mounted installation                        |    | No      |
| Over voltage category  |    | 3       |
| Pollution degree   |    | 2       |
| Width in number of modular spacings                            |    | 4       |
| Built-in depth   | mm | 70.5    |
| Additional equipment possible                                  |    | Yes     |
| Degree of protection (IP)                                      |    | IP20    |
|  |    |         |