



RoHS

MODEL 721X-XXX SHOWN







FEATURES / BENEFITS

- Field adjustable set point ranges from 0.03" H₂O to 25 psi
- High resolution / high accuracy field adjustment mechanism
- Many standard ports and mounting options
- Custom design and engineering available
- Miniature size, lightweight, low cost
- · Dependable long life (20+ million cycles)
- Gold contact points
- PCB terminals available



SPECIFICATIONS

MECHANICAL				
RALCHARICAL				

Standard Tolerance	Varies by option — see Set Point Options overleaf
Switch Type	SPST (single pole / single throw) normally open normally closed option — contact us
Switching Medium	Air; compatible fluids on "High" port side
Mechanical Life	More than 20 million cycles
Maximum Operating Pressure	Varies by option — see Set Point Options overleaf
Operating Temp.	+40°F to +150°F (standard) -46°F to +205°F (contact us) +50° - 86°F (700 range)

PHYSICAL

Case Material	Polycarbonate (optional: Lexan 141, Ryton, Ultem®, Noryl®)
Porting Options	Many standard ports — see Low Port / High Port Options overleaf
Diaphragm Material	Polyurethane / Teflon® (other material options available)
Contact Points	Gold
Electrical Connections	Terminals – .187"x.020" spade (recessed) for use with quick disconnects uninsulated (ref. AMP Faston, #8-640917-1, 187 Series) (PCB terminals available)
Mounting	#4 Screws through mounting lugs; #2 Screws through eyelets; mounting clip available
Weight	Less than 10 grams

ELECTRICAL

Current Rating	40mA resistive for life in excess of 20 million cycles				
Operating Voltage	AC/DC - 30V or less with resistive load; 120 VAC neon lamp load				

Note: For higher load capabilities see our PSF103, PSF109 and Goldtech series switches.

World Magnetics' exclusive DesignFlex[™] feature allows you to quickly custom design a proven pressure, vacuum or differential switch for your application. Choose from our standard PSF102 options as shown or contact our vertically integrated in-house design and engineering team for special features.

SET POINT	OPTIONS							
	700	710	711	712	713	723	714	
In. H ₂ 0	0.03 to 0.1	0.1 to 0.5	0.5 to 2.0	2.0 to 15.0	15.0 to 60.0	60.0 to 100.0	100.0 to 692.0	
mbar	0.07 to 0.25	0.25 to 1.25	1.25 to 4.98	4.98 to 37.36	37.36 to 149.5	149.5 to 249.0	249.0 to 1723.5	
psi	0.001 to 0.004	0.004 to 0.018	0.018 to 0.072	0.072 to 0.542	0.542 to 2.17	2.17 to 3.61	3.61 to 25.0	
Maximum Operating Pressure	2psi	4psi	8psi	8psi	15psi	30psi	30psi	
Tolerance	+/- 0.03" H20	+/- 0.1" H ₂ 0	+/- 0.2" H ₂ 0	+/- 0.5" H ₂ 0	+/- 10%	+/- 10%	+/- 10%	
Diaphragm Material	PUR only	Teflon only	PUR or Teflon	PUR or Teflon	PUR or Teflon	PUR or Teflon	PUR or Teflon	
LOW PORT O	PTIONS			HIGH	PORT OPTI	ONS		
1	2		1	0	2	3		
Smooth Port .156" diar for 1/8" ID tubing w/mt		h Port .156" diameter D tubing w/o mtg. lugs	Smooth Port .19 for 1/8" ID		Smooth Port .187" diam for 5/32" ID tubing		Port .250" diameter 7/32" ID tubing	
3	4				4	5		
No Port (.060" vent hole) w/mtç	g. lugs (.060" ve	No Port ent hole) w/o mtg. lugs	- 1	6330	1/8" NPT Port	for	Barbed Port 3/16" ID tubing	
5	6			ine (standard)	6	7		
Barbed Port for 3/16" ID tubing w/mi	tg. lugs for 3/16"	Barbed Port ID tubing w/o mtg. lugs	2 Teflon (option	onal)	No Port (.060" vent hole)		r-Thru Barbed Port r 1/8" ID tubing	
7	8		8	0	9	0		
Barbed Port for 1/8" ID tubing w/mtg	g. lugs for 1/8" l	Barbed Port D tubing w/o mtg. lugs		Barbed Port 1/4" Port for 1/8" ID tubing for Quick Connect Fittin		ng	M8 x 1.25 Port	
Model	PSF102	Series Low Port	Low Port High Port Diaphragm Three Digit Set Point Option Number				on Number	

Model Design Guide PSF102 Seri Number Low Port Option Number High Port Option Number Diaphragm Option Number