



Technical details

Approvals:	CE;cULus Listed;TÜV;CCC
Application options:	Safety gate monitor;Instantaneous E-STOP monitoring;Limit switch;Delayed E-STOP monitoring
Operating modes:	Single-channel;Automatic reset;Dual-channel;Detection of shorts across contacts;Monitored manual reset
Product standard:	EN 60947-5-1
Standards:	EN 60204-1;EN 62061;EN ISO 13849-1;VDE 0113-1
Supply voltage (V):	24,0
Supply voltage type:	DC
Terminal style:	fixed
Terminal type:	Screw terminal
Number of instantaneous safety contacts:	2
Number of delayed safety contacts:	2
Safety contact delay type:	Delay-on de-energisation
Selectable times:	0,10 s;0,50 s;1,00 s;10,00 s;15,00 s;2,00 s;20,00 s;25,00 s;30,00 s;4,00 s;6,00 s;8,00 s
Stop category:	0/1
Max. current at DC13 I (6 cycles/min):	7.0 A
Max. current at AC15:	5.0 A
Width dimension:	45.0 mm
Height dimension:	87.0 mm
Depth dimension:	121.0 mm

Gross weight:	355 g
Net weight:	345 g
Ambient temperature:	-10 - 55 °C