

The versatile high-current PSF109S vacuum switch offers a wide-range field adjustable set point; snap action; and choice of standard vacuum port design options. For custom applications, our in-house design and engineering team provides rapid prototyping and manufacturing turnaround.

FEATURES / BENEFITS

- Field adjustable vacuum set point ranges, from -3" H₂O to -12 psi
- Snap action basic switch, up to 25A*, 125/250 VAC
 *Not available on all ranges
- .250" diameter; 1/8" NPT; or 1/4" Quick Connect Fitting port
- Custom design and engineering available
- Small size, lightweight, low cost
- Dependable long life (10+ million cycles)



SPECIFICATIONS

MECHANICAL		
Standard Tolerance	±20% (Tighter tolerances available)	
Switch Type	SPDT normally open or normally closed	
Switching Medium	Air; compatible fluids	
Mechanical Life	More than 10 million cycles	
Operating Temp.	+40°F to +150°F (standard) -46°F to +205°F (contact us)	
PHYSICAL		
Case Material	Polycarbonate (optional: Lexan 141, Ryton, Ultem®, Noryl®)	
Vacuum Port Options	.250" diameter, 1/8" NPT, Quick Connect Fitting Port	
Diaphragm Material	Polyurethane / Teflon® (other material options available)	
Contact Points	Silver (Gold available on special order)	
Electrical Connections	Terminals – .187"x.020" tab-type for use with quick disconnects (ref. AMP #2-520182-2 or equivalent) .250" available — contact us	
Mounting	#2 Screws through eyelets	
Weight	Less than 20 grams	
ELECTRICAL		
Current Rating	Varies by option — see Adjustable Vacuum Set Point Options overleaf	
Operating Voltage	125/250 VAC— see Adjustable Vacuum Set Point Options (overleaf)	


ADJUSTABLE VACUUM SET POINT / PORT / ELECTRIC RATING OPTIONS

	20161	20112	20623
Description	109S-3-8	109S-9-80	109S-81-330
- In. Hg	0.2205 to 0.5885	0.6613 to 5.878	5.951 to 24.25
- In. H ₂ 0	3 to 8	9 to 80	81 to 330
- mbar	7.5 to 20	22 to 199	202 to 822
- psi	0.1 to 0.30	0.30 to 2.90	2.9 to 11.9
Port Style (see drawing below)	A	А	A
Electrical 125/250VAC Resisitive Load	3A	10A	15A
	20901	20890	20897
Description	109S-NPT-3-8	109S-NPT-9-80	109S-NPT-81-330
- In. Hg	0.2205 to 5885	0.6613 to 5.878	5.951 to 24.25
- In. H ₂ 0	3 to 8	9 to 80	81 to 330
- mbar	7.5 to 20	22 to 199	202 to 822
- psi	0.10 to 0.30	0.30 to 2.90	2.9 to 11.9
Port Style (see drawing below)	В	В	В
Electrical 125/250VAC Resisitive Load	3A	10A	15A
	21472	21473	21474
Description	109S-QC-3-8	109S-QC-9-80	109S-QC-81-330
- In. Hg	0.2205 to 5885	0.6613 to 5.878	5.951 to 24.25
- In. H ₂ 0	3 to 8	9 to 80	81 to 330
- mbar	7.5 to 20	22 to 199	202 to 822
- psi	0.10 to 0.30	0.30 to 2.90	2.9 to 11.9
Port Style (see drawing below)	C	С	С
Electrical 125/250VAC Resisitive Load	3A	10A	15A

SAMPLE SWITCH available by request – Call 1-800-643-3884

PORT STYLE A

Ø 0.25 STEPPED AXIAL PORT



PORT STYLE B

0.29 [7.3] 0.69 [17.6] 0.44 HEX 1/8-27 NPT ADJUSTMENT SCREW IN PORT

PORT STYLE C

JOHN GUEST (QUICK DISCONNECT)

