# Technical Datasheet



# 3M<sup>™</sup> SecureFit<sup>™</sup> SF200 Series Protective Eyewear

## **Product Description**

The 3M<sup>TM</sup> SecureFit<sup>TM</sup> series is comprised of a rimless lens and fixed-length temple arm. An integrated side-shield is included for added protection. Temples also feature 3M Pressure Diffusion Temple Technology which helps diffuse pressure over the ear to enhance frame comfort across a diverse workforce. This innovative design promotes improved comfort and security of fit.

### **Product Range**

SF201AF-EU PC 3M™ SecureFit™ CLEAR AS/AF SF202AF-EU PC 3M™ SecureFit™ GREY AS/AF SF203AF-EU PC 3M™ SecureFit™ AMBER AS/AF SF201AS-EU PC 3M™ SecureFit™ CLEAR AS

#### Intended Use

These products are intended for protection against high speed particles at low energy (F) at extreme temperature conditions, -5°C and +55°C, (T) in accordance with EN166:2001. They also protect against UV radiation in accordance with EN170:2002, and sun glare in accordance with EN172:1994 (grey lens only).

A number of lens options are available for a variety of different applications

- Clear Good colour recognition and excellent UV protection
- Grey Protection from sunglare
- Amber Enhanced contrast in low light conditions

## **Key Features**

- Optical class 1 lens suitable for prolonged use
- · Design provides excellent coverage and good field of vision
- Offers excellent protection against Ultraviolet (UV) radiation
- Lightweight design (18g)
- 3M Pressure Diffusion Temple Technology for secure and comfortable fit
- · Self-adjusts to comfortably fit a wide range of head sizes

### **Applications**

These products can be used in a wide range of applications including:

- Construction
- Engineering
- · General assembly
- Inspection work
- · Light duty maintenance and repair

#### **Use Limitation**

- Never modify or alter this product
- Do not use this product against hazards other than those specified in this document.
- These products are not suitable for grinding or welding
- These products are NOT designed to be worn over prescription spectacles.
- In accordance with EN166:2001 safety spectacles cannot be tested and approved for use against liquid droplets. Where liquid protection is specified a suitable product should be considered, for example safety goggles.



## Standards and Approval

This protective eyewear has been shown to meet the basic safety requirements under Article 10 of the European Community Directive 89/686/EEC and is thus CE marked.

These products have been examined at the design stage by ECS GmbH - European Certification Service, Huettfeldstrasse 50, 73430 Aalen, Germany (Notified Body number 1883).

These products are tested and CE approved against EN166:2001.

## **Materials Listing**

Component	Material
Lens	Polycarbonate
Temple Arm	Xylex
Temple Pin	Zinc plated steel
Total Weight	18g

## **Important Notice**

3M does not accept liability of any kind, be it direct or consequential (including, but not limited to, loss of profits, business and/or goodwill) arising from reliance upon any information herein provided by 3M. The user is responsible for determining the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence.

## **Marking**

The products have demonstrated compliance with the requirements of EN 166:2001 and associated standards and bear the following marks:

Clear lens	2C-1.2 3M 1 FT
Amber lens	2C-1.2 3M 1 FT
Grey lens	5-3.1 3M 1 FT
Frames (all variants)	3M EN166 FT CE SF200 Series

## **Explanation of Marking**

Marking	Description
<b>2C-1.2</b> (EN 170:2002)	UV protection with good colour recognition. This product conforms to the requirements of the standard, providing UV protection for the complete specified range (210nm – 365nm).
<b>5-3.1</b> (EN 172:1994 (as amended))	Sun-glare protection conforming to the requirements of the standard, providing UV protection for the complete specified range (280nm – 350nm).
1	Optical class
F	Impact protection against high speed particle at low energy (45m/s)
Т	Tested for impact protection at extreme temperature conditions -5°C and +55°C



Personal Safety Division EMEA Region

3M Centre, Cain Road, Bracknell Berkshire RG12 8HT United Kingdom Tel: +44 (0) 1344 858000 www.3M.eu/safety