Elmasonic S 30 (H)

Ultrasonic cleaning unit

EMA

| Elma Order Nos. | |
|--------------------------------|----------|
| Elmasonic S 30 (220-240 V) | 100 4631 |
| Elmasonic S 30 (115-120 V) | 100 7140 |
| Elmasonic S 30 H (220-240 V) | 100 1955 |
| Elmasonic S 30 H (115-120 V) | 100 7141 |
| Basket stainless steel | 100 4176 |
| Cover (plastic) | 100 3281 |
| Further accessories on request | |



The new Elmasonic S units are available in 16 different sizes ranging from 0.5 litres to 90 litres. State-of-the art microprocessor controlled ultrasonic cleaning and sweep technology. The user-friendly LED-display ensures an excellent operation.

Further advantages:

- high-performance 37 kHz sandwich transducer systems
- cleaning tank made of cavitation-resistant stainless steel
- user-friendly and clear operating panel, splash water proof
- LED-Display showing set and remaining time of cleaning period
- Turning knob for setting continued and short-period operation from 1 to 30 min
- temperature-controlled ultrasonic operation (applies only for units with heating)
- sweep function for an optimised sound field distribution in the cleaning liquid by frequency modulation
- degas function for the efficient degassing of the cleaning liquid and for laboratory purposes
- auto degas function for automatic degassing cycles, i.e. with fresh cleaning liquids
- dry-run protected heating (applies only for units with heating)
- LED-Display for pre-set and actual temperature (applies only for units with heating)
- plug-in mains supply (S 10 S 300H)
- ergonomically shaped plastic handles
- Turning knob for tank drainage at side of unit for simple get effective draining of tank

Technical data

| Mains voltage (Vac) | 115-120 V/220-240 V | Max. filling volume tank (lit. / gal |
|---|---------------------|--------------------------------------|
| Mains frequency (Hz) | 50 / 60 | Weight (kg) |
| Ultrasonic frequency (kHz) | 37 | Material tank |
| Power consumption total S 30 H (W) | 280 | Material casing |
| Ultrasonic power effective (W) | 80 | Drain |
| Ultrasonic peak performance max.**(W) | 320 | Carrying handles (plastic) |
| Heating power (units w. heating) (W) | 200 | CE-compliant |
| Unit outer dimensions W / D / H (mm) | 300 / 179 / 214 | Protection class |
| Tank internal dimensions W / D / H (mm) | 240 / 137 / 100 | |

| Max. filling volume tank (lit. / gal.) | 2.75 / 0.73 |
|--|-----------------|
| Weight (kg) | 3,3 |
| Material tank | stainless steel |
| Material casing | stainless steel |
| Drain | 3/8" |
| Carrying handles (plastic) | \checkmark |
| CE-compliant | \checkmark |
| Protection class | IP 20 |

** S 10 – S 15 H: impulse wave form; S 30 – S 900 H: standard sine-wave modulation

The choice of the waveform has been matched to the relevant tank size. The signal form of the wave results Sin a factor 4 or 8 for the ultrasonic peak max., depending on the modulation of the wave.