

plastic tubing PUN-H-10X1,5-TGN

Part number: 8048707

FESTO

Approved for use in food processing (hydrolysis resistant)
This product is not suitable for CN and PK push-in fittings.



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	52 mm
Inside diameter	7 mm
Min. bending radius	28 mm
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Tubing test conditions	Suitable for energy chains: > 5 million cycles to FN 942021
Temperature dependent operating pressure	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-:] Water as per manufacturer's declaration at www.festo.com
Material fire test	UL94 HB
Ambient temperature	-35 ... 60 °C
Product weight according to length	0.0465 kg/m
Pneumatic connection	For push-in connector outside diameter 10 mm
Colour	Translucent green
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Material tubing	TPE-U(PU)