



Model Number

UB120-12GM-E5-V1


Single head system

Features

- · Extremely narrow projection cone
- · Switch output
- · Very small unusable area
- 5 different output functions can be set
- · Short response time

Diagrams

Characteristic response curve



Curve 1: flat surface 10 mm x 10 mm Curve 2: round bar, Ø 8 mm

Technical data General specifications 15 ... 120 mm Sensing range Adjustment range 20 ... 120 mm Dead band 0 ... 15 mm Standard target plate 10 mm x 10 mm Transducer frequency approx. 850 kHz Response delay approx. 9 ms Indicators/operating means LED yellow indication of the switching state flashing: program function object detected LED red solid red: Error red, flashing: program function, object not detected **Electrical specifications** Operating voltage U_B 10 ... 30 V DC , ripple 10 $\%_{SS}$ No-load supply current I₀ \leq 30 mA Input 1 program input Input type operating distance 1: -U $_{B} \ldots$ +1 V, operating distance 2: +6 V ... +U_B input impedance: > 4,7 kΩ program pulse: ≥ 1 s Output 1 switch output PNP Normally open/closed , programmable Output type Rated operating current I_e 100 mA , short-circuit/overload protected Default setting Switch point A1: 20 mm Switch point A2: 120 mm Voltage drop U_d ≤3 V Repeat accuracy ≤1 % ≤ 52 Hz Switching frequency f Range hysteresis H 1 % of the set operating distance Temperature influence ± 1.5 % of full-scale value **Ambient conditions** Ambient temperature -25 ... 70 °C (-13 ... 158 °F) -40 ... 85 °C (-40 ... 185 °F) Storage temperature Mechanical specifications Connection type Connector M12 x 1, 4-pin Degree of protection Material Housing brass, nickel-plated Transducer epoxy resin/hollow glass sphere mixture; foam polyurethane, cover PBT

Compliance with standards and

Standard conformity

Standards EN 60947-5-2:2007+A1:2012


IEC 60947-5-2:2007 + A1:2012

Approvals and certificates

UL approval cULus Listed, Class 2 Power Source


CCC approval CCCC

Dimensions



Additional Information

Programmable output modes




5. A1 -> ∞ , A2 -> ∞ : Object presence detection mode Object detected: Switch output closed No object detected: Switch output open

Electrical Connection

Standard symbol/Connections: (version E5, pnp)





Core colours in accordance with EN 60947-5-2.

Pinout



Wire colors in accordance with EN 60947-5-2

1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)

2

Accessories

UB-PROG2

Programming unit

BF 5-30

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm

BF 12

Mounting flange, 12 mm

BF 12-F

Mounting flange with dead stop, 12 mm

V1-G-2M-PVC

Female cordset, M12, 4-pin, PVC cable

V1-W-2M-PUR

Female cordset, M12, 4-pin, PUR cable

UVW90-M12

Ultrasonic -deflector

Adjusting the switching points

The ultrasonic sensor features a switch output with two teachable switching points. These are set by applying the supply voltage $-U_B$ or $+U_B$ to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. Switching point A1 is taught with $-U_B$, A2 with $+U_B$.

Five different output functions can be set

- 1. Window mode, normally-open function
- 2. Window mode, normally-closed function
- 3. one switching point, normally-open function
- 4. one switching point, normally-closed function
- 5. Detection of object presence

TEACH-IN window mode, normally-open function

- Set target to near switching point
- TEACH-IN switching point A1 with -UB
- Set target to far switching point
- TEACH-IN switching point A2 with +UB

TEACH-IN window mode, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A2 with +UB
- Set target to far switching point
- TEACH-IN switching point A1 with -U_B

TEACH-IN switching point, normally-open function

- Set target to near switching point
- TEACH-IN switching point A2 with +U_B
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UB

TEACH-IN switching point, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A1 with -UB
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A2 with +UB

TEACH-IN detection of objects presence

- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UB
- TEACH-IN switching point A2 with +UB

LED Displays

188174_eng.xml

Date of issue: 2017-07-12

Release date: 2017-07-12 08:57

Displays in dependence on operating mode		Red LED	Yellow LED
TEACH-IN switching point:			
C	Object detected	off	flashes
Ν	No object detected	flashes	off
C	Object uncertain (TEACH-IN invalid)	On	off
Normal operation		off	Switching state
F	-ault	on	Previous state

Installation conditions

If the sensor is installed at places, where the environment temperature can fall below 0 °C, for the sensors fixation, one of the mounting flanges BF 12, BF 12-F or BF 5-30 must be used. In case of direct mounting of the sensor in a through hole, it has to be fixed at the middle of the housing thread.