





Model Number

UB120-12GM-U-V1


Single head system

Features

- · Extremely narrow projection cone
- Analog output 0 ... 10 V
- Very small unusable area
- Measuring window adjustable
- Short response time

Diagrams

Characteristic response curve



Curve 1: flat surface 10 mm x 10 mm Curve 2: round bar, Ø 8 mm

Technical data	
General specifications	
Sensing range	15 120 mm
Adjustment range	20 120 mm
Dead band	0 15 mm
Standard target plate	10 mm x 10 mm
Transducer frequency	approx. 850 kHz
Response delay	approx. 27 ms
Indicators/operating means	
LED yellow	solid yellow: object in the evaluation range yellow, flashing: program function, object detected
LED red	solid red: Error red, flashing: program function, object not detected
Electrical specifications	
Operating voltage U _B	15 30 V DC , ripple 10 % _{SS}
No-load supply current I ₀	≤ 30 mA
Input	
Input type	1 program input lower evaluation limit A1: $-U_B +1 V$, upper evaluation limit A2: $+4 V +U_B$ input impedance: $> 4.7 k\Omega$, pulse duration: $\ge 1 s$
Output	
Output type	1 analog output 0 10 V
Resolution	0.17 mm
Deviation of the characteristic curve	± 1 % of full-scale value
Repeat accuracy	± 0.5 % of full-scale value
Load impedance	> 1 kOhm
Temperature influence	± 1.5 % of full-scale value
Ambient conditions	
Ambient temperature	-25 70 °C (-13 158 °F)
Storage temperature	-40 85 °C (-40 185 °F)
Mechanical specifications	
Connection type	Connector M12 x 1 , 4-pin
Degree of protection	IP67

Material brass, nickel-plated Housing

epoxyresin/hollow glass sphere mixture; foam polyurethane, cover PBT Transducer

25 g Mass Compliance with standards and

directives

Standard conformity Standards


EN 60947-5-2:2007+A1:2012 IEC 60947-5-2:2007 + A1:2012 EN 60947-5-7:2003 IEC 60947-5-7:2003

Approvals and certificates

UL approval cULus Listed, Class 2 Power Source


CCC approval CCC approval / marking not required for products rated ≤36 V

Dimensions




Additional Information

Programming the analog output mode



Electrical Connection

Standard symbol/Connections: (version U)



Core colors in accordance with EN 60947-5-2.

Pinout



Wire colors in accordance with EN 60947-5-2

1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)

FPEPPERL+FUCHS

Accessories

UB-PROG2

Programming unit

BF 5-30

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm

BF 12

Mounting flange, 12 mm

BF 12-F

Mounting flange with dead stop, 12 mm

V1-G-2M-PVC

Female cordset, M12, 4-pin, PVC cable

V1-W-2M-PUR

Female cordset, M12, 4-pin, PUR cable

UVW90-M12

Ultrasonic -deflector

Adjusting the evaluation limits

The ultrasonic sensor features an analogue output with two teachable evaluation limits. These are set by applying the supply voltage $-U_B$ or $+U_B$ to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. The lower evaluation limit A1 is taught with $-U_B$, A2 with $+U_B$.

Two different output functions can be set:

- 1. Analogue value increases with rising distance to object (rising ramp)
- 2. Analogue value falls with rising distance to object (falling ramp)

TEACH-IN rising ramp (A2 > A1)

- Position object at lower evaluation limit
- TEACH-IN lower limit A1 with UB
- Position object at upper evaluation limit
- TEACH-IN upper limit A2 with + UB

TEACH-IN falling ramp (A1 > A2):

- Position object at lower evaluation limit
- TEACH-IN lower limit A2 with + U_R
- Position object at upper evaluation limit
- TEACH-IN upper limit A1 with UR

Default setting

A1: unusable area

A2: nominal sensing range

Mode of operation: rising ramp

LED Displays

Displays in dependence on operating mode	Red LED	Yellow LED
TEACH-IN evaluation limit		
Object detected	off	flashes
No object detected	flashes	off
Object uncertain (TEACH-IN invalid)	on	off
Normal mode (evaluation range)	off	on
Fault	on	previous state

Installation conditions

If the sensor is installed at places, where the environment temperature can fall below 0 °C, for the sensors fixation, one of the mounting flanges BF 12, BF 12-F or BF 5-30 must be used. In case of direct mounting of the sensor in a through hole, it has to be fixed at the middle of the housing thread.

www.pepperl-fuchs.com