

Model Number

NBN4-F25-2Z4L-V1

Features

- Direct mounting on standard actuators
- Small construction with sturdy plastic housing of protection class IP 67
- 2-wire DC sensor with minimum offstate current
- M12 male connector

Accessories

BT32 Activator for F25 series BT33 Activator for F25 series BT34 Activator for F25 series BT32XAS Activator for F25 series BT43-RG-01 Activator for F25 series including protective housing and mounting plate

Technical Data	
General specifications	
Switching function	
Output type	
Rated operating distance	s _n
Installation	
Output polarity	
Assured operating distance	sa
Actual operating distance	s _r
Reduction factor r _{Al}	
Reduction factor r _{Cu}	
Reduction factor r ₃₀₄	
Reduction factor r _{St37}	
Output type	
Nominal ratings	
Operating voltage	UB
Switching frequency	f
Hysteresis	н
Reverse polarity protection	
Short-circuit protection	
Voltage drop	U _d
Design data	
Operating current Off-state current	IL .
Time delay before availability	l _r t _v
Switching state indicator	۰v
Ambient conditions	
Ambient temperature Storage temperature	
Mechanical specifications	
•	
Connection type	
Connector housing	
Housing material	
Sensing face	
Degree of protection Mass	
Tightening torque, fastening screws	
Note	
Compliance with standards and	
directives	
Standard conformity	

Approval	s and	certificate	es

UL approval CCC approval


Standards


Dimensions

	2 x normally open (NO)
	Two-wire
'n	4 mm
	flush mountable
	DC
a	0 3.24 mm
r	3.6 4.4 mm typ.
	0.6
	0.45
	1
	1.2
	2x 2-wire
J _B	5 30 V DC
U	0 500 Hz
1	typ. 5 %
	reverse polarity protected
	pulsing
Jd	≤ 4.5 V
	4 100 mA
	120 200 μA typ. 175 μA at 25 °C
v	≤ 100 ms
	LED, yellow
	-25 70 °C (-13 158 °F)
	-40 85 °C (-40 185 °F)
	Connector plug M12 x 1, 4-pin
	metal
	PBT
	PC
	IP67
	49 g
	M5 x 25 : 2.7 Nm
	Mounted on mechanical drive

EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012

cULus Listed CCC approval / marking not required for products rated ≤36 V





Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group USA: www.pepperl-fuchs.com fa-info@u

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com




1

F PEPPERL+FUCHS

NBN4-F25-2Z4L-V1

Electrical Connection



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group USA: + www.pepperl-fuchs.com fa-info@us

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



2