CE

**Features** 

parts

series

Visible red light

cULus approval

**Product information** 

•

٠

•

•

•

**Model Number** GL20-RT/32/40a/98a

Photoelectric slot sensor

with 3-pin, M8 x 1 connector

High switching frequency

Degree of protection IP67

Sturdy aluminum housing

Optimized for the detection of small

Multiple device installation possible,

switch as standard features of this

Photoelectric slot sensors offer vast installation benefits thanks to their housing design. When it comes to operation, these new generation devices boast features such as high

resolution, high repeatability, automatic signal threshold adjustment, ambient light resis-

tance, and detection of and/or light


transmission through transparent objects.

Cross-talk protection enables parallel installation of devices despite extremely high switching frequency. These characteristics


guarantee reliable detection of small parts, from 0.3 mm, across the entire detection range, even in very fast moving applications.

no mutual interference (no cross-talk) Sensitivity adjuster and light/dark

## **Dimensions**



## **Electrical connection**






Pinout





## Indicators/operating means



1	Functional display	red
2	Light-/dark switch	
3	Sensitivity adjuster	



Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Cable socket, M8, 3-pin, PUR cable

Other suitable accessories can be found at

Accessories V3-WM-2M-PUR

www.pepperl-fuchs.com

Technical data			
General specifications			
Light source		LED	
Light type		modulated visible red light	
Tests		EN 60947-5-2	
Target size		0.3 mm	
Slot width		20 mm	
Slot depth		17 mm	
Ambient light limit		100000 Lux	
Functional safety related para	ameters		
MTTF <sub>d</sub>		1290 a	
Mission Time (T <sub>M</sub> )		20 a	
Diagnostic Coverage (DC)		0 %	
Indicators/operating means			
Function indicator		LED red in connector	
Control elements		Sensitivity adjuster, light/dark switch	
Electrical specifications			
Operating voltage	U <sub>B</sub>	10 30 V DC, class 2	
Ripple	- D	10 %	
No-load supply current	I <sub>0</sub>	≤ 15 mA	
Output	0		
Switching type		light/dark on	
Signal output		1 PNP, short-circuit protected, open collector	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Repeat accuracy		0.05 mm	
Switching frequency	f	3 kHz	
Response time		≤ 160 μs	
Ambient conditions		· · · · ·	
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-20 75 °C (-4 167 °F)	
Mechanical specifications			
Degree of protection		IP67	
Connection		M8 connector, 3-pin	
Material			
Housing		black anodized aluminum	
Optical face		glass	
Mass		25 g	
		· •	
Approvals and certificates			
CE conformity		CE	
UL approval		cULus	
CCC approval		CCC approval / marking not required for products rated ≤36 V	

## **Operating principle**

Photoelectric slot sensors are photoelectric sensors that operate according to the thru-beam sensor principle. The transmitter sends signals directly to the receiver. If an object breaks the light beam, the switching element function is triggered. The special U-shaped design means the transmitter and receiver can be accommodated in one housing, which ensures high resistance to vibrations. In contrast to standard thru-beam sensors, photoelectric slot sensors have the added advantage of not requiring complex electrical installation, as only one device needs to be connected. Also, adjustment of the optical axes is not necessary.

2

