

# Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Configurable safety module (basic module), 8 safe inputs, 2 safe outputs, 2 reset inputs, 2 signal outputs, 4 clock outputs, can be extended via TBUS, up to SILCL 3, Cat. 4/PL e, SIL 3, plug-in Push-in terminal block, TBUS connector not included

## Product Description


The configurable and individually scalable PSRmodular safety system is a flexible safety solution for monitoring your machine or system. The freely configurable base module is used to monitor various pieces of safety equipment such as emergency stop, safety doors, and light grids. The base module has safe inputs and outputs, as well as signal outputs and clock outputs.

## Your advantages

- ✓ Economical safety solution with a high level of adaptability to individual requirements
- ✓ Fast startup, thanks to easy hardware and software configuration
- ✓ Machine downtime minimized with comprehensive, easy-to-understand diagnostics
- ✓ Flexible extension with safe inputs and outputs
- ✓ Possibility of connecting fieldbus gateways for bidirectional communication between the base module and the higher-level controller
- ✓ Narrow housing width of just 22.6 mm
- ✓ Tool-free and time-saving installation with Push-in technology
- ✓ Up to Cat. 4/PL e according to ISO 13849-1, SILCL 3 according to IEC 62061, SIL 3 according to IEC 61508
- ✓ Suitable for lift applications according to EN 81-20



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 967592
GTIN	4055626967592
Weight per Piece (excluding packing)	141.000 g
Custom tariff number	85371098
Country of origin	Italy
Sales Key	DNA361

## Technical data

### Dimensions

# Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

## Technical data

### Dimensions

Width	22.61 mm
Height	107.74 mm
Depth	113.6 mm

### Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C (observe derating)
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (non-condensing)
Max. permissible humidity (storage/transport)	95 % (non-condensing)
Maximum altitude	≤ 2000 m (Above sea level)

### Power supply

Designation	A1/A2
Rated control circuit supply voltage $U_s$	24 V DC -20 % / +20 % (external fuse, typically 4 A)
	19.2 V DC ... 28.8 V DC
Rated control supply current $I_s$	typ. 55 mA (Outputs inactive)
	typ. 70 mA (Outputs active, without load)
Current consumption	max. 4 A (with full load)
Power consumption at $U_s$	typ. 1.32 W (Outputs inactive)
Inrush current	9.5 A ( $\Delta t = 1$ ms at $U_s$ )
Filter time	typ. 5 ms (at A1 in the event of voltage dips at $U_s$ )
Protective circuit	Inverse-parallel protection against polarity reversal
	Suppressor diode

### Digital inputs

Input name	IN1, IN2, IN3, IN4, IN5, IN6, IN7, IN8
Description of the input	Safety-related digital inputs
	EN 61131-2 type 1
Number of inputs	8
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 28.8 V DC
Input current range "0" signal	< 1 mA
Current consumption	typ. 8 mA (typically with $U_s$ )
	max. 10 mA (at a control voltage of 28.8 V DC)
Filter time	min. 3 ms $\pm$ 2 ms (adjustable)
	max. 250 ms $\pm$ 2 ms (adjustable)
	Test pulse rate $\geq$ 2x set filter time, min. Test pulse rate = 10 ms
Max. permissible overall conductor resistance	max. 1.2 k $\Omega$ (Input and reset circuit at $U_s$ )
Cable length	max. 100 m (per input)
Protective circuit/component	Suppressor diode

### 2. Digital inputs

Input name	Reset inputs
------------	--------------

# Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

## Technical data

### 2. Digital inputs

	FBK1, FBK2
Description of the input	IEC 61131-2 type 3
	non-safety-related (configurable)
Number of inputs	2
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 28.8 V DC
Input current range "0" signal	< 1 mA
Current consumption	typ. 10 mA (typically with U <sub>S</sub> )
	max. 13 mA (at a control voltage of 28.8 V DC)
Filter time	250 ms ±2 ms (Test pulse rate > 500 ms)
Max. permissible overall conductor resistance	1.2 kΩ (Input and reset circuit at U <sub>S</sub> )
Cable length	max. 100 m (per input)
Protective circuit/component	Suppressor diode

### 3. Digital inputs

Input name	Enable inputs
	EN1, EN2
Number of inputs	2
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	8 V DC ... 28.8 V DC
Current consumption	typ. 0.7 mA (typically with U <sub>S</sub> )
	max. 1 mA (at a control voltage of 28.8 V DC)
Protective circuit/component	Suppressor diode

### Digital outputs

Output name	O1A, O1B, O2A, O2B
Output description	Safety-related digital outputs
	PNP, OSSD
	IEC 61131-2 type 0.5 (observe limiting continuous current)
Number of outputs	4 (can be used as 2 two-channel outputs)
Nominal output voltage	24 V DC (Supply via A1)
Nominal output voltage range	18 V DC ... 27.6 V DC (U <sub>S</sub> - 1.2 V)
Limiting continuous current	400 mA (per channel)
	1.6 A (Total current of all safe digital outputs)
Inrush current	max. 750 mA (Δt # 1 s)
Output voltage when switched off	< 1.5 V
Leakage current	max. 500 μA
Cable length	max. 100 m (per output)
Ohmic load	min. 50 Ω (Observe limiting continuous current)
Max. capacitive load	max. 680 nF
Max. inductive load	max. 1.4 mH

# Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

## Technical data

### Digital outputs

Switching frequency	max. $1/4 \times t_{\text{cycle}}$ [Hz]
Test pulses	< 80 $\mu\text{s}$ (Test pulse width of low test pulses)
	Test pulse rate for low test pulses > 2 x $T_{\text{Cycle}}$
	< 20 $\mu\text{s}$ (Test pulse width, high test pulse)
	$\geq 1.5$ s (Test pulse rate, high test pulse)
Protective circuit/component	Suppressor diode
Short-circuit protection	Yes (self-limitation at 1.1 A)
Error detection time at 1-channel structure	< 3.5 s (OFF state)
	< 4 x $t_{\text{cycle}}$ [ms] (ON state)
Discharging circuit	Yes, internal

### Alarm outputs

Designation	MO1, MO2
Output description	PNP, IEC 61131-2 Typ 0,1
	non-safety-related
Number of outputs	2
Voltage	24 V DC (via A1)
Output voltage range	18.2 V DC ... 27.8 V DC ( $U_S - 1$ V)
Output voltage when switched off	max. 0.1 V
Maximum inrush current	1.1 A ( $\Delta t = 3$ s at $U_S$ )
Switching frequency	max. $1/4 \times t_{\text{cycle}}$ [Hz]
Limiting continuous current	100 mA (per channel)
	200 mA (Total current of all digital signal outputs)
Leakage current	max. 100 $\mu\text{A}$
Protective circuit/component	Suppressor diode
Short-circuit protection	Yes (self-limitation at 1.1 A)
Cable length	max. 100 m (per output)

### Clock outputs

Designation	T1, T2, T3, T4
Output description	PNP, IEC 61131-2 type 0.5
Number of outputs	4
Voltage	24 V DC (via A1)
Nominal voltage range	18.2 V DC ... 27.8 V DC ( $U_S - 1$ V)
Output voltage when switched off	max. 0.1 V
Maximum inrush current	1.1 A ( $\Delta t = 3$ s at $U_S$ )
Limiting continuous current	100 mA (per channel)
	400 mA (Total current of all outputs)
Leakage current	max. 100 $\mu\text{A}$
Cable length	max. 100 m (per output)
Max. capacitive load	max. 470 nF

# Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

## Technical data

### Clock outputs

Max. inductive load	max. 2.4 mH
Test pulses	≤ 220 μs (Test pulse duration)
	Test pulse rate = 8 x t <sub>cycle</sub> [ms]
Protective circuit/component	Suppressor diode
Short-circuit protection	Yes (self-limitation at 1.1 A)
Discharging circuit	Yes, internal

### Times

Response time	see user manual
Restart time	min. 5 s (Boot time)
	max. 10 s (Boot time)
Cycle time	see user manual

### General

Nominal operating mode	100% operating factor
Net weight	141 g
Mounting position	vertical or horizontal
Mounting type	DIN rail mounting
Assembly instructions	Observe derating
Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Protection class	III (EN 50178)
Housing material	Polyamide PA non-reinforced
Housing color	yellow
Operating voltage display	1 x green LED
Status display	1 x LED (green), 1 x LED (orange), 1 x LED (blue)
	2 x LED (green, red)
	12 x LED (yellow)
Indication	2 x LED (red)

### Connection data

Connection method	Push-in connection
pluggable	Yes
Conductor cross section solid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16
Stripping length	10 mm

### Safety-related characteristic data

Stop category	0
Designation	IEC 61508 - High-demand for 2-channel wiring
Safety Integrity Level (SIL)	3
Designation	IEC 61508 - High-demand for 1-channel wiring

# Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

## Technical data

### Safety-related characteristic data

Safety Integrity Level (SIL)	2
Designation	EN ISO 13849
Performance level (PL)	e (2-channel wiring)
	d (1-channel wiring)
Designation	EN 62061
Safety Integrity Level Claim Limit (SIL CL)	3 (2-channel wiring)
	2 (1-channel wiring)

### Standards and Regulations


Designation	Air clearances and creepage distances between the power circuits
Standards/regulations	EN 50178
Rated insulation voltage	250 V AC
Rated surge voltage/insulation	Basic insulation 4 kV between all current paths and housing
Degree of pollution	2
Overvoltage category	II
Shock	10g for $\Delta t = 16$ ms (continuous shock, 1000 shocks in each space direction)
Vibration (operation)	10 Hz ... 150 Hz, 2g
Conformance	CE-compliant

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


## Drawings

Application drawing



# Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

Block diagram



## Classifications

### eCl@ss

eCl@ss 10.0.1	27371819
eCl@ss 11.0	27371819
eCl@ss 8.0	27371819
eCl@ss 9.0	27371819

### ETIM

ETIM 5.0	EC001449
----------	----------

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / cULus Listed

#### Ex Approvals

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
-----------	--	---	---------------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

## Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

### Accessories

#### Accessories

#### Coding element

Coding profile - CP-MSTB - 1734634

Coding profile, is inserted into the slot on the plug or inverted header, red insulating material



Coding section - CR-MSTB - 1734401

Coding section, inserted into the recess in the header or the inverted plug, red insulating material



### Configuration memory

Configuration memory - PSR-M-MEMORY - 1105142



Optional memory block for the PSRmodular system for easy storage and backup of configuration data

### DIN rail connector

DIN rail bus connectors - ME 22,5 TBUS 1,5/ 5-ST-3,81 YE - 2200244



DIN rail connector, color: yellow, nominal current: 8 A (parallel contacts), rated voltage (III/2): 125 V, Number of positions per row: 5, pitch: 3.81 mm, mounting: DIN rail mounting, Locking: without, type of packaging: packed in cardboard, Item with gold-plated contacts, bus connectors for connecting with electronics housings, 5 parallel contacts

DIN rail bus connectors - ME 22,5 TBUS 1,5/ 5-ST-3,81 YE - 1PCS - 1225375



DIN rail connector, nominal current: 8 A (parallel contacts), rated voltage (III/2): 125 V, number of positions: 5, pitch: 3.81 mm, color: yellow, mounting: DIN rail, item with gold-plated contacts, bus connector for connecting to electronics housings, 5 parallel contacts

## Safety module - PSR-M-B1-SDI8-SDO2-DO2-PI - 1104972

### Accessories

#### Filter terminal block

Filter terminal block - PSR-FTB/1.5/11.5 - 2904476



Terminal block for filtering test pulses from safe semiconductor outputs with adjustable filter values (1.5  $\mu$ F/11.5  $\mu$ F), as well as for EMC filtering of 24 V signals up to an amperage of 2 A.

---

Filter terminal block - PSR-FTB/20/86 - 2904477



Terminal block for filtering test pulses from safe semiconductor outputs with adjustable filter values (20  $\mu$ F/86  $\mu$ F), as well as for EMC filtering of 24 V signals up to an amperage of 2 A.

---

#### Programming cable

USB cable - CABLE-USB/MINI-USB-3,0M - 2986135



USB connecting cable: USB plug type A to USB plug type Mini-B; length: 3 m

---