	Technical data		
	General specifications		
	Sensing range	60 2000 mm	
	Adjustment range	90 2000 mm	
	Dead band	0 60 mm	
	Standard target plate	100 mm x 100 mm	
	Transducer frequency	approx. 175 kHz	
	Response delay	approx. 150 ms	
	Indicators/operating means		
	LED green	solid green: Power on	
	LED yellow	solid: object in evaluation range flashing: program function	
	LED red	normal operation: "fault"	
		program function: no object detected	
	Electrical specifications		
	Operating voltage U <sub>B</sub>	10 30 V DC , ripple 10 % <sub>SS</sub>	
	No-load supply current I <sub>0</sub>	≤ 50 mA	
	Input/Output		
	Synchronization	bi-directional 0 level -U <sub>R</sub> +1 V	
		1 level: $+4$ V $+U_B$	
		input impedance: > 12 KOhm	
Model Number		synchronization pulse: $\geq$ 100 $\mu$ s, synchronization interpulse	
	Cumphranization from the second	period: ≥ 2 ms	
UB2000-F42-I-V15	Synchronization frequency Common mode operation	≤ 30 Hz	
	Multiplex operation	$\leq$ 30 Hz. n = number of sensors	
Single head system	Output		
-	Output type	1 analog output 4 20 mA	
Features	Default setting	evaluation limit A1: 90 mm, evaluation limit A2: 2000 mm,	
Analog output 4 mA 20 mA	Resolution	wide sound lobe 0.7 mm	
<ul> <li>Extremely small unusable area</li> </ul>	Deviation of the characteristic curve	± 1 % of full-scale value	
-	Repeat accuracy	$\pm 0.1$ % of full-scale value	
• TEACH-IN	Load impedance	0 300 Ohm	
<ul> <li>Interference suppression</li> </ul>	Temperature influence	± 1 % of full-scale value	
(adjustable divergence of sound	Ambient conditions		
cone in close range)	Ambient temperature	-25 70 °C (-13 158 °F)	
. Tomporature componention	Storage temperature	-40 85 °C (-40 185 °F)	
Temperature compensation	Mechanical specifications	Connector M10 x 1 E nin	
<ul> <li>Synchronization options</li> </ul>	Connection type Degree of protection	Connector M12 x 1 , 5-pin IP54	
•	Material		
<ul> <li>Mode of operation adjustable</li> </ul>	Housing	ABS	
D'	Transducer	epoxy resin/hollow glass sphere mixture; foam polyurethane,	
Diagrams		cover PBT	
	Mass	140 g	
Characteristic response curve	Compliance with standards and directives		
· · · · · · · · · · · · · · · · · · ·			
	Standard conformity	EN 60947-5-2:2007+A1:2012	
Distance Y [m]	Standards	EN 60947-5-2:2007+A1:2012 IEC 60947-5-2:2007 + A1:2012	
Flat surface 100 mm x 100 mm		EN 60947-5-7:2003	
		IEC 60947-5-7:2003	
0.5	Approvals and certificates		
	EAC conformity	TR CU 020/2011	
	UL approval	cULus Listed, General Purpose	
-0.5	CSA approval	cCSAus Listed, General Purpose	
	CCC approval	CCC approval / marking not required for products rated $\leq$ 36 V	
Round bar, Ø 25 mm			
0.0 0.5 1.0 1.5 2.0 2.5 3.0 3.5			
Distance X [m]			
wide sonic beam			
narrow sonic beam			

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 G

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com






UB2000-F42-I-V15

# Dimensions




**Additional Information** 

## Analogue output programmation



# **Electrical Connection**



Core colours in accordance with EN 60947-5-2.

## Pinout



#### Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



## Accessories

MH 04-3505 Mounting aid for FP and F42 sensors

MHW 11 Mounting brackets for sensors

DA5-IU-2K-V Process control and indication equipment

V15-G-2M-PVC Female cordset, M12, 5-pin, PVC cable

## **Functional Description**

The sensor may be completely parameterised via two keys on the side panel of the housing. As a special feature provided by this sensor, the ultrasound beam width may be adapted to the environmental conditions at the place of operation of the sensor.

## Specifying the evaluation limits:

The evaluation limits determine the characteristic line and the working range of the analog output.

Specifying the A1 evaluation limit by pressing the A1 key	
Holding down the A1key > 2 seconds	The sensor switches to learn mode and the user may specify the A1 evaluation limit
Position the target object at the desired distance	The yellow LED of the sensor flashes fast to indicate that the target object is recognised. The red LED flashes if the object is not recognised.
Briefly pressing the A1 key	The sensor terminates the specification of the A1 eval- uation limit and saves it as a non-volatile value. The specified value is invalid if the object is uncertain (i.e. the red LED lights up at irregular intervals). The learn mode is exited.

The A2 evaluation limit is specified via the A2 key, analogous to the description above.

Alternatively, the evaluation limits may also be specified electrically via the learn input. To specify the A1 evaluation limit, the learn input must be connected to

 $-U_B$ ; to specify the A2 evaluation limit, it must be connected to  $+U_B$ . Specified values are saved upon the disconnection from the learn input.

Evaluation limits may only be specified within the first 5 minutes after Power on. To modify the evaluation limits later, the user may specify the desired values only after a new Power On.

#### Proceed as follows to parameterise the output function and the ultrasound beam width:

Press the A1 key during Power on and hold down the key for another second to ensure that the sensor starts the two-step parameterisation of the operating modes.

## Step 1, parameterisation of the output function

The output function parameterised last is displayed. All output functions available may be selected via consecutive, brief strokes of the A2 key. These strokes are visualised via short flashes of the green LED.

Operating mode	Flash sequence of the green LED	A2 key
Rising edge	-Ö,Ö,	$\bigcirc$
Falling edge	-ऴॣ॔ pauseऴॣ॔	$\downarrow$
Zero point straight line		

The "Zero point straight line" setting fixedly specifies the A1 evaluation limit to 0 (see specification of the evaluation limits). The A2 evaluation limit determines the steepness of the output characteristic line.

Hold down the A1 key for 2 seconds to save the selected output mode, complete the parameterisation and ensure that the sensor returns to normal mode. If you briefly press the A1 key, Step 2 is entered (parameterisation of the ultrasound beam width).

## Step 2, parameterisation of the ultrasound beam width

Via Step 2, the ultrasound beam width may be adapted to the requirements of the corresponding application.

The beam width parameterised last is displayed first. Available beam width settings may be selected via consecutive, brief strokes of the A2 key. These strokes are visualised via the flash sequence of the red LED.

133990\_eng.xml

Date of issue: 2016-08-01

Release date: 2016-08-01 13:41

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Beam width	Flash sequence of the red LED	A2 key
Small beam	-Ŏ pause -Ŏ	$\bigcirc$
Medium beam	-ऴॣ॔ pauseऴॣ॔	$\checkmark$
Large beam	- Ŏ, Ŏ, Ŏ, pause	$\bigcup$

Hold down the A1 key for 2 seconds to save the selected beam shape, terminate the parameterisation and ensure that the sensor returns to normal mode. Briefly press the A1 key to return to Step 1 (parameterisation of the output function).

If the parameterisation mode is not terminated within 5 minutes (hold down the A1 key for 2 seconds), the sensor aborts this mode without modifying the settings.

#### Synchronisation

The sensor provides a synchronisation port to suppress mutual influencing. If this port has not been connected, the sensor works at an internally generated cycle rate. Several sensors may be synchronised via the following options.

#### External synchronisation:

The sensor may be synchronised via the external application of a square wave voltage. A synchronisation pulse on the synchronisation input initiates a measuring cycle. The pulse width must be greater than 100  $\mu$ s. The measuring cycle is started with the falling edge. A low level > 1 s or an open synchronisation input initiate the transition to normal sensor mode. A high level on the synchronisation input deactivates the sensor.

#### Two modes are possible:

- Several sensors are controlled via the same synchronisation signal. The sensors work in common mode.
- The synchronisation pulses are forwarded at cyclic intervals to respectively one single sensor. The sensors work in multiplex mode.

#### Self-synchronisation:

The synchronisation ports of up to 5 sensors suitable for self-synchronisation are connected to each other. These sensors work in multiplex mode after Power on. The On delay increases depending on the number of sensors to be synchronised. While the learn mode is active, no synchronisation is possible (and vice-versa). To specify the switching points, the sensors must be operated in non-synchronised mode.

## Note:

Release date: 2016-08-01 13:41 Date of issue: 2016-08-01 133990 end.xml

Refer

Pepp

www.pepperl-fuchs.com

If the synchronisation option is not used, the synchronisation input must be connected to ground (0V) or the sensor must be operated with a (4-pole) V1 connecting cable.

erl+Fuchs Group	USA: +1 330 486 0001	Germany: +49 621 776 4411	Singapore: +65 6779 9091
to "General Notes Rela	ting to Pepperl+Fuchs Product Inforr	nation".	

fa-info@de.pepperl-fuchs.com

fa-info@sg.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

