


Model 4846-UU SMA Plug to SMA Plug, RG178B/U





Model 4846-UU SMA Plug to SMA Plug, RG178B/U

Small size, and durability for confident connections

Features

- DC 4GHz bandwidth.
- Connectors are precision machined and gold-plated for low loss.
- Perfect for applications where space, weight, performance and ease of connection are required.

Materials

SMA Male Connector:

Center Contact: Brass, Gold Plated Connector Body: Brass, Gold Plated Crimp Ferrule: Copper, Nickel Plated

Insulators: PTFE

Specifications

Cable Type	RG178B/U
Impedance	50Ω
Frequency Range	DC - 4GHz
Insulation Resistance	≥ 5000 MΩ
Working Voltage	170 Vrms max.
Dielectric Withstand	
Voltage	500 Vrms min.
Temperature Range	-65° C to +165°C
	(-85°F to +329°F)

Ordering Information

Model: 4846

Cable Designator: **UU** = RG178B/U

Standard Lengths: 12", 24", 36", 48", 60"

- 12" ± .157" (305mm ± 4mm)

- 24" ± .275" (610mm ± 7mm)

- 36" ± .394" (914mm ± 10mm)

- 48" ± .512" (1219mm ± 13mm)

 $-60" \pm .630" (1524 mm \pm 16 mm)$

Ordering Example: **4846-UU-48**, Cable is RG178B/U with length of 48" (1219mm)

USA: Sales: 800-490-2361

Technical Support: technicalsupport@pomonatest.com

Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.