NOC

AOC Q27T1 computer monitor $68.6 \text{ cm} (27") 2560 \times 1440 \text{ pixels}$ Quad HD LED Silver

Brand : AOC Product code: Q27T1

Product name: Q27T1

Q27T1 - Outstanding, 3-sides frameless design, 27-inch QHD IPS panel with vivid colours

AOC Q27T1 computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD LED Silver:

Outstanding, 3-sides frameless design, 27-inch QHD IPS panel with vivid colours

Designed by Studio F.A. Porsche, the Q27T1 impresses with an asymmetrical metal stand, 1440p resolution, 27", 3-sides frameless IPS panel with a wide colour gamut (90% NTSC). AOC Q27T1. Display diagonal: 68.6 cm (27"), Display resolution: 2560 x 1440 pixels, HD type: Quad HD, Display technology: LED, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Product colour: Silver







Display		Ports & interfaces	
Display diagonal * 68.6 cm (27") Display brightness (typical) 350 cd/m² Display resolution * 2560 x 1440 pixels Native aspect ratio * 16:9 Response time 5 ms	350 cd/m ² 2560 x 1440 pixels 16:9	DisplayPorts quantity DisplayPort version Audio input Headphone out * Headphone outputs	1 1.2 X 1
HD type * Display technology *	Quad HD LED	Headphone connectivity Microphone in	3.5 mm ✓
Backlight type	W-LED	Ergonomics	
Screen shape * Supported graphics resolutions Contrast ratio (typical) * Contrast ratio (dynamic) Maximum refresh rate * Viewing angle, horizontal Viewing angle, vertical Display number of colours *	Flat 2560 x 1440 1000:1 50000000:1 75 Hz 178° 178° 16.78 million colours	Cable lock slot type Height adjustment * Tiltable Tilt angle range On Screen Display (OSD) On Screen Display (OSD) languages	Kensington
3D Panel type *	X IPS	Number of OSD languages	Italian, Japanese, Korean, Polish, Portuguese, Russian, SER
Pixel pitch	0.2331 x 0.2331 mm		10
Horizontal scan range	30 - 114 kHz	Power	
Vertical scan range Viewable size, horizontal Viewable size, vertical Colour depth RGB colour space sRGB coverage (typical)	48 - 75 Hz 96.8 cm 33.6 cm 8 bit sRGB 107%	Energy efficiency class (SDR) * F Energy consumption (SDR) per 1000 hours * 26 kWh Power consumption (typical) * 30 W Power consumption (standby) * 0.3 W Power consumption (off) 0.3 W	26 kWh 30 W 0.3 W
Adobe RGB coverage	90%	AC input voltage	100 - 240 V
Performance AMD FreeSync type	FreeSync	AC input frequency External power adapter Energy efficiency scale	50 - 60 Hz ✓ A to G
AMD FreeSync *	√	Sustainability	
AMD FreeSync refresh rate range VESA Adaptive Sync support Flicker-free technology	48 - 75 Hz ✓	Sustainability certificates	Rohs, Epeat Silver, Energy Star

Performance		Weight & dimensions	
Low Blue Light technology	✓	Width (with stand)	610.6 mm
Multimedia		Depth (with stand)	160.1 mm
Built-in speaker(s) * Built-in camera *	×	Weight (with stand)	460.7 mm 4.12 kg 3.29 kg
Design		Packaging data	
Market positioning * Product colour * Frameless design Feet colour Heavy metals free Certification	Home Silver ✓ Silver Hg (mercury) CE	Cables included DisplayPort cable length HDMI cable length	AC, HDMI 1.8 m 1.8 m
		Recycling data	
		Recyclable material	100%
Ports & interfaces		Other features	
Built-in USB hub * DVI port HDMI * HDMI ports quantity HDMI version	X X V 2 1.4	Power cable length On/off switch TV tuner integrated Recyclable packaging material Bezel thickness type Mean time between failures (MTBF) Anti-Blue-Light technology	1.2 m ✓ X 100% Frameless 50000 h



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.