



TVS-h1688X-W1250-32G	
CPU	Intel® Xeon® W-1250 6-core/12-thread processor, up to 4.7 GHz
CPU Architecture	64-bit x86
Graphic Processors	Intel® UHD Graphics P630
Floating Point Unit	Yes
Encryption Engine	Yes (AES-NI)
Hardware-accelerated Transcoding	Yes
System Memory	32GB ECC UDIMM DDR4 (2 x 16 GB)
Maximum Memory	128 GB (4 x 32 GB)
Memory Slot	4 x UDIMM DDR4
Flash Memory	5GB (Dual boot OS protection)
Drive Bay	12 x 3.5-inch SATA 6Gb/s, 3Gb/s + 4 x 2.5-inch SATA 6Gb/s, 3Gb/s
Drive Compatibility	3.5-inch bays: 3.5-inch SATA hard disk drives 2.5-inch SATA solid state drives 2.5-inch bays: 2.5-inch SATA solid state drives
Hot-swappable	Yes
M.2 Slot	2 x M.2 22110/2280 NVMe PCIe Gen3 x4 slots
SSD Cache Acceleration Support	Yes
GPU pass-through	Yes
2.5 Gigabit Ethernet Port (2.5G/1G/100M)	4 (also support 10M)
5 Gigabit Ethernet Port (5G/2.5G/1G/100M)	Optional via an adapter

10 Circleit Ethania ( D. )	2 × 10 CPASE T (10 C (1 C)
10 Gigabit Ethernet Port	2 x 10GBASE-T (10G/1G)
25 Gigabit Ethernet Port	Optional via an adapter
Wake on LAN (WOL)	Yes
Jumbo Frame	Yes
Thunderbolt Port	Optional via the QXP-T32P 2-port Thunderbolt 3 PCIe adapter
PCIe Slot	3 Slot 1: PCIe Gen3 x8 Slot 2: PCIe Gen3 x4 Slot 3: PCIe Gen3 x4
USB 3.2 Gen 2 (10Gbps) Port	2 x Type-C 4 x Type-A
HDMI Output	1, HDMI 1.4b (up to 4096 x 2160 @ 30Hz)
Audio Input	- (No longer available on units manufactured on or after 2021/1/1)
Audio Output	- (The line out jack and speaker are no longer available on units manufactured on or after 2021/1/1)
Form Factor	Tower
LED Indicators	System status, LAN, USB, Disk 1~16, M.2 SSD 1~2
LCD Display/ Button	Yes
Buttons	Power, Reset, USB Auto Copy
Dimensions (HxWxD)	303.84 × 369.89 × 319.8 mm
Weight (Net)	13.41 kg
Weight (Gross)	16.3 kg
Operating temperature	0 - 40°C (32°F - 104°F)
Storage Temperature	-20 - 70°C (-4°F - 158°F)
Relative Humidity	5-95% RH non-condensing, wet bulb: 27°C (80.6°F)
Power Supply Unit	550W PSU, 100~240V
Power Consumption: HDD Sleep Mode	91.26 W
Power Consumption: Operating Mode, Typical	108.67 W
Fan	System fan: 3 x 80mm, 12VDC CPU fan: 2 x 97mm, 12VDC
System Warning	Buzzer
Kensington Security Slot	Yes

Max. Number of 10000 Concurrent Connections (CIFS) - with Max. Memory

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications.

Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting.

\* Sound Level Test

Environment: Refer to ISO 7779; Maximum HDD loaded; Bystander Position; Average data from 1 meter in front of operating NAS. Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.