Features

- 80 to 305VAC input voltage range
- 150% peak power capability

Wide temperature range: -40°C to +90°C

- **Regulated Converter**
- No load power consumption <150mW Household and ITE certified
- 4kVac isolation

Description

The RAC04-K/277 series delivers an uncompromising 4 watts of continuous output power (6W peak) in harsh industrial and household environments. These modules deliver full load output power from -40°C to 75°C across the entire input range of 80VAC to 305VAC and are certified for operation with power derating up to 90°C air ambient. A peak load capability of up to 150% supports dynamic power demands of applications. This series of fully encapsulated AC/DC modules is a complete solution without the need for external components which supports Ecodesign Lot 6 standby mode operation for worldwide applications in automation, industry 4.0, IoT, household, and home automation. With international safety and EMC certifications for industrial, domestic, ITE, and household applications, these are some of the most versatile power modules on the market. Due to their reinforced class II installation rating for floating outputs and their significantly wide margin to class B emissions compliance without external components and a certified 4kV AC (5.25 kV DC) isolation, these are the easiest to use modular power solutions in the industry.



RAC04-K/277





Selection Guide						
Part Number	Input Voltage Range [(VAC]	Output Voltage [VDC]	Output Current ⁽¹⁾ [mA]	Efficiency typ. ⁽²⁾ [%]	Max. Capacitive Load [µF)	
RAC04-05SK/277	80-305	5	800	76	7200	
RAC04-12SK/277	80-305	12	333	78	1000	
RAC04-15SK/277	80-305	15	267	80	820	
RAC04-24SK/277	80-305	24	167	80	220	
On Request						
RAC04-3.3SK/277	80-305	3.3	1200	73	10000	



Notes:

Note1: Refer to "Line Derating" graph

Note2: Measured @ 230VAC/50Hz at +25°C with constant resistant mode at full load

IEC60950-1 (pending) IEC62368-1 (pending) UL62368-1 certified CSA/CAN C22.2 No. 62368-1-14 certified EN62368-1 compliant EN60335-1 compliant IEC/EN61558-1 compliant IEC/EN61558-2-16 compliant EN55032 compliant EN55024 compliant EN55014-1 /-2 compliant IEC/EN61204-3 compliant FCC 47 Part 15 CB Report (pending)

Model Numbering



R/

uering Examples		
AC04-05SK/277 =	5Vout	Single
AC04-12SK/277 =	12Vout	Single

RAC04-K/277

Series

BASIC CHARACTERISTICS					
Input Voltage Range (3)	nom. Vin= 277VAC		80VAC 110VDC		305VAC 390VDC
Input Current	115 ¹ 230 ¹	VAC VAC			250mA 100mA
Inrush Current	cold start at +25°C	115VAC 230VAC			10A 20A
No load Power Consumption	80-305VA0	C, 50/60Hz		100mW	150mW
ErP Standby Mode Conformity (Output Load Capability)	Input Power=	0.5W 1W			0.3W 0.65W
Input Frequency Range	AC ir	nput	47Hz		63Hz
Start-up Time				20ms	
Rise Time				10ms	
Hold-up time	115VAC 230VAC			20ms 80ms	
Minimum Load			0%		
Power Factor	115VAC 230VAC		0.6 0.45		
Internal Operating Frequency	full l	oad		130kHz	
Output Ripple and Noise (4)					1% of nom. Vout

Notes:

Note3: The products were submitted for safety files at AC-Input operation

Measurements are made with a $1.0\mu F$ MLCC and a $10\mu F$ MLCC across output Note4:

Efficiency vs. Load





continued on next page

RAC04-K/277 Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



REGULATIONS	
Parameter	Condition Value
Output Accuracy	±1.0% typ.
Line Regulation	±0.5% typ.
Load Regulation	1.0% typ.
Transient Response	25% load step change4.0% max.recovery time500µs
Deviation vs. Load (80-305VAC) RAC04-05SK/27	7 RAC04-12SK/277
0.5	0.5
0 /iation [%]	
-0.5	-0.5
Output Load [%]	Output Load [%]
	continued on next page

REV.: 0/2019

RAC04-K/277

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Series



PROTECTIONS			
Parameter	T	уре	Value
Input Fuse (5)	int	ternal	T1A, slow blow
Short Circuit Protection (SCP)			Hiccup Mode, auto recovery
Over Voltage Protection (OVP)			125% - 195%, Hiccup Mode
Over Voltage Category (OVC)			OVCII
Over Current Protection (OCP)			150% - 210%, Hiccup Mode
Class of Equipment			Class II
Isolation Voltage (safety certified) (6)	I/P to O/P	1 mintue	5.75kVDC 4kVAC
Isolation Resistance	Viso=	500VDC	1GΩ min.
Isolation Capacitance	I/P to O/P	100kHz, 0.1V	100pF max.
Insulation Grade			reinforced
Leakage Current			0.25mA max.

Notes:

Note5: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage.

Peak Load Capability (7)

Peak Load Calculation

- $P_{nom} = nom.$ output power [W]
- P_{P} = peak output power (6W max.) [W]
- P, = recovery output power [W] [S]
- t₁ = peak time set (10s max.)
- = recovery time (min. $4 \times t_1$) t₂
- k = safety factor 1.3
- [S] []
- $\mathbf{P_{r}} = \frac{P_{nom} \, x \, (t_1 + t_2) P_{P} \, x \, t_1}{t_2 \, x \, k}$



Practical Example:

Take the RAC04-05SK/277 at 230VAC input Voltage and full load at $T_{AMB} = 50^{\circ}C$ (4W).

 $\mathbf{P}_{r} = \frac{4 \times (10 + 4 \times 10) - (6 \times 10)}{4 \times 10 \times 1.3} = \underline{2.69W}$

 $P_{nom.} =$ please refer to derating graph (4W)

Pp = 6W

$$t_1 = 10s$$

$$t_2 = min. 4 \times t_1$$

RAC04-K/277 Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

ENVIRONMENTAL						
Parameter	Condition			Value		
Approxima Tomporatura Papao	@ natural convection 0.1m/c full lo		oad	-40°C to +75°C		
Operating temperature hange		refer to "Derating Graph"		-40°C to +90°C		
Maximum Case Temperature				+100°C		
Temperature Coefficient				±0.02%/K		
Operating Altitude ⁽⁸⁾	according to IEC62368-1 (EN60335-1)		-1)	5000m (4000m)		
Operating Humidity	non-condensing			20% - 95%, RH max.		
Pollution Degree				PD2		
Vibration	according to MIL-STD-202G			10-500Hz, 2G 10min. / 1 cycle, periode 60min. each along x, y, z axis		
MTBF	according to MIL-HDBK-2	217F, G.B	+25°C	>500 x 10 ³ hours		
Design Lifetime	230VAC		+25°C	125 x 10 ³ hours		
			+70°C	51 x 10 ³ hours		
	277VAC		+25°C	105 x 10 ³ hours		
			+70°C	37 x 10 ³ hours		

Notes:

Note8: Recognized by safety agency for safe operation up to 5000m. High altitude operation may impact the performance and lifetime. Please contact RECOM tech support for advice.

Line Derating

Derating Graph

(@ Chamber and natural convection 0.1m/s)



SAFETY AND CERTIFICATIONS					
Certificate Type	Report / File Number	Standard			
Audio/video, information and communication technology equipment - Safety requirements	E224736	UL62368-1:2014, 2nd Edition CAN/CSA C22.2 No. 62368-1-14, 2nd Edition			
Information Technology Equipment, General Requirements for Safety (CB)	(pending)	IEC60950-1:2005 + A2:2013, 2nd Edition			
Audio/video, information and communication technology equipment - Safety requirements (CB)	(pending)	IEC/EN62368-1:2014, 2nd Edition			
Audio/video, information and communication technology equipment - Safety requirements (LVD)		EN62368-1:2014 + A11:2017			
Household and similar electrical appliances - Safety - Part 1: General requirements (LVD)		EN60335-1:2012 + A1:2018			
Safety of power transformers, power supplies, reactors and similar products for supply voltages		IEC61558-1:2005 2nd Edition + A1:2009			
up to 1100 V		EN61558-1:2005 + A1:2009			

RAC04-K/277

Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Certificate Type	Report / File Number	Standard
Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100 V - Part 2-16: Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units (LVD)		IEC61558-2-16:2009 + A1:2013, 1st Edition EN61558-2-16:2009 + A1:2013
Safety requirements for electrical equipment for measurement, control and laboratory use - Part 1: General requirements (LVD)		EN61010-1:2010
RoHS2		RoHs-2011/65/EU + AM-2015/863
EMC Compliance (Household)	Report / File Number	Standard / Criterion
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 1: Emission ®		EN55014-1:2006 + A2:2011
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 2: Immunity		EN55014-2:2015
ESD Electrostatic discharge immunity test	Air \pm 8kV; Contact \pm 4kV	IEC61000-4-2:2008, Criteria B
Fast Transient and Burst Immunity	AC Power Port: ±1.0kV	IEC61000-4-4:2012, Criteria B
Surge Immunity	AC Power Port: L-N ± 1.0 kV	IEC61000-4-5:2014, Criteria B
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port: 3V	EN61000-4-6:2013, Criteria A
Voltage Dips and Interruptions	Voltage Dips: 100% 60%	EN61000-4-11:2004, Criteria C EN61000-4-11:2004, Criteria C
EMC Compliance (Multimedia)	Condition	Standard / Criterion
Low voltage power supplies, d.c. output - Part 3: Electromagnetic compatibility		IEC/EN61204-3:2000, Class B
Electromagnetic compatibility of multimedia equipment - Emission requirements (9)		EN55032:2015, Class B
Information technology equipment - Immunity characteristics - Limits and methods of measurement		EN55024:2010 + A1:2015
ESD Electrostatic discharge immunity test	Air ±2,4,8kV; Contact ±4kV	IEC61000-4-2:2008, Criteria B
	10V/m (80 - 1000MHz)	IEC61000-4-3, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m (1800MHz, 2600Mhz, 3500MHz, 5000MHz)	IEC61000-4-3:2006 + A2:2010, Criteria A
Foot Transient and Durat Immunity	AC Power Port: ±2.0kV	IEC61000-4-4, Criteria B
Fast transient and Burst initiumity	AC Power Port: ±1.0kV	IEC61000-4-4:2012, Criteria A
Surge Immunity	AC Power Port: L-N ±1.0kV	IEC61000-4-5:2014, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port: 10V	IEC61000-4-6, Criteria A
	100% / 30%	IEC61000-4-11:2004, Criteria A
Voltage Dire and Interruptions	Voltage Dips: 70%	IEC61000-4-11:2004, Criteria B
voltage bips and intentipuons	40%	IEC61000-4-11:2004, Criteria C
	Interruptions: >95%	IEC61000-4-11:2004, Criteria A
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013
Limitations on the amount of electromagnetic interference allowed from digital and electronic devices	WTS19S01003086E	FCC 47 Part 15 Subpart B:2017, Class B
Notes:		

Note9: If output is connected to GND, please contact RECOM tech support for further information

DIMENSION and PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
	case/baseplate	plastic, (UL94 V-0)		
Material	potting	silicone, (UL94 V-0)		
	PCB	FR4, (UL94 V-0)		
Dimension (LxWxH)		36.7 x 27.2 x 17.4mm		
Weight		30g typ.		

continued on next page

RAC04-K/277

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Series



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	tube	506.4 x 29.8 x 25.5mm		
Packaging Quantity		12pcs		
Storage Temperature Range		-40°C to +85°C		
Storage Humidity	non-condensing	20% to 90% RH max.		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.