# Features Constant Current LED Driver

- 7W Class II AC-DC LED power supply
- Suitable for high brightness LED
- 250mA, 350mA, 500mA and 700mA constant current operation
- 3.75kVAC isolation
- Fused input and SCP, OCP, OVP, OLP
- IP67 rated

#### Description

The RACD07 is a constant current 7W AC/DC source for LED lighting with a wide input voltage range. The LED drivers are available with constant current outputs of 250mA, 350mA, 500mA or 700mA. The series is IP67 rated and suitable for use in dry, damp or wet areas. RACD07 drivers have a 3 year warranty.

<b>Selection Gui</b>	ide				
Part Number	Input Voltage Range	Mo		Efficiency min.	Rated Power max.
	[VAC]	[VDC]	[mA]	[%]	[W]
RACD07-250	90-295	14-28	250	75	7
RACD07-350	90-295	10-20	350	70	7.3
RACD07-500	90-295	5-14.5	500	70	7.2
RACD07-700	90-295	3-10.5	680	70	7.4

All LED Drivers may not be used without a load. They must be switched on the primary side only.


Noncompliance may damage the LED or reduce its lifetime.

#### Notes:

Note1:

Constant current operation region is within 75%-100% rated output voltage. This is the suitable operation region for LED related applications, but please reconfirm special electrical requirements for some specific system design.

#### **Model Numbering**



#### Specifications (measured @ ta= 25°C and 115/230VAC)

BASIC CHARACTERISTICS					
Parameter	Condition	Min.	Тур.	Max.	
Innut Valtage Denge		90VAC	230VAC	295VAC	
Input Voltage Range		120VDC		415VDC	
Input Current	full load, 100VAC			200mA	
Inrush Current	230VAC			10A	
No Load Power Consumption	230VAC			0.5W	
Input Frequency Range		47Hz		63Hz	
Power Factor		0.90			
Start-up Time				1s	
Hold-up Time		18ms			
Set-up Time	full load, 230VAC			0.5s	
Internal Operating Frequency			45kHz		
Output Ripple Current (2)	20MHz BW		30mAp-p		

#### Notes:

Note2: Measured with a 12" twisted pair-wire terminated with  $0.1\mu F$  &  $47\mu F$  parallel capacitor continued on next page



### RACD07

# 7 Watt Constant Current Single Output













UL8750 certified UL1310 certified CAN/CSA-C22.2 No. 223-M91 certified IEC/EN61347 certified IEC/EN61347-2-13 certified EAC certified




## RACD07

## **Series**

#### Specifications (measured @ ta= 25°C and 115/230VAC)





REGULATIONS				
Parameter	Condition	Value		
Output Voltage Accuracy	includes: line, load and tolerance	±5%		
Output Current Accuracy		±3% typ. / ±7% max.		

PROTECTION		
Parameter	Condition	Value
Internal Input Fuse		T1A, slow blow
Short Circuit Protection (SCP)		Hiccup Mode, autorecovery after fault condition is removed
Overload Protection (OLP)		105% - 120% typ.
Over Current Protection (OCP)		Constant current mode protection
Isolation Voltage	I/P to O/P	3.75kVAC / 1 minute
Isolation Resistance	500VDC	100M $\Omega$ min.

#### Notes:

Note3: Refer to local wiring regulations if input over-current protection is also required

#### Maximum loading of automatic circuit breakers\*

\* @ 115VAC, 10hm, 90° phase angle and max. load

Circuit Breaker	Circ	uit Brea	ker Cur	rent
Тур	10A	16A	20A	25A
С	101	128	171	228

\* @ 230VAC, 10hm, 90° phase angle and max. load

Circuit Breaker	Circuit Breaker Current			
Тур	10A	16A	20A	25A
В	61	100	121	150
С	121	164	221	291

\* @ 277VAC, 10hm, 90° phase angle and max. load

Circuit Breaker	Circuit Breaker Current			
Тур	10A	16A	20A	25A
В	70	115	139	172
С	139	188	254	334


ENVIRONMENTAL					
Parameter	Condition		Value		
Operating Temperature Range	@ natural convection 0.1m/s, full	load	-20°C to +50°C		
Max. Case Temperature			+65°C		
Operating Humidity	non condensing		20% - 90% RH		
IP Rating			IP67		
Vibration	10-500Hz, 2G; 10 minute/cycl	Э	1 cycle period for 60 min each along X, Y and Z axes		
Design Lifetime	+25°C ambient		70 x 10 <sup>3</sup> hours		
MTBF	according to MIL-HDBK-217F, G.B.	-25°C	200 x 10 <sup>3</sup> hours		
continued on next page					



## RACD07

## Series

#### **Specifications** (measured @ ta= 25°C and 115/230VAC)



SAFETY AND CERTIFICATIONS				
Certificate Type (Safety)	Report Number			
Standard for LED Equipment for use in Lighting Products		UL8750, 1st Edition, 2012		
Standard for Class 2 Power Units	E340696-1-7	UL1310, 6th Edition, 2013		
LED Equipment for Lighting Applications		CAN/CSA-C22.2 No. 250.13-12, 1st Edition, 2013		
Safety of control gear for LED modules		IEC/EN61347-2-13, 2nd Edition, 2006		
Safety requirements for lamp controlgear	PSE102-0283	IEC61347-1, 2nd Edition, 2010 EN61347-1, 2nd Edition, 2011		
RoHS2		RoHS-2011/65/EU + AM-2015/863		
EAC	RU Д- АТ.А ГОЗ. В.67369	TP TC 004/020, 2011		
EMC Compliance	Condition	Standard / Criterion		
Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment		EN55015, Class B		
Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement		CISPR22, 3rd Edition, 1997		
Radio Frequency Devices, Subpart B - Unintentional Radiators		CFR 47, Part 15, Class B		
Methods of Measurement of Radio-Noise Emissions from Low-Voltage Electrical and Electronic Equipment in the Range of 9 kHz to 40 GHz		ANSI C63.4		
Alternating Current High Voltage Power Systems		Canadian ICES-004 issue 5, 2012		
Limits for harmonic current emissions		IEC61000-3-2, 2009		
Limitation of voltage fluctuations/flicker in low-voltage systems		IEC61000-3-3, 2008		
ESD Electrostatic discharge immunity test	±8kV Air Discharge, ±4kV Contact Discharge	EN61547, 2009 / IEC61000-4-2, 2008		
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61547, 2009 / IEC61000-4-3, 2010		
Fast Transient and Burst Immunity	±0.5kV / ±1kV (AC Input)	EN61547, 2009 / IEC61000-4-4, 2012		
Surge Immunity	±0.5kV (AC Input)	EN61547, 2009 / IEC61000-4-5, 2005		
Immunity to conducted disturbances, induced by radio-frequency fields	3kV	EN61547, 2009 / IEC61000-4-6, 2008		
Power Frequency Magnetic Field Immunity	3A/m at 50/60Hz	EN61547, 2009 / IEC61000-4-8, 2009		
Voltage Short Interruptions	100% reduction, 10ms	EN61547, 2009 / IEC61000-4-11, 2004		
Voltage Dips	30% reduction, 200ms	EN61547, 2009 / IEC61000-4-11, 2004		





# RACD07

### **Series**

#### Specifications (measured @ ta= 25°C and 115/230VAC)

DIMENSION and PHYSICAL CHARACTERISTICS			
Parameter	Туре	Value	
Material	case	plastic (UL94V-2)	
	potting	silicone (UL94V-0)	
Dimension (LxWxH)		57.0 x 40.8 x 24.0mm	
Weight		75g	





PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	cardboard box	286.0 x 201.0 x 88.0mm		
Packaging Quantity		25pcs		
Storage Temperature Range		-40°C to +85°C		
Storage Humidity	non condensing	10% - 90% RH		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.